



Product Description

MHN-TD

Double-ended quartz Metal-halide lamp

Benefits

- All types are UV-Block for reduced health and fading risks

Features

- Quartz discharge tube containing high-pressure mercury and a mixture of dysprosium, holmium and thulium halides (4200 K) or tin iodide (3000 K), with sodium and thallium added for color correction and arc stabilization
- Double-ended lamps housed in a tubular clear UV-Block quartz evacuated outer envelope
- Restricted burning position

Application


- Indoors - accent lighting, general lighting in downlighters, e.g. in shops and malls
- Downlighters, uplighters and wall-washers, e.g. in shops and malls
- Outdoors - floodlighting monuments, facades and billboards

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MHN-TD

Dimensional drawing



Product	D (max)	D	O	C (max)
MHN-TD 70W/842 RX7s 1CT/12	19.5 mm	0.75 in	7.7 mm	117.6 mm
MHN-TD 150W/842 RX7s 1CT/12	23.0 mm	0.89 in	17.8 mm	135.4 mm
MHN-TD 70W/730 RX7s 1CT/12	19.5 mm	0.75 in	7.7 mm	117.6 mm
MHN-TD 150W/730 RX7s 1CT/12	23.0 mm	0.89 in	17.8 mm	135.4 mm

Controls and Dimming

Dimmable	No
----------	----

General Information

Cap-Base	RX7S
Life To 5% Failures (Min)	4000 h
Life To 5% Failures (Nom)	5000 h
Operating Position	P45

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	TD

Approval and Application

Order Code	Full Product Name	Energy	Mercury (Hg)	Mercury (Hg)
		Consumption kWh/	Content	Content
		1000 h	(Max)	(Nom)
21532500	MHN-TD 70W/842 RX7s 1CT/12	77 kWh	11 mg	11 mg
21536300	MHN-TD 150W/842 RX7s 1CT/12	155 kWh	12.3 mg	12.3 mg

Order Code	Full Product Name	Energy	Mercury (Hg)	Mercury (Hg)
		Consumption kWh/	Content	Content
		1000 h	(Max)	(Nom)
21530100	MHN-TD 70W/730 RX7s 1CT/12	77 kWh	13.4 mg	13.4 mg
21534900	MHN-TD 150W/730 RX7s 1CT/12	155 kWh	18 mg	18 mg

Operating and Electrical

Order Code	Full Product Name	Lamp Current (EM) (Nom)	Voltage (Max)	Voltage (Min)	Voltage (Nom)	Power (Nom)
21532500	MHN-TD 70W/842 RX7s 1CT/12	1.0 A	100 V	80 V	90 V	77.0 W
21536300	MHN-TD 150W/842 RX7s 1CT/12	1.8 A	108 V	88 V	98 V	155.0 W
21530100	MHN-TD 70W/730 RX7s 1CT/12	0.98 A	98 V	78 V	90 V	77.0 W
21534900	MHN-TD 150W/730 RX7s 1CT/12	1.8 A	106 V	86 V	96 V	155.0 W

General Information

Order Code	Full Product Name	Life To 20%	Life To 20%	Life To 50%	Life To 50%
		Failures	Failures	Failures	Failures
		(Min)	(Nom)	(Min)	(Nom)
21532500	MHN-TD 70W/842 RX7s 1CT/12	6500 h	8000 h	8500 h	10500 h

MHN-TD

Order Code	Full Product Name	Life To 20%	Life To 20%	Life To 50%	Life To 50%
		Failures (Min)	Failures (Nom)	Failures (Min)	Failures (Nom)
21536300	MHN-TD 150W/842 RX7s 1CT/12	6500 h	8000 h	8500 h	10500 h
21530100	MHN-TD 70W/730 RX7s 1CT/12	5800 h	7000 h	7500 h	9000 h

Order Code	Full Product Name	Life To 20%	Life To 20%	Life To 50%	Life To 50%
		Failures (Min)	Failures (Nom)	Failures (Min)	Failures (Nom)
21534900	MHN-TD 150W/730 RX7s 1CT/12	6500 h	8000 h	8500 h	10500 h

Luminaire Design Requirements

Order Code	Full Product Name	Bulb Temperature (Max)
21532500	MHN-TD 70W/842 RX7s 1CT/12	500 °C
21536300	MHN-TD 150W/842 RX7s 1CT/12	650 °C

Order Code	Full Product Name	Bulb Temperature (Max)
21530100	MHN-TD 70W/730 RX7s 1CT/12	500 °C
21534900	MHN-TD 150W/730 RX7s 1CT/12	650 °C

Light Technical (1/3)

Order Code	Full Product Name	Chromaticity	Chromaticity	Colour Code	Colour Designation	Correlated Colour Temperature (Nom)	Colour	Lumen Maintenance 10000 h (Min)
		Coordinate X (Nom)	Coordinate Y (Nom)				Rendering Index (Nom)	
21532500	MHN-TD 70W/842 RX7s 1CT/12	0.371	0.366	842	Cool White (CW)	4200 K	75	40 %
21536300	MHN-TD 150W/842 RX7s 1CT/12	0.371	0.366	842	Cool White (CW)	4200 K	81	60 %
21530100	MHN-TD 70W/730 RX7s 1CT/12	0.434	0.398	730	Warm White (WW)	3000 K	65	45 %
21534900	MHN-TD 150W/730 RX7s 1CT/12	0.434	0.398	730	Warm White (WW)	3000 K	67	50 %

Light Technical (2/3)


Order Code	Full Product Name	Lumen Maintenance	Lumen Maintenance	Lumen Maintenance	Lumen Maintenance	Lumen Maintenance	Luminous Efficacy	Luminous Efficacy	Luminous Flux	Luminous Flux
		10000 h (Nom)	2000 h (Min)	2000 h (Nom)	5000 h (Min)	5000 h (Nom)	(rated) (Min)	(rated) (Nom)	(Nom)	(Rated) (Min)
21532500	MHN-TD 70W/842 RX7s 1CT/12	75 %	79 %	85 %	68 %	80 %	67 lm/W	75 lm/W	5800 lm	5220 lm
21536300	MHN-TD 150W/842 RX7s 1CT/12	70 %	74 %	80 %	68 %	75 %	73 lm/W	81 lm/W	12500 lm	11250 lm
21530100	MHN-TD 70W/730 RX7s 1CT/12	55 %	59 %	65 %	53 %	60 %	67 lm/W	75 lm/W	5800 lm	5220 lm
21534900	MHN-TD 150W/730 RX7s 1CT/12	60 %	69 %	75 %	58 %	65 %	81 lm/W	90 lm/W	13400 lm	12510 lm

Light Technical (3/3)

Order Code	Full Product Name	Luminous Flux (Rated) (Nom)
21532500	MHN-TD 70W/842 RX7s 1CT/12	5800 lm
21536300	MHN-TD 150W/842 RX7s 1CT/12	12500 lm

Order Code	Full Product Name	Luminous Flux (Rated) (Nom)
21530100	MHN-TD 70W/730 RX7s 1CT/12	5800 lm
21534900	MHN-TD 150W/730 RX7s 1CT/12	13900 lm

Colour Rendering Diagrams



LDCR_MHN-TD_70W-Colour rendering diagram

