



# Smart Halogen Downlight – a reliable way to make your merchandise stand out

## Smart Halogen Downlight QBS020

Shop owners opening a new outlet or refurbishing their current installation and contractors looking for attractive propositions for their customers (small/non-chain retailers) now have the ideal solution for impactful, yet affordable accent lighting. Our Smart Halogen Downlight offers customers a choice of different shapes to suit different functions, and the professional finish lends the luminaire an air of contemporary sophistication. Thanks to its robust housing, the Smart Halogen Downlight is a long-lasting solution. Quality clips ensure ease of installation.

### Benefits

- Affordable yet highly effective accent-lighting solution
- Safe and durable
- Wide choice for customers; contemporary sophistication

### Features

- Robust housing
- Different shapes to suit different functions
- Professional finish
- Good-quality clips for easy installation

# Smart Halogen Downlight QBS020

## Application

- Retail – sales areas, shop windows
- Offices – exhibition and highlight areas
- Hospitality and cruise ships – corridors, service areas, reception areas, lobbies, lounges, restaurants, cabins
- Healthcare – corridors, reception areas, waiting areas
- Airports – arrival/departure halls, corridors, waiting areas, service desks, shops

## Specifications

<b>Type</b>	Die-cast aluminum versions and for MR11 lamp types: <ul style="list-style-type: none"><li>- QBS020, 022: fixed</li><li>- QBS021: adjustable</li></ul> Die-cast aluminum versions and for MR16 lamp types: <ul style="list-style-type: none"><li>- QBS023, 026, QBS040~046: fixed</li><li>- QBS024, 025, 027~029, QBS047: adjustable</li></ul> Cast aluminum versions and for MR16 lamp types: <ul style="list-style-type: none"><li>- QBS030, 032: fixed</li><li>- QBS031: cardanic</li></ul>
<b>Light source</b>	Halogen: <ul style="list-style-type: none"><li>- 1 x ESSENTIAL 1CT / GU4 / 20, 35 W</li><li>- 1 x ESSENTIAL Closed 1CT / GU5.3 / 20, 50 W</li></ul>
<b>Lamp beam angle</b>	30 , 36°
<b>Lamp included</b>	No

<b>Lamp position</b>	Vertical
<b>Light distribution</b>	Direct (D)
<b>Transformer</b>	12 V (not included)
<b>Material</b>	QBS020~029, QBS040~047 versions: <ul style="list-style-type: none"><li>- Die-cast aluminum</li></ul> QBS030~032 versions: <ul style="list-style-type: none"><li>- Cast aluminum</li></ul>
<b>Color</b>	QBS020~029, QBS040~047 versions: <ul style="list-style-type: none"><li>- White and grey</li></ul> QBS030~032 versions: <ul style="list-style-type: none"><li>- Silver</li></ul>
<b>Installation</b>	Fixation by means of spring fasteners
<b>Maintenance</b>	Direct lamp access
<b>Main applications</b>	Retail, fashion, hospitality

## Versions



GU5.3

