



# CoreLine Wall-mounted – the clear choice for LED

## CoreLine Wall-mounted

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Wall-mounted range of LED products can be used to replace traditional wall-mounted luminaires incorporating compact fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

### Benefits

- Up to 55% energy savings compared with luminaires with PL-C lamps
- Direct replacement for traditional wall-mounted luminaires
- Complete range covering all application requirements in one product (light levels, IP65, IK10, certified emergency lighting, built-in controls)

### Features

- Unobtrusive design
- Three lumen packages replacing traditional wall-mounted luminaires with 1x18 W / 2x18 W / 2x26 W PL-C
- Water- and vandal-proof as standard
- Phase-cut dimming as standard
- Frosted diffuser ensuring homogeneous light effect and visual comfort
- Optional emergency lighting
- Optional on/off movement detection or programmed 100%-10%-0% corridor dimming functionality

# CoreLine Wall-mounted

## Application

- Corridors
- Staircases
- Public entrance areas
- Bathrooms
- Emergency exits
- Parking garages
- Outdoor safety lighting

## Specifications

<b>Type</b>	WL120V (round version)
	WL121V (oval version)
<b>Light source</b>	Non-replaceable LED module
<b>Power (+/-10%)</b>	8 W (LED5S version)
	18 W (LED12S version)
	24 W (LED16S version)
<b>Beam angle</b>	120°
<b>Luminous flux</b>	500 lm (LED5S version)
	1200 lm (LED12S version)
	1600 lm (LED16S version)
<b>Correlated Color</b>	3000 or 4000 K
<b>Temperature</b>	
<b>Color Rendering Index</b>	≥ 80
<b>Median useful life</b>	50,000 hours
<b>L70B50</b>	
<b>Median useful life</b>	30,000 hours
<b>L80B50</b>	
<b>Median useful life</b>	15,000 hours
<b>L90B50</b>	
<b>Average ambient temperature</b>	+25 °C
<b>Operating temperature range</b>	
	-20 to +35 °C (wall-mounted position)
	-20 to +25 °C (ceiling-mounted position)
	0 to +25 °C (emergency lighting)

<b>Driver</b>	Built-in, replaceable
<b>Mains voltage</b>	220-240V / 50-60 Hz
<b>Dimming</b>	TE/LE dimming, compatible with most commercial available ELV dimmers
<b>Options</b>	Emergency lighting (integrated): 3 hours (EL3)
	Movement detection unit (integrated): on/off switch with day light override (MDU)
	DALI driver and movement detection unit (integrated): corridor functionality (PSD MDU)
<b>Material</b>	Housing: nylon 30% fiber glass re-inforced, UV resistant Difuser: high grade polycarbonate, UV resistant
<b>Color</b>	White (RAL 9010)
	Grey (RAL 7043)
<b>Optical cover</b>	Polycarbonate difuser
<b>Connection</b>	Push-in connector with pull relief (PIP)
<b>Maintenance</b>	LED module closed, no internal cleaning required
<b>Installation</b>	Screw mounting, directly onto surface
	4-point screw installation of housing to wall
	4-point torx screw connection difuser to housing Through-wiring not possible

## Versions




CoreLine Wall-Mounted Gen2

# CoreLine Wall-mounted

## Product details



CoreLine\_Wall-mounted-  
WL131V\_D35\_CTO\_PSD-DPP.TIF



CoreLine\_Wall-mounted-  
WL130V-2DPP.TIF



CoreLine\_Wall-mounted-  
WL131V\_D35\_CTO\_PSR\_MDU-  
DPP.TIF



CoreLine\_Wall-mounted-  
WL130V\_CTO-DPP.TIF



CoreLine\_Wall-mounted-  
WL130V-1DPP.TIF



CoreLine\_Wall-mounted-  
WL130V\_D35\_CTO\_MDU-DPP.TIF

# CoreLine Wall-mounted

## Approval and Application

Mech. impact protection code	IK08
Ingress protection code	IP65

## General Information

Beam angle of light source	120 °
CE mark	CE mark
Protection class IEC	Safety class II (II)
Optical cover/lens type	OP
Driver included	Yes
ENEC mark	ENEC mark
Light source replaceable	No
Number of gear units	1 unit
Optic type	Opal prismatic reflector

## Initial Performance (IEC Compliant)

Init. Colour rendering index	80
Luminous flux tolerance	+/-10%

## Mechanical and Housing

Colour	White
--------	-------

-

Order Code	Full Product Name	Driver failure rate at 5,000 hours
40268600	WL131V LED12S/830 PSED EL3 WH	1 %
40269300	WL131V LED12S/840 PSED EL3 WH	1 %
40270900	WL131V LED20S/830 PSED EL3 WH	1 %
40271600	WL131V LED20S/840 PSED EL3 WH	1 %
40272300	WL131V LED34S/830 PSED WH	1 %
40273000	WL131V LED34S/840 PSED WH	1 %
40274700	WL131V LED34S/830 PSED EL3 WH	1 %
40275400	WL131V LED34S/840 PSED EL3 WH	1 %
40282200	WL131V LED12S/830 PSR EL3 MDU WH	1 %
40283900	WL131V LED12S/840 PSR EL3 MDU WH	1 %
40284600	WL131V LED20S/830 PSR EL3 MDU WH	1 %
40285300	WL131V LED20S/840 PSR EL3 MDU WH	1 %
40286000	WL131V LED34S/830 PSR EL3 MDU WH	1 %
40287700	WL131V LED34S/840 PSR EL3 MDU WH	1 %
96095700	WL131V LED12S/840 PSU EL3 WH	-
96097100	WL131V LED20S/840 PSU EL3 WH	-
34000599	WL131V LED12S/830 PSU WH	-
34001299	WL131V LED12S/840 PSU WH	-
34002999	WL131V LED20S/830 PSU WH	-
34003699	WL131V LED20S/840 PSU WH	-
38784699	WL131V LED34S/830 PSU WH	0.7 %
38785399	WL131V LED34S/840 PSU WH	0.7 %
38786099	WL131V LED12S/830 PSR MDU WH	0.7 %
38787799	WL131V LED12S/840 PSR MDU WH	0.7 %
38788499	WL131V LED20S/830 PSR MDU WH	0.7 %
38789199	WL131V LED20S/840 PSR MDU WH	0.7 %
38790799	WL131V LED34S/830 PSR MDU WH	0.7 %
38791499	WL131V LED34S/840 PSR MDU WH	0.7 %
38792199	WL131V LED12S/830 PSED WH	0.7 %
38793899	WL131V LED12S/840 PSED WH	0.7 %
38794599	WL131V LED20S/830 PSED WH	0.7 %
38778599	WL130V LED12S/830 PSU WH	0.7 %
38779299	WL130V LED12S/840 PSU WH	0.7 %
38780899	WL130V LED20S/830 PSU WH	0.7 %
38781599	WL130V LED20S/840 PSU WH	0.7 %
38782299	WL130V LED20S/830 PSU MDU WH	0.7 %
38783999	WL130V LED20S/840 PSU MDU WH	0.7 %

## Application Conditions

Order Code	Full Product Name	Ambient temperature range	Maximum dimming level	Suitable for random switching	Order Code	Full Product Name	Ambient temperature range	Maximum dimming level	Suitable for random switching
40268600	WL131V LED12S/830 PSED EL3 WH	0 to +40 °C	10%	No	40271600	WL131V LED20S/840 PSED EL3 WH	0 to +40 °C	10%	No
40269300	WL131V LED12S/840 PSED EL3 WH	0 to +40 °C	10%	No	40272300	WL131V LED34S/830 PSED WH	-20 to +40 °C	10%	No
40270900	WL131V LED20S/830 PSED EL3 WH	0 to +40 °C	10%	No	40273000	WL131V LED34S/840 PSED WH	-20 to +40 °C	10%	No

## CoreLine Wall-mounted

Order Code	Full Product Name	Ambient temperature range	Maximum dimming level	Suitable for random switching
40274700	WL131V LED34S/830 PSED EL3 WH	0 to +40 °C	10%	No
40275400	WL131V LED34S/840 PSED EL3 WH	0 to +40 °C	10%	No
40282200	WL131V LED12S/830 PSR EL3 MDU WH	0 to +40 °C	20%	Yes
40283900	WL131V LED12S/840 PSR EL3 MDU WH	0 to +40 °C	20%	Yes
40284600	WL131V LED20S/830 PSR EL3 MDU WH	0 to +40 °C	20%	Yes
40285300	WL131V LED20S/840 PSR EL3 MDU WH	0 to +40 °C	20%	Yes
40286000	WL131V LED34S/830 PSR EL3 MDU WH	0 to +40 °C	20%	Yes
40287700	WL131V LED34S/840 PSR EL3 MDU WH	0 to +40 °C	20%	Yes
96095700	WL131V LED12S/840 PSU EL3 WH	0 to +40 °C	Not applicable	Yes
96097100	WL131V LED20S/840 PSU EL3 WH	0 to +40 °C	Not applicable	Yes
34000599	WL131V LED12S/830 PSU WH	-20 to +40 °C	Not applicable	Not applicable
34001299	WL131V LED12S/840 PSU WH	-20 to +40 °C	Not applicable	Not applicable
34002999	WL131V LED20S/830 PSU WH	-20 to +40 °C	Not applicable	Not applicable
34003699	WL131V LED20S/840 PSU WH	-20 to +40 °C	Not applicable	Not applicable
38784699	WL131V LED34S/830 PSU WH	-20 to +40 °C	Not applicable	Yes
38785399	WL131V LED34S/840 PSU WH	-20 to +40 °C	Not applicable	Yes

Order Code	Full Product Name	Ambient temperature range	Maximum dimming level	Suitable for random switching
38786099	WL131V LED12S/830 PSR MDU WH	-20 to +40 °C	10%	Yes
38787799	WL131V LED12S/840 PSR MDU WH	-20 to +40 °C	10%	Yes
38788499	WL131V LED20S/830 PSR MDU WH	-20 to +40 °C	10%	Yes
38789199	WL131V LED20S/840 PSR MDU WH	-20 to +40 °C	10%	Yes
38790799	WL131V LED34S/830 PSR MDU WH	-20 to +40 °C	10%	Yes
38791499	WL131V LED34S/840 PSR MDU WH	-20 to +40 °C	10%	Yes
38792199	WL131V LED12S/830 PSED WH	-20 to +40 °C	10%	Yes
38793899	WL131V LED12S/840 PSED WH	-20 to +40 °C	10%	Yes
38794599	WL131V LED20S/830 PSED WH	-20 to +40 °C	10%	Yes
38778599	WL130V LED12S/830 PSU WH	-20 to +40 °C	Not applicable	Yes
38779299	WL130V LED12S/840 PSU WH	-20 to +40 °C	Not applicable	Yes
38780899	WL130V LED20S/830 PSU WH	-20 to +40 °C	Not applicable	Yes
38781599	WL130V LED20S/840 PSU WH	-20 to +40 °C	Not applicable	Yes
38782299	WL130V LED20S/830 PSU MDU WH	-20 to +40 °C	Not applicable	Yes
38783999	WL130V LED20S/840 PSU MDU WH	-20 to +40 °C	Not applicable	Yes

### Controls and Dimming

Order Code	Full Product Name	Dimmable
40268600	WL131V LED12S/830 PSED EL3 WH	Yes
40269300	WL131V LED12S/840 PSED EL3 WH	Yes
40270900	WL131V LED20S/830 PSED EL3 WH	Yes
40271600	WL131V LED20S/840 PSED EL3 WH	Yes
40272300	WL131V LED34S/830 PSED WH	Yes
40273000	WL131V LED34S/840 PSED WH	Yes
40274700	WL131V LED34S/830 PSED EL3 WH	Yes
40275400	WL131V LED34S/840 PSED EL3 WH	Yes
40282200	WL131V LED12S/830 PSR EL3 MDU WH	Yes
40283900	WL131V LED12S/840 PSR EL3 MDU WH	Yes
40284600	WL131V LED20S/830 PSR EL3 MDU WH	Yes
40285300	WL131V LED20S/840 PSR EL3 MDU WH	Yes
40286000	WL131V LED34S/830 PSR EL3 MDU WH	Yes
40287700	WL131V LED34S/840 PSR EL3 MDU WH	Yes

Order Code	Full Product Name	Dimmable
96095700	WL131V LED12S/840 PSU EL3 WH	No
96097100	WL131V LED20S/840 PSU EL3 WH	No
34000599	WL131V LED12S/830 PSU WH	No
34001299	WL131V LED12S/840 PSU WH	No
34002999	WL131V LED20S/830 PSU WH	No
34003699	WL131V LED20S/840 PSU WH	No
38784699	WL131V LED34S/830 PSU WH	No
38785399	WL131V LED34S/840 PSU WH	No
38786099	WL131V LED12S/830 PSR MDU WH	Yes
38787799	WL131V LED12S/840 PSR MDU WH	Yes
38788499	WL131V LED20S/830 PSR MDU WH	Yes
38789199	WL131V LED20S/840 PSR MDU WH	Yes
38790799	WL131V LED34S/830 PSR MDU WH	Yes
38791499	WL131V LED34S/840 PSR MDU WH	Yes

## CoreLine Wall-mounted

Order Code	Full Product Name	Dimmable
38792199	WL131V LED12S/830 PSED WH	Yes
38793899	WL131V LED12S/840 PSED WH	Yes
38794599	WL131V LED20S/830 PSED WH	Yes
38778599	WL130V LED12S/830 PSU WH	No
38779299	WL130V LED12S/840 PSU WH	No

Order Code	Full Product Name	Dimmable
38780899	WL130V LED20S/830 PSU WH	No
38781599	WL130V LED20S/840 PSU WH	No
38782299	WL130V LED20S/830 PSU MDU WH	No
38783999	WL130V LED20S/840 PSU MDU WH	No

### Operating and Electrical

Order Code	Full Product Name	Input Voltage
40268600	WL131V LED12S/830 PSED EL3 WH	220-240 V
40269300	WL131V LED12S/840 PSED EL3 WH	220-240 V
40270900	WL131V LED20S/830 PSED EL3 WH	220-240 V
40271600	WL131V LED20S/840 PSED EL3 WH	220-240 V
40272300	WL131V LED34S/830 PSED WH	220-240 V
40273000	WL131V LED34S/840 PSED WH	220-240 V
40274700	WL131V LED34S/830 PSED EL3 WH	220-240 V
40275400	WL131V LED34S/840 PSED EL3 WH	220-240 V
40282200	WL131V LED12S/830 PSR EL3 MDU WH	220-240 V
40283900	WL131V LED12S/840 PSR EL3 MDU WH	220-240 V
40284600	WL131V LED20S/830 PSR EL3 MDU WH	220-240 V
40285300	WL131V LED20S/840 PSR EL3 MDU WH	220-240 V
40286000	WL131V LED34S/830 PSR EL3 MDU WH	220-240 V
40287700	WL131V LED34S/840 PSR EL3 MDU WH	220-240 V
96095700	WL131V LED12S/840 PSU EL3 WH	220/240 V
96097100	WL131V LED20S/840 PSU EL3 WH	220/240 V
34000599	WL131V LED12S/830 PSU WH	220/240 V
34001299	WL131V LED12S/840 PSU WH	220/240 V
34002999	WL131V LED20S/830 PSU WH	220/240 V

Order Code	Full Product Name	Input Voltage
34003699	WL131V LED20S/840 PSU WH	220/240 V
38784699	WL131V LED34S/830 PSU WH	220-240 V
38785399	WL131V LED34S/840 PSU WH	220-240 V
38786099	WL131V LED12S/830 PSR MDU WH	220-240 V
38787799	WL131V LED12S/840 PSR MDU WH	220-240 V
38788499	WL131V LED20S/830 PSR MDU WH	220-240 V
38789199	WL131V LED20S/840 PSR MDU WH	220-240 V
38790799	WL131V LED34S/830 PSR MDU WH	220-240 V
38791499	WL131V LED34S/840 PSR MDU WH	220-240 V
38792199	WL131V LED12S/830 PSED WH	220-240 V
38793899	WL131V LED12S/840 PSED WH	220-240 V
38794599	WL131V LED20S/830 PSED WH	220-240 V
38778599	WL130V LED12S/830 PSU WH	220-240 V
38779299	WL130V LED12S/840 PSU WH	220-240 V
38780899	WL130V LED20S/830 PSU WH	220-240 V
38781599	WL130V LED20S/840 PSU WH	220-240 V
38782299	WL130V LED20S/830 PSU MDU WH	220-240 V
38783999	WL130V LED20S/840 PSU MDU WH	220-240 V

### General Information (1/2)

Order Code	Full Product Name	Emergency lighting	Flammability mark	Gear	Glow-wire test
40268600	WL131V LED12S/830 PSED EL3 WH	EL3	NO	-	850/30
40269300	WL131V LED12S/840 PSED EL3 WH	EL3	NO	-	850/30
40270900	WL131V LED20S/830 PSED EL3 WH	EL3	NO	-	850/30
40271600	WL131V LED20S/840 PSED EL3 WH	EL3	NO	-	850/30
40272300	WL131V LED34S/830 PSED WH	No	NO	-	850/30
40273000	WL131V LED34S/840 PSED WH	No	NO	-	850/30
40274700	WL131V LED34S/830 PSED EL3 WH	EL3	NO	-	850/30
40275400	WL131V LED34S/840 PSED EL3 WH	EL3	NO	-	850/30
40282200	WL131V LED12S/830 PSR EL3 MDU WH	EL3	NO	-	850/30

Order Code	Full Product Name	Emergency lighting	Flammability mark	Gear	Glow-wire test
40283900	WL131V LED12S/840 PSR EL3 MDU WH	EL3	NO	-	850/30
40284600	WL131V LED20S/830 PSR EL3 MDU WH	EL3	NO	-	850/30
40285300	WL131V LED20S/840 PSR EL3 MDU WH	EL3	NO	-	850/30
40286000	WL131V LED34S/830 PSR EL3 MDU WH	EL3	NO	-	850/30
40287700	WL131V LED34S/840 PSR EL3 MDU WH	EL3	NO	-	850/30
96095700	WL131V LED12S/840 PSU EL3 WH	EL3	D	-	850/30
96097100	WL131V LED20S/840 PSU EL3 WH	EL3	D	-	850/30
34000599	WL131V LED12S/830 PSU WH	-	D	-	650/30
34001299	WL131V LED12S/840 PSU WH	-	D	-	650/30

## CoreLine Wall-mounted

Order Code	Full Product Name	Emergency lighting	Flammability mark	Gear	Glow-wire test
34002999	WL131V LED20S/830 PSU WH	-	D	-	650/30
34003699	WL131V LED20S/840 PSU WH	-	D	-	650/30
38784699	WL131V LED34S/830 PSU WH	-	NO	-	650/30
38785399	WL131V LED34S/840 PSU WH	-	NO	-	650/30
38786099	WL131V LED12S/830 PSR MDU WH	-	NO	-	650/30
38787799	WL131V LED12S/840 PSR MDU WH	-	NO	-	650/30
38788499	WL131V LED20S/830 PSR MDU WH	-	NO	-	650/30
38789199	WL131V LED20S/840 PSR MDU WH	-	NO	-	650/30
38790799	WL131V LED34S/830 PSR MDU WH	-	NO	-	650/30
38791499	WL131V LED34S/840 PSR MDU WH	-	NO	-	650/30

Order Code	Full Product Name	Emergency lighting	Flammability mark	Gear	Glow-wire test
38792199	WL131V LED12S/830 PSED WH	-	NO	-	650/30
38793899	WL131V LED12S/840 PSED WH	-	NO	-	650/30
38794599	WL131V LED20S/830 PSED WH	-	NO	-	650/30
38778599	WL130V LED12S/830 PSU WH	-	NO	-	650/30
38779299	WL130V LED12S/840 PSU WH	-	NO	-	650/30
38780899	WL130V LED20S/830 PSU WH	-	NO	-	650/30
38781599	WL130V LED20S/840 PSU WH	-	NO	-	650/30
38782299	WL130V LED20S/830 PSU MDU WH	-	NO	-	650/30
38783999	WL130V LED20S/840 PSU MDU WH	-	NO	-	650/30

### General Information (2/2)

Order Code	Full Product Name	Lamp family code	Embedded control	Product family code
40268600	WL131V LED12S/830 PSED EL3 WH	LED12	No	WL131V
40269300	WL131V LED12S/840 PSED EL3 WH	LED12	No	WL131V
40270900	WL131V LED20S/830 PSED EL3 WH	LED20	No	WL131V
40271600	WL131V LED20S/840 PSED EL3 WH	LED20	No	WL131V
40272300	WL131V LED34S/830 PSED WH	LED34S	No	WL131V
40273000	WL131V LED34S/840 PSED WH	LED34S	No	WL131V
40274700	WL131V LED34S/830 PSED EL3 WH	LED34S	No	WL131V
40275400	WL131V LED34S/840 PSED EL3 WH	LED34S	No	WL131V
40282200	WL131V LED12S/830 PSR EL3 MDU WH	LED12	MDU	WL131V
40283900	WL131V LED12S/840 PSR EL3 MDU WH	LED12	MDU	WL131V
40284600	WL131V LED20S/830 PSR EL3 MDU WH	LED20	MDU	WL131V
40285300	WL131V LED20S/840 PSR EL3 MDU WH	LED20	MDU	WL131V
40286000	WL131V LED34S/830 PSR EL3 MDU WH	LED34S	MDU	WL131V
40287700	WL131V LED34S/840 PSR EL3 MDU WH	LED34S	MDU	WL131V

Order Code	Full Product Name	Lamp family code	Embedded control	Product family code
96095700	WL131V LED12S/840 PSU EL3 WH	LED12	No	WL131V
96097100	WL131V LED20S/840 PSU EL3 WH	LED20	No	WL131V
34000599	WL131V LED12S/830 PSU WH	LED12	-	-
34001299	WL131V LED12S/840 PSU WH	LED12	-	-
34002999	WL131V LED20S/830 PSU WH	LED20	-	-
34003699	WL131V LED20S/840 PSU WH	LED20	-	-
38784699	WL131V LED34S/830 PSU WH	LED34S	-	-
38785399	WL131V LED34S/840 PSU WH	LED34S	-	-
38786099	WL131V LED12S/830 PSR MDU WH	LED12	MDU	-
38787799	WL131V LED12S/840 PSR MDU WH	LED12	MDU	-
38788499	WL131V LED20S/830 PSR MDU WH	LED20	MDU	-
38789199	WL131V LED20S/840 PSR MDU WH	LED20	MDU	-
38790799	WL131V LED34S/830 PSR MDU WH	LED34S	MDU	-
38791499	WL131V LED34S/840 PSR MDU WH	LED34S	MDU	-
38792199	WL131V LED12S/830 PSED WH	LED12	-	-
38793899	WL131V LED12S/840 PSED WH	LED12	-	-
38794599	WL131V LED20S/830 PSED WH	LED20	-	-
38778599	WL130V LED12S/830 PSU WH	LED12	-	-

## CoreLine Wall-mounted

Order Code	Full Product Name	Lamp family code	Embedded control	Product family code
38779299	WL130V LED12S/840 PSU WH	LED12	-	-
38780899	WL130V LED20S/830 PSU WH	LED20	-	-
38781599	WL130V LED20S/840 PSU WH	LED20	-	-
38782299	WL130V LED20S/830 PSU MDU WH	LED20	MDU	-

Order Code	Full Product Name	Lamp family code	Embedded control	Product family code
38783999	WL130V LED20S/840 PSU MDU WH	LED20	MDU	-

### Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
40268600	WL131V LED12S/830 PSED EL3 WH	(0.44, 0.41)	3000 K	100 lm/W	1200 lm
40269300	WL131V LED12S/840 PSED EL3 WH	(0.39, 0.39)	4000 K	100 lm/W	1200 lm
40270900	WL131V LED20S/830 PSED EL3 WH	(0.44, 0.41)	3000 K	91 lm/W	2000 lm
40271600	WL131V LED20S/840 PSED EL3 WH	(0.39, 0.39)	4000 K	91 lm/W	2000 lm
40272300	WL131V LED34S/830 PSED WH	(0.44, 0.41)	3000 K	94 lm/W	3400 lm
40273000	WL131V LED34S/840 PSED WH	(0.39, 0.39)	4000 K	94 lm/W	3400 lm
40274700	WL131V LED34S/830 PSED EL3 WH	(0.44, 0.41)	3000 K	94 lm/W	3400 lm
40275400	WL131V LED34S/840 PSED EL3 WH	(0.39, 0.39)	4000 K	94 lm/W	3400 lm
40282200	WL131V LED12S/830 PSR EL3 MDU WH	(0.44, 0.41)	3000 K	100 lm/W	1200 lm
40283900	WL131V LED12S/840 PSR EL3 MDU WH	(0.39, 0.39)	4000 K	100 lm/W	1200 lm
40284600	WL131V LED20S/830 PSR EL3 MDU WH	(0.44, 0.41)	3000 K	91 lm/W	2000 lm
40285300	WL131V LED20S/840 PSR EL3 MDU WH	(0.39, 0.39)	4000 K	91 lm/W	2000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
40286000	WL131V LED34S/830 PSR EL3 MDU WH	(0.44, 0.41)	3000 K	94 lm/W	3400 lm
40287700	WL131V LED34S/840 PSR EL3 MDU WH	(0.39, 0.39)	4000 K	94 lm/W	3400 lm
96095700	WL131V LED12S/840 PSU EL3 WH	(0.39, 0.39)	4000 K	80 lm/W	1200 lm
96097100	WL131V LED20S/840 PSU EL3 WH	(0.39, 0.39)	4000 K	80 lm/W	2000 lm
34000599	WL131V LED12S/830 PSU WH	(0.44, 0.41)	3000 K	100 lm/W	1200 lm
34001299	WL131V LED12S/840 PSU WH	(0.39, 0.39)	4000 K	100 lm/W	1200 lm
34002999	WL131V LED20S/830 PSU WH	(0.44, 0.41)	3000 K	90 lm/W	2000 lm
34003699	WL131V LED20S/840 PSU WH	(0.39, 0.39)	4000 K	90 lm/W	2000 lm
38784699	WL131V LED34S/830 PSU WH	(0.44, 0.41)	3000 K	95 lm/W	3400 lm
38785399	WL131V LED34S/840 PSU WH	(0.39, 0.39)	4000 K	95 lm/W	3400 lm
38786099	WL131V LED12S/830 PSR MDU WH	(0.44, 0.41)	3000 K	80 lm/W	1200 lm
38787799	WL131V LED12S/840 PSR MDU WH	(0.39, 0.39)	4000 K	80 lm/W	1200 lm



## CoreLine Wall-mounted

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
38788499	WL131V LED20S/830 PSR MDU WH	(0.44, 0.41) SDCM<3	3000 K	80 lm/W	2000 lm
38789199	WL131V LED20S/840 PSR MDU WH	(0.39, 0.39) SDCM<3	4000 K	80 lm/W	2000 lm
38790799	WL131V LED34S/830 PSR MDU WH	(0.44, 0.41) SDCM<3	3000 K	90 lm/W	3400 lm
38791499	WL131V LED34S/840 PSR MDU WH	(0.39, 0.39) SDCM<3	4000 K	90 lm/W	3400 lm
38792199	WL131V LED12S/830 PSED WH	(0.44, 0.41) SDCM<3	3000 K	90 lm/W	1200 lm
38793899	WL131V LED12S/840 PSED WH	(0.39, 0.39) SDCM<3	4000 K	90 lm/W	1200 lm
38794599	WL131V LED20S/830 PSED WH	(0.44, 0.41) SDCM<3	3000 K	90 lm/W	2000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
38778599	WL130V LED12S/830 PSU WH	(0.44, 0.41) SDCM<3	3000 K	100 lm/W	1200 lm
38779299	WL130V LED12S/840 PSU WH	(0.39, 0.39) SDCM<3	4000 K	100 lm/W	1200 lm
38780899	WL130V LED20S/830 PSU WH	(0.44, 0.41) SDCM<3	3000 K	90 lm/W	2000 lm
38781599	WL130V LED20S/840 PSU WH	(0.44, 0.41) SDCM<3	4000 K	90 lm/W	2000 lm
38782299	WL130V LED20S/830 PSU MDU WH	(0.44, 0.41) SDCM<3	3000 K	80 lm/W	2000 lm
38783999	WL130V LED20S/840 PSU MDU WH	(0.39, 0.39) SDCM<3	4000 K	80 lm/W	2000 lm

### Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
40268600	WL131V LED12S/830 PSED EL3 WH	12 W
40269300	WL131V LED12S/840 PSED EL3 WH	12 W
40270900	WL131V LED20S/830 PSED EL3 WH	22 W
40271600	WL131V LED20S/840 PSED EL3 WH	22 W
40272300	WL131V LED34S/830 PSED WH	36 W
40273000	WL131V LED34S/840 PSED WH	36 W
40274700	WL131V LED34S/830 PSED EL3 WH	36 W
40275400	WL131V LED34S/840 PSED EL3 WH	36 W
40282200	WL131V LED12S/830 PSR EL3 MDU WH	12 W
40283900	WL131V LED12S/840 PSR EL3 MDU WH	12 W
40284600	WL131V LED20S/830 PSR EL3 MDU WH	22 W
40285300	WL131V LED20S/840 PSR EL3 MDU WH	22 W
40286000	WL131V LED34S/830 PSR EL3 MDU WH	36 W
40287700	WL131V LED34S/840 PSR EL3 MDU WH	36 W
96095700	WL131V LED12S/840 PSU EL3 WH	15 W
96097100	WL131V LED20S/840 PSU EL3 WH	25 W
34000599	WL131V LED12S/830 PSU WH	12 W
34001299	WL131V LED12S/840 PSU WH	12 W
34002999	WL131V LED20S/830 PSU WH	22 W

Order Code	Full Product Name	Initial input power
34003699	WL131V LED20S/840 PSU WH	22 W
38784699	WL131V LED34S/830 PSU WH	36 W
38785399	WL131V LED34S/840 PSU WH	36 W
38786099	WL131V LED12S/830 PSR MDU WH	15 W
38787799	WL131V LED12S/840 PSR MDU WH	15 W
38788499	WL131V LED20S/830 PSR MDU WH	25 W
38789199	WL131V LED20S/840 PSR MDU WH	25 W
38790799	WL131V LED34S/830 PSR MDU WH	38 W
38791499	WL131V LED34S/840 PSR MDU WH	38 W
38792199	WL131V LED12S/830 PSED WH	13 W
38793899	WL131V LED12S/840 PSED WH	13 W
38794599	WL131V LED20S/830 PSED WH	23 W
38778599	WL130V LED12S/830 PSU WH	12 W
38779299	WL130V LED12S/840 PSU WH	12 W
38780899	WL130V LED20S/830 PSU WH	22 W
38781599	WL130V LED20S/840 PSU WH	22 W
38782299	WL130V LED20S/830 PSU MDU WH	23 W
38783999	WL130V LED20S/840 PSU MDU WH	23 W

## CoreLine Wall-mounted

