



MSR Gold™ MiniFastFit – lamp replacement in seconds

MSR Gold™ MiniFastFit (Touring/Stage)

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Benefits

- Lamp replacement in just seconds
- Easy handling, smaller and lighter fixtures
- Reduces early lamp or lamp holder failures. Excellent current transfer
- High perceived brightness
- High beam intensity

Features

- Philips MiniFastFit
- Compact design
- Innovative gold plated pins
- High color temperature
- Very short arc

MSR Gold™ MiniFastFit (Touring/Stage)


Application

- Events
- Shows
- Touring/Stage

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold 400 MiniFastFit 1CT/16	23.2	3.0	55 mm	57 mm	56	111 mm	36.5	36	35.3
MSR Gold 700/2 MiniFastFit 1CT/4	23.2	3.8	55 mm	57 mm	56	112 mm	36.5	36	35.3

General Information

Cap-Base	PGJX28
Operating Position	UNIVERSAL

Controls and Dimming

Dimmable	Yes
----------	-----

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux (Min)	Luminous Flux
15828800	MSR Gold™ 400 MiniFastFit 1CT/16	6700 K	60	-	-	28,000 lumen
22117300	MSR Gold™ 700/2 MiniFastFit 1CT/4	7200 K	75	2	44,000 lumen	47,000 lumen

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption	Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
15828800	MSR Gold™ 400 MiniFastFit 1CT/16	7.2 A	400 W	22117300	MSR Gold™ 700/2 MiniFastFit 1CT/4	10.2 A	700 W

MSR Gold™ MiniFastFit (Touring/Stage)

