



Energy-efficient lighting for industrial and commercial applications

GreenUp Wellglass

GreenUp LED Welglass luminaire is designed to replace traditional WelGlass up to 70W with only 35% of the load for similar illumination. It is a perfect LED solution for outdoor application and industry of harsh condition like power plant, metal, and non hazardous area in chemical and petrochemical industry. Compared to conventional HID WelGlass, it improves reliability, comfort, while reducing energy and maintenance cost dramatically. GreenUp Welglass comes with 2 different mounting, pipe and bracket, and comes with 2 beam, lambertian and batwing.

Benefits

- Safe and reliable qualities
- High energy saving
- Comfortable light


Features

- Waterproof, dustproof, impact proof and corrosion proof features, meeting requirements of outdoor application
- System efficacy 100lm/W, 1:1 replacement of HID up to 68% energy saving
- CRI>80, comfortable light with low glare ratings
- 50,000 hrs life with 70% lumen maintained
- Two mounting options: pipe mounting and bracket for wall/ceiling mounting

Application

- Harsh Industry Application

Versions



Accessories

Ordercode 01579111



Approval and Application

Mech. impact protection code	IK08
Ingress protection code	IP65

Controls and Dimming

Dimmable	No
----------	----

Operating and Electrical

Input Voltage	220-240 V
---------------	-----------

General Information

CE mark	-
Protection class IEC	Safety class I (I)
Optical cover/lens type	PCF
Driver included	Yes
Light source replaceable	No

Initial Performance (IEC Compliant)

Init. Colour rendering index	>80
Initial LED luminaire efficacy	110 lm/W
Luminous flux tolerance	+/-10%

Mechanical and Housing

Colour	Dark gray
--------	-----------

Application Conditions

Order Code	Full Product Name	Ambient temperature range
01512261	BY200P LED44 L-B/CW PSU	-30 to +45 °C
01512361	BY200P LED44 L-B/NW PSU	-30 to +45 °C
01512461	BY200P LED32 L-B/CW PSU	-30 to +50 °C
01512561	BY200P LED32 L-B/NW PSU	-30 to +50 °C

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux	Initial input power
01512261	BY200P LED44 L-B/CW PSU	6500 K	4400 lm	40 W
01512361	BY200P LED44 L-B/NW PSU	4000 K	4400 lm	40 W

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux	Initial input power
01512461	BY200P LED32 L-B/CW PSU	6500 K	3200 lm	29 W
01512561	BY200P LED32 L-B/NW PSU	4000 K	3200 lm	29 W

