

Standard electromagnetic ballast for fluorescent applications

BTA EM ballasts for TL Fluorescent lamps

This efficient, reliable, long-life electromagnetic ballast for TL-D fluorescent lamps features a balanced combination of essential characteristics, thus allowing a wide variety of standard applications.

Benefits

- Reliable electrical and mechanical performance
- Compact dimensions
- Electrical design for optimum lamp performance

Features


- Long lifetime
- Quick and easy wiring
- Easy to recognize: blue product label
- Tw marking 130 °C (means average lifetime of 10 years' continuous operation @ 130 °C)
- High-quality screw-in or insert contact

Application

- Retail
- Offices
- Industry
- Home

BTA EM ballasts for TL Fluorescent lamps

Dimensional drawing



Product	D1	C1	C3	A1	A2	A3	A4	B1	B2
BTA 36W	4.0	28.0	1.2	155.0	140.0	48.0	50.0	39.0	20.0
220V C SC	mm	mm	mm	mm	mm	mm	mm	mm	mm

