



RoadFlair – Sleek and superior beyond anticipation

RoadFlair

Designed for major and city roads, Philips RoadFlair is a new and exciting product set to brighten your streets beyond imagination. Smartly-designed to bring cities the highest savings possible with best-in-class lumen per watt, this road lighting production comes at a competitive price bound to excite. Philips RoadFlair brings energy efficiency, improves a city's sustainability drive and delivers significant cost reduction in urban environments. The right road luminaire coupled with the right lighting application will create the best environment for your municipality, benefiting local communities and boosting tourism and businesses.

Benefits

- High lumen efficacy 120 to 140 lumen per watt – much higher than currently available solutions
- Unique functional design Sleek, light-weight and well-designed luminaire
- Control and dimming ready Supports CityTouch connect application, 7-Pin Nema socket and standard outdoor dimming protocols
- Value for money Most competitive product in its segment. Perfect for renovation, upgrading projects
- Best-in-class LED lighting technology at an unmatched, competitive price
- Equipped with a service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information

Features

- Excellent thermal management operating temperature -40 to 50 °C
- Exposed Optic – Transparent and weather-resistant grade polycarbonate optics
- Multiple optic – Options to meet all road and street lighting application requirements
- Lightweight housing design
- Available in 3000K, 4000K, 5000K and 5700K CCT options
- 10 kV or 15 kV surge-protection device

Application

- Pedestrian Road
- Highway Road
- Residential Road
- Interchange

Versions



BRP394 LED 220-240V DM



BRP392/393 LED 220-240V DM



BRP391 LED 220-240V DM


Product details



RoadFlair BRP392 BRP393 Back



RoadFlair BRP394 Back



RoadFlair BRP391 Back

Approval and Application

Mech. impact protection code	IK08
------------------------------	------

General Information

CE mark	CE mark
Driver included	Yes
Flammability mark	F
Light source replaceable	No

Initial Performance (IEC Compliant)

Init. Colour Rendering Index	>70
------------------------------	-----

Light Technical

Standard tilt angle posttop	-
-----------------------------	---

Mechanical and Housing

Colour	Gray
--------	------

Application Conditions

Order Code	Full Product Name	Maximum dim level
01814798	BRP394 LED348/NW 290W 220-240V DM	Not applicable
01814898	BRP394 LED300/NW 250W 220-240V DM	Not applicable
01814998	BRP394 LED312/NW 260W 220-240V DM	Not applicable
01815098	BRP394 LED288/NW 240W 220-240V DM	Not applicable
01815198	BRP394 LED276/NW 230W 220-240V DM	Not applicable
01815298	BRP394 LED252/NW 210W 220-240V DM	Not applicable
01815398	BRP394 LED240/NW 200W 220-240V DM	Not applicable
01815498	BRP394 LED228/NW 190W 220-240V DM	Not applicable
01816898	BRP394 LED204/NW 170W 220-240V DM	Not applicable
01816998	BRP394 LED216/NW 180W 220-240V DM	Not applicable
01817098	BRP394 LED264/NW 220W 220-240V DM	Not applicable
01817198	BRP394 LED324/NW 270W 220-240V DM	Not applicable
01817298	BRP394 LED336/NW 280W 220-240V DM	Not applicable
01817398	BRP394 LED360/NW 300W 220-240V DM	Not applicable
01817498	BRP394 LED372/NW 310W 220-240V DM	Not applicable
01817598	BRP394 LED384/NW 320W 220-240V DM	Not applicable
01864198	BRP394 LED449/NW 316W 220-240V DM PSR	10%
01864298	BRP394 LED437/NW 308W 220-240V DM PSR	10%
01864398	BRP394 LED424/NW 300W 220-240V DM PSR	10%
01864498	BRP394 LED412/NW 285W 220-240V DM PSR	10%
01864598	BRP394 LED398/NW 276W 220-240V DM PSR	10%
01864698	BRP394 LED385/NW 268W 220-240V DM PSR	10%
01864798	BRP394 LED373/NW 259W 220-240V DM PSR	10%
01864898	BRP394 LED360/NW 251W 220-240V DM PSR	10%
01864998	BRP394 LED348/NW 242W 220-240V DM PSR	10%
01865098	BRP394 LED336/NW 234W 220-240V DM PSR	10%
01867998	BRP394 LED421/WW 316W 220-240V DM PSR	10%
01868098	BRP394 LED410/WW 308W 220-240V DM PSR	10%
01868198	BRP394 LED400/WW 300W 220-240V DM PSR	10%
01868298	BRP394 LED386/WW 285W 220-240V DM PSR	10%
01868398	BRP394 LED373/WW 276W 220-240V DM PSR	10%
01868498	BRP394 LED361/WW 268W 220-240V DM PSR	10%
01868598	BRP394 LED350/WW 259W 220-240V DM PSR	10%
01868698	BRP394 LED338/WW 251W 220-240V DM PSR	10%
01868798	BRP394 LED326/WW 242W 220-240V DM PSR	10%
01868898	BRP394 LED315/WW 234W 220-240V DM PSR	10%
01815598	BRP392 LED156/NW 130W 220-240V DM	Not applicable
01815698	BRP392 LED120/NW 100W 220-240V DM	Not applicable
01816298	BRP392 LED108/NW 90W 220-240V DM	Not applicable
01816398	BRP392 LED132/NW 110W 220-240V DM	Not applicable
01816498	BRP392 LED144/NW 120W 220-240V DM	Not applicable
01816598	BRP392 LED168/NW 140W 220-240V DM	Not applicable
01816698	BRP392 LED180/NW 150W 220-240V DM	Not applicable
01816798	BRP392 LED192/NW 160W 220-240V DM	Not applicable
01862498	BRP392 LED224/NW 158W 220-240V DM PSR	10%
01862598	BRP392 LED212/NW 150W 220-240V DM PSR	10%
01862698	BRP392 LED200/NW 138W 220-240V DM PSR	10%
01862798	BRP392 LED186/NW 130W 220-240V DM PSR	10%
01862898	BRP392 LED174/NW 121W 220-240V DM PSR	10%
01862998	BRP392 LED161/NW 113W 220-240V DM PSR	10%
01863098	BRP392 LED150/NW 104W 220-240V DM PSR	10%

Order Code	Full Product Name	Maximum dim level
01863198	BRP392 LED136/NW 96W 220-240V DM PSR	10%
01863298	BRP392 LED124/NW 88W 220-240V DM PSR	10%
01863398	BRP393 LED323/NW 225W 220-240V DM PSR	10%
01863498	BRP393 LED311/NW 217W 220-240V DM PSR	10%
01863598	BRP393 LED298/NW 208W 220-240V DM PSR	10%
01863698	BRP393 LED286/NW 200W 220-240V DM PSR	10%
01863798	BRP393 LED273/NW 192W 220-240V DM PSR	10%
01863898	BRP393 LED261/NW 183W 220-240V DM PSR	10%
01863998	BRP393 LED248/NW 174W 220-240V DM PSR	10%
01864098	BRP393 LED236/NW 166W 220-240V DM PSR	10%
01866298	BRP392 LED210/WW 158W 220-240V DM PSR	10%
01866398	BRP392 LED200/WW 150W 220-240V DM PSR	10%
01866498	BRP392 LED186/WW 138W 220-240V DM PSR	10%
01866598	BRP392 LED175/WW 130W 220-240V DM PSR	10%
01866698	BRP392 LED163/WW 121W 220-240V DM PSR	10%
01866798	BRP392 LED151/WW 113W 220-240V DM PSR	10%
01866898	BRP392 LED140/WW 104W 220-240V DM PSR	10%
01866998	BRP392 LED128/WW 96W 220-240V DM PSR	10%
01867098	BRP392 LED116/WW 88W 220-240V DM PSR	10%
01867198	BRP393 LED303/WW 225W 220-240V DM PSR	10%
01867298	BRP393 LED291/WW 217W 220-240V DM PSR	10%
01867398	BRP393 LED280/WW 208W 220-240V DM PSR	10%
01867498	BRP393 LED268/WW 200W 220-240V DM PSR	10%
01867598	BRP393 LED256/WW 192W 220-240V DM PSR	10%
01867698	BRP393 LED245/WW 183W 220-240V DM PSR	10%
01867798	BRP393 LED233/WW 174W 220-240V DM PSR	10%
01867898	BRP393 LED221/WW 166W 220-240V DM PSR	10%
01815798	BRP391 LED96/NW 80W 220-240V DM	Not applicable
01815898	BRP391 LED48/NW 40W 220-240V DM	Not applicable
01815998	BRP391 LED60/NW 50W 220-240V DM	Not applicable
01816098	BRP391 LED72/NW 60W 220-240V DM	Not applicable
32822500	BRP391 LED84/NW 70W 220-240V DM	Not applicable
01861398	BRP390 LED81/NW 57W 220-240V DM	-
01861498	BRP390 LED74/NW 52W 220-240V DM	-
01861598	BRP390 LED68/NW 48W 220-240V DM	-
01861698	BRP390 LED62/NW 46W 220-240V DM	-
01861798	BRP390 LED56/NW 41W 220-240V DM	-
01861898	BRP390 LED50/NW 36W 220-240V DM	-
01861998	BRP391 LED112/NW 80W 220-240V DM PSR	10%
01862098	BRP391 LED105/NW 75W 220-240V DM PSR	10%
01862198	BRP391 LED100/NW 70W 220-240V DM PSR	10%
01862298	BRP391 LED93/NW 67W 220-240V DM PSR	10%
01862398	BRP391 LED87/NW 63W 220-240V DM PSR	10%
01865198	BRP390 LED76/WW 57W 220-240V DM	-
01865298	BRP390 LED70/WW 52W 220-240V DM	-
01865398	BRP390 LED64/WW 48W 220-240V DM	-
01865498	BRP390 LED58/WW 46W 220-240V DM	-
01865598	BRP390 LED52/WW 41W 220-240V DM	-
01865698	BRP390 LED46/WW 36W 220-240V DM	-
01865798	BRP391 LED105/WW 80W 220-240V DM PSR	10%
01865898	BRP391 LED100/WW 75W 220-240V DM PSR	10%
01865998	BRP391 LED93/WW 70W 220-240V DM PSR	10%

Order Code	Full Product Name	Maximum dim level
01866098	BRP391 LED87/WW 67W 220-240V DM PSR	10%
01866198	BRP391 LED81/WW 63W 220-240V DM PSR	10%

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
01814798	BRP394 LED348/NW 290W 220-240V DM	No	01862698	BRP392 LED200/NW 138W 220-240V DM PSR	Yes
01814898	BRP394 LED300/NW 250W 220-240V DM	No	01862798	BRP392 LED186/NW 130W 220-240V DM PSR	Yes
01814998	BRP394 LED312/NW 260W 220-240V DM	No	01862898	BRP392 LED174/NW 121W 220-240V DM PSR	Yes
01815098	BRP394 LED288/NW 240W 220-240V DM	No	01862998	BRP392 LED161/NW 113W 220-240V DM PSR	Yes
01815198	BRP394 LED276/NW 230W 220-240V DM	No	01863098	BRP392 LED150/NW 104W 220-240V DM PSR	Yes
01815298	BRP394 LED252/NW 210W 220-240V DM	No	01863198	BRP392 LED136/NW 96W 220-240V DM PSR	Yes
01815398	BRP394 LED240/NW 200W 220-240V DM	No	01863298	BRP392 LED124/NW 88W 220-240V DM PSR	Yes
01815498	BRP394 LED228/NW 190W 220-240V DM	No	01863398	BRP393 LED323/NW 225W 220-240V DM PSR	Yes
01816898	BRP394 LED204/NW 170W 220-240V DM	No	01863498	BRP393 LED311/NW 217W 220-240V DM PSR	Yes
01816998	BRP394 LED216/NW 180W 220-240V DM	No	01863598	BRP393 LED298/NW 208W 220-240V DM PSR	Yes
01817098	BRP394 LED264/NW 220W 220-240V DM	No	01863698	BRP393 LED286/NW 200W 220-240V DM PSR	Yes
01817198	BRP394 LED324/NW 270W 220-240V DM	No	01863798	BRP393 LED273/NW 192W 220-240V DM PSR	Yes
01817298	BRP394 LED336/NW 280W 220-240V DM	No	01863898	BRP393 LED261/NW 183W 220-240V DM PSR	Yes
01817398	BRP394 LED360/NW 300W 220-240V DM	No	01863998	BRP393 LED248/NW 174W 220-240V DM PSR	Yes
01817498	BRP394 LED372/NW 310W 220-240V DM	No	01864098	BRP393 LED236/NW 166W 220-240V DM PSR	Yes
01817598	BRP394 LED384/NW 320W 220-240V DM	No	01866298	BRP392 LED210/WW 158W 220-240V DM PSR	Yes
01864198	BRP394 LED449/NW 316W 220-240V DM PSR	Yes	01866398	BRP392 LED200/WW 150W 220-240V DM PSR	Yes
01864298	BRP394 LED437/NW 308W 220-240V DM PSR	Yes	01866498	BRP392 LED186/WW 138W 220-240V DM PSR	Yes
01864398	BRP394 LED424/NW 300W 220-240V DM PSR	Yes	01866598	BRP392 LED175/WW 130W 220-240V DM PSR	Yes
01864498	BRP394 LED412/NW 285W 220-240V DM PSR	Yes	01866698	BRP392 LED163/WW 121W 220-240V DM PSR	Yes
01864598	BRP394 LED398/NW 276W 220-240V DM PSR	Yes	01866798	BRP392 LED151/WW 113W 220-240V DM PSR	Yes
01864698	BRP394 LED385/NW 268W 220-240V DM PSR	Yes	01866898	BRP392 LED140/WW 104W 220-240V DM PSR	Yes
01864798	BRP394 LED373/NW 259W 220-240V DM PSR	Yes	01866998	BRP392 LED128/WW 96W 220-240V DM PSR	Yes
01864898	BRP394 LED360/NW 251W 220-240V DM PSR	Yes	01867098	BRP392 LED116/WW 88W 220-240V DM PSR	Yes
01864998	BRP394 LED348/NW 242W 220-240V DM PSR	Yes	01867198	BRP393 LED303/WW 225W 220-240V DM PSR	Yes
01865098	BRP394 LED336/NW 234W 220-240V DM PSR	Yes	01867298	BRP393 LED291/WW 217W 220-240V DM PSR	Yes
01867998	BRP394 LED421/WW 316W 220-240V DM PSR	Yes	01867398	BRP393 LED280/WW 208W 220-240V DM PSR	Yes
01868098	BRP394 LED410/WW 308W 220-240V DM PSR	Yes	01867498	BRP393 LED268/WW 200W 220-240V DM PSR	Yes
01868198	BRP394 LED400/WW 300W 220-240V DM PSR	Yes	01867598	BRP393 LED256/WW 192W 220-240V DM PSR	Yes
01868298	BRP394 LED386/WW 285W 220-240V DM PSR	Yes	01867698	BRP393 LED245/WW 183W 220-240V DM PSR	Yes
01868398	BRP394 LED373/WW 276W 220-240V DM PSR	Yes	01867798	BRP393 LED233/WW 174W 220-240V DM PSR	Yes
01868498	BRP394 LED361/WW 268W 220-240V DM PSR	Yes	01867898	BRP393 LED221/WW 166W 220-240V DM PSR	Yes
01868598	BRP394 LED350/WW 259W 220-240V DM PSR	Yes	01815798	BRP391 LED96/NW 80W 220-240V DM	No
01868698	BRP394 LED338/WW 251W 220-240V DM PSR	Yes	01815898	BRP391 LED48/NW 40W 220-240V DM	No
01868798	BRP394 LED326/WW 242W 220-240V DM PSR	Yes	01815998	BRP391 LED60/NW 50W 220-240V DM	No
01868898	BRP394 LED315/WW 234W 220-240V DM PSR	Yes	01816098	BRP391 LED72/NW 60W 220-240V DM	No
01815598	BRP392 LED156/NW 130W 220-240V DM	No	32822500	BRP391 LED84/NW 70W 220-240V DM	No
01815698	BRP392 LED120/NW 100W 220-240V DM	No	01861398	BRP390 LED81/NW 57W 220-240V DM	No
01816298	BRP392 LED108/NW 90W 220-240V DM	No	01861498	BRP390 LED74/NW 52W 220-240V DM	No
01816398	BRP392 LED132/NW 110W 220-240V DM	No	01861598	BRP390 LED68/NW 48W 220-240V DM	No
01816498	BRP392 LED144/NW 120W 220-240V DM	No	01861698	BRP390 LED62/NW 46W 220-240V DM	No
01816598	BRP392 LED168/NW 140W 220-240V DM	No	01861798	BRP390 LED56/NW 41W 220-240V DM	No
01816698	BRP392 LED180/NW 150W 220-240V DM	No	01861898	BRP390 LED50/NW 36W 220-240V DM	No
01816798	BRP392 LED192/NW 160W 220-240V DM	No	01861998	BRP391 LED112/NW 80W 220-240V DM PSR	Yes
01862498	BRP392 LED224/NW 158W 220-240V DM PSR	Yes	01862098	BRP391 LED105/NW 75W 220-240V DM PSR	Yes
01862598	BRP392 LED212/NW 150W 220-240V DM PSR	Yes	01862198	BRP391 LED100/NW 70W 220-240V DM PSR	Yes

Order Code	Full Product Name	Dimmable
01862298	BRP391 LED93/NW 67W 220-240V DM PSR	Yes
01862398	BRP391 LED87/NW 63W 220-240V DM PSR	Yes
01865198	BRP390 LED76/WW 57W 220-240V DM	No
01865298	BRP390 LED70/WW 52W 220-240V DM	No
01865398	BRP390 LED64/WW 48W 220-240V DM	No
01865498	BRP390 LED58/WW 46W 220-240V DM	No
01865598	BRP390 LED52/WW 41W 220-240V DM	No

Order Code	Full Product Name	Dimmable
01865698	BRP390 LED46/WW 36W 220-240V DM	No
01865798	BRP391 LED105/WW 80W 220-240V DM PSR	Yes
01865898	BRP391 LED100/WW 75W 220-240V DM PSR	Yes
01865998	BRP391 LED93/WW 70W 220-240V DM PSR	Yes
01866098	BRP391 LED87/WW 67W 220-240V DM PSR	Yes
01866198	BRP391 LED81/WW 63W 220-240V DM PSR	Yes

General Information (1/2)

Order Code	Full Product Name	Light source colour	Optical cover/lens type	Lamp family code	Number of gear units
01814798	BRP394 LED348/NW 290W 220-240V DM	740 neutral white	No	-	2 units
01814898	BRP394 LED300/NW 250W 220-240V DM	740 neutral white	No	-	2 units
01814998	BRP394 LED312/NW 260W 220-240V DM	740 neutral white	No	-	2 units
01815098	BRP394 LED288/NW 240W 220-240V DM	740 neutral white	No	-	2 units
01815198	BRP394 LED276/NW 230W 220-240V DM	740 neutral white	No	-	2 units
01815298	BRP394 LED252/NW 210W 220-240V DM	740 neutral white	No	-	2 units
01815398	BRP394 LED240/NW 200W 220-240V DM	740 neutral white	No	-	2 units
01815498	BRP394 LED228/NW 190W 220-240V DM	740 neutral white	No	-	2 units
01816898	BRP394 LED204/NW 170W 220-240V DM	740 neutral white	No	-	2 units
01816998	BRP394 LED216/NW 180W 220-240V DM	740 neutral white	No	-	2 units
01817098	BRP394 LED264/NW 220W 220-240V DM	740 neutral white	No	-	2 units
01817198	BRP394 LED324/NW 270W 220-240V DM	740 neutral white	No	-	2 units
01817298	BRP394 LED336/NW 280W 220-240V DM	740 neutral white	No	-	2 units
01817398	BRP394 LED360/NW 300W 220-240V DM	740 neutral white	No	-	2 units
01817498	BRP394 LED372/NW 310W 220-240V DM	740 neutral white	No	-	2 units
01817598	BRP394 LED384/NW 320W 220-240V DM	740 neutral white	No	-	2 units
01864198	BRP394 LED449/NW 316W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01864298	BRP394 LED437/NW 308W 220-240V DM PSR	740 neutral white	PC-MLO	-	-

Order Code	Full Product Name	Light source colour	Optical cover/lens type	Lamp family code	Number of gear units
01864398	BRP394 LED424/NW 300W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01864498	BRP394 LED412/NW 285W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01864598	BRP394 LED398/NW 276W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01864698	BRP394 LED385/NW 268W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01864798	BRP394 LED373/NW 259W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01864898	BRP394 LED360/NW 251W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01864998	BRP394 LED348/NW 242W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01865098	BRP394 LED336/NW 234W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01867998	BRP394 LED421/WW 316W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01868098	BRP394 LED410/WW 308W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01868198	BRP394 LED400/WW 300W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01868298	BRP394 LED386/WW 285W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01868398	BRP394 LED373/WW 276W 220-240V DM PSR	730 warm white	PC-MLO	-	-

Order Code	Full Product Name	Light source colour	Optical cover/lens type	Lamp family code	Number of gear units
01868498	BRP394 LED361/WW 268W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01868598	BRP394 LED350/WW 259W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01868698	BRP394 LED338/WW 251W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01868798	BRP394 LED326/WW 242W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01868898	BRP394 LED315/WW 234W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01815598	BRP392 LED156/NW 130W 220-240V DM	740 neutral white	No	-	1 unit
01815698	BRP392 LED120/NW 100W 220-240V DM	740 neutral white	No	-	1 unit
01816298	BRP392 LED108/NW 90W 220-240V DM	740 neutral white	No	-	1 unit
01816398	BRP392 LED132/NW 110W 220-240V DM	740 neutral white	No	-	1 unit
01816498	BRP392 LED144/NW 120W 220-240V DM	740 neutral white	No	-	1 unit
01816598	BRP392 LED168/NW 140W 220-240V DM	740 neutral white	No	-	1 unit
01816698	BRP392 LED180/NW 150W 220-240V DM	740 neutral white	No	-	1 unit
01816798	BRP392 LED192/NW 160W 220-240V DM	740 neutral white	No	-	1 unit
01862498	BRP392 LED224/NW 158W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01862598	BRP392 LED212/NW 150W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01862698	BRP392 LED200/NW 138W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01862798	BRP392 LED186/NW 130W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01862898	BRP392 LED174/NW 121W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01862998	BRP392 LED161/NW 113W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01863098	BRP392 LED150/NW 104W 220-240V DM PSR	740 neutral white	PC-MLO	-	-

Order Code	Full Product Name	Light source colour	Optical cover/lens type	Lamp family code	Number of gear units
01863198	BRP392 LED136/NW 96W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01863298	BRP392 LED124/NW 88W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01863398	BRP393 LED323/NW 225W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01863498	BRP393 LED311/NW 217W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01863598	BRP393 LED298/NW 208W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01863698	BRP393 LED286/NW 200W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01863798	BRP393 LED273/NW 192W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01863898	BRP393 LED261/NW 183W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01863998	BRP393 LED248/NW 174W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01864098	BRP393 LED236/NW 166W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01866298	BRP392 LED210/WW 158W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01866398	BRP392 LED200/WW 150W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01866498	BRP392 LED186/WW 138W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01866598	BRP392 LED175/WW 130W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01866698	BRP392 LED163/WW 121W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01866798	BRP392 LED151/WW 113W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01866898	BRP392 LED140/WW 104W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01866998	BRP392 LED128/WW 96W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01867098	BRP392 LED116/WW 88W 220-240V DM PSR	730 warm white	PC-MLO	-	-

Order Code	Full Product Name	Light source colour	Optical cover/lens type	Lamp family code	Number of gear units
01867198	BRP393 LED303/WW 225W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01867298	BRP393 LED291/WW 217W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01867398	BRP393 LED280/WW 208W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01867498	BRP393 LED268/WW 200W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01867598	BRP393 LED256/WW 192W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01867698	BRP393 LED245/WW 183W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01867798	BRP393 LED233/WW 174W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01867898	BRP393 LED221/WW 166W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01815798	BRP391 LED96/NW 80W 220-240V DM	740 neutral white	No	-	1 unit
01815898	BRP391 LED48/NW 40W 220-240V DM	740 neutral white	No	-	1 unit
01815998	BRP391 LED60/NW 50W 220-240V DM	740 neutral white	No	-	1 unit
01816098	BRP391 LED72/NW 60W 220-240V DM	740 neutral white	No	-	1 unit
32822500	BRP391 LED84/NW 70W 220-240V DM	740 neutral white	No	-	1 unit
01861398	BRP390 LED81/NW 57W 220-240V DM	740 neutral white	PC-MLO	-	-
01861498	BRP390 LED74/NW 52W 220-240V DM	740 neutral white	PC-MLO	-	-
01861598	BRP390 LED68/NW 48W 220-240V DM	740 neutral white	PC-MLO	-	-

Order Code	Full Product Name	Light source colour	Optical cover/lens type	Lamp family code	Number of gear units
01861698	BRP390 LED62/NW 46W 220-240V DM	740 neutral white	PC-MLO	-	-
01861798	BRP390 LED56/NW 41W 220-240V DM	740 neutral white	PC-MLO	-	-
01861898	BRP390 LED50/NW 36W 220-240V DM	740 neutral white	PC-MLO	-	-
01861998	BRP391 LED112/NW 80W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01862098	BRP391 LED105/NW 75W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01862198	BRP391 LED100/NW 70W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01862298	BRP391 LED93/NW 67W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01862398	BRP391 LED87/NW 63W 220-240V DM PSR	740 neutral white	PC-MLO	-	-
01865198	BRP390 LED76/WW 57W 220-240V DM	730 warm white	PC-MLO	-	-
01865298	BRP390 LED70/WW 52W 220-240V DM	730 warm white	PC-MLO	-	-
01865398	BRP390 LED64/WW 48W 220-240V DM	730 warm white	PC-MLO	-	-
01865498	BRP390 LED58/WW 46W 220-240V DM	730 warm white	PC-MLO	-	-
01865598	BRP390 LED52/WW 41W 220-240V DM	730 warm white	PC-MLO	-	-
01865698	BRP390 LED46/WW 36W 220-240V DM	730 warm white	PC-MLO	-	-
01865798	BRP391 LED105/WW 80W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01865898	BRP391 LED100/WW 75W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01865998	BRP391 LED93/WW 70W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01866098	BRP391 LED87/WW 67W 220-240V DM PSR	730 warm white	PC-MLO	-	-
01866198	BRP391 LED81/WW 63W 220-240V DM PSR	730 warm white	PC-MLO	-	-

General Information (2/2)

Order Code	Full Product Name	Optic type
01814798	BRP394 LED348/NW 290W 220-240V DM	-
01814898	BRP394 LED300/NW 250W 220-240V DM	-
01814998	BRP394 LED312/NW 260W 220-240V DM	-
01815098	BRP394 LED288/NW 240W 220-240V DM	-
01815198	BRP394 LED276/NW 230W 220-240V DM	-
01815298	BRP394 LED252/NW 210W 220-240V DM	-
01815398	BRP394 LED240/NW 200W 220-240V DM	-
01815498	BRP394 LED228/NW 190W 220-240V DM	-

Order Code	Full Product Name	Optic type
01816898	BRP394 LED204/NW 170W 220-240V DM	-
01816998	BRP394 LED216/NW 180W 220-240V DM	-
01817098	BRP394 LED264/NW 220W 220-240V DM	-
01817198	BRP394 LED324/NW 270W 220-240V DM	-
01817298	BRP394 LED336/NW 280W 220-240V DM	-
01817398	BRP394 LED360/NW 300W 220-240V DM	-
01817498	BRP394 LED372/NW 310W 220-240V DM	-
01817598	BRP394 LED384/NW 320W 220-240V DM	-

Order Code	Full Product Name	Optic type
01864198	BRP394 LED449/NW 316W 220-240V DM PSR	-
01864298	BRP394 LED437/NW 308W 220-240V DM PSR	-
01864398	BRP394 LED424/NW 300W 220-240V DM PSR	-
01864498	BRP394 LED412/NW 285W 220-240V DM PSR	-
01864598	BRP394 LED398/NW 276W 220-240V DM PSR	-
01864698	BRP394 LED385/NW 268W 220-240V DM PSR	-
01864798	BRP394 LED373/NW 259W 220-240V DM PSR	-
01864898	BRP394 LED360/NW 251W 220-240V DM PSR	-
01864998	BRP394 LED348/NW 242W 220-240V DM PSR	-
01865098	BRP394 LED336/NW 234W 220-240V DM PSR	-
01867998	BRP394 LED421/WW 316W 220-240V DM PSR	-
01868098	BRP394 LED410/WW 308W 220-240V DM PSR	-
01868198	BRP394 LED400/WW 300W 220-240V DM PSR	-
01868298	BRP394 LED386/WW 285W 220-240V DM PSR	-
01868398	BRP394 LED373/WW 276W 220-240V DM PSR	-
01868498	BRP394 LED361/WW 268W 220-240V DM PSR	-
01868598	BRP394 LED350/WW 259W 220-240V DM PSR	-
01868698	BRP394 LED338/WW 251W 220-240V DM PSR	-
01868798	BRP394 LED326/WW 242W 220-240V DM PSR	-
01868898	BRP394 LED315/WW 234W 220-240V DM PSR	-
01815598	BRP392 LED156/NW 130W 220-240V DM	-
01815698	BRP392 LED120/NW 100W 220-240V DM	-
01816298	BRP392 LED108/NW 90W 220-240V DM	-
01816398	BRP392 LED132/NW 110W 220-240V DM	-
01816498	BRP392 LED144/NW 120W 220-240V DM	-
01816598	BRP392 LED168/NW 140W 220-240V DM	-
01816698	BRP392 LED180/NW 150W 220-240V DM	-
01816798	BRP392 LED192/NW 160W 220-240V DM	-
01862498	BRP392 LED224/NW 158W 220-240V DM PSR	-
01862598	BRP392 LED212/NW 150W 220-240V DM PSR	-
01862698	BRP392 LED200/NW 138W 220-240V DM PSR	-
01862798	BRP392 LED186/NW 130W 220-240V DM PSR	-
01862898	BRP392 LED174/NW 121W 220-240V DM PSR	-
01862998	BRP392 LED161/NW 113W 220-240V DM PSR	-
01863098	BRP392 LED150/NW 104W 220-240V DM PSR	-
01863198	BRP392 LED136/NW 96W 220-240V DM PSR	-
01863298	BRP392 LED124/NW 88W 220-240V DM PSR	-
01863398	BRP393 LED323/NW 225W 220-240V DM PSR	-
01863498	BRP393 LED311/NW 217W 220-240V DM PSR	-
01863598	BRP393 LED298/NW 208W 220-240V DM PSR	-
01863698	BRP393 LED286/NW 200W 220-240V DM PSR	-
01863798	BRP393 LED273/NW 192W 220-240V DM PSR	-
01863898	BRP393 LED261/NW 183W 220-240V DM PSR	-
01863998	BRP393 LED248/NW 174W 220-240V DM PSR	-
01864098	BRP393 LED236/NW 166W 220-240V DM PSR	-

Order Code	Full Product Name	Optic type
01866298	BRP392 LED210/WW 158W 220-240V DM PSR	-
01866398	BRP392 LED200/WW 150W 220-240V DM PSR	-
01866498	BRP392 LED186/WW 138W 220-240V DM PSR	-
01866598	BRP392 LED175/WW 130W 220-240V DM PSR	-
01866698	BRP392 LED163/WW 121W 220-240V DM PSR	-
01866798	BRP392 LED151/WW 113W 220-240V DM PSR	-
01866898	BRP392 LED140/WW 104W 220-240V DM PSR	-
01866998	BRP392 LED128/WW 96W 220-240V DM PSR	-
01867098	BRP392 LED116/WW 88W 220-240V DM PSR	-
01867198	BRP393 LED303/WW 225W 220-240V DM PSR	-
01867298	BRP393 LED291/WW 217W 220-240V DM PSR	-
01867398	BRP393 LED280/WW 208W 220-240V DM PSR	-
01867498	BRP393 LED268/WW 200W 220-240V DM PSR	-
01867598	BRP393 LED256/WW 192W 220-240V DM PSR	-
01867698	BRP393 LED245/WW 183W 220-240V DM PSR	-
01867798	BRP393 LED233/WW 174W 220-240V DM PSR	-
01867898	BRP393 LED221/WW 166W 220-240V DM PSR	-
01815798	BRP391 LED96/NW 80W 220-240V DM	-
01815898	BRP391 LED48/NW 40W 220-240V DM	-
01815998	BRP391 LED60/NW 50W 220-240V DM	-
01816098	BRP391 LED72/NW 60W 220-240V DM	-
32822500	BRP391 LED84/NW 70W 220-240V DM	-
01861398	BRP390 LED81/NW 57W 220-240V DM	-
01861498	BRP390 LED74/NW 52W 220-240V DM	-
01861598	BRP390 LED68/NW 48W 220-240V DM	-
01861698	BRP390 LED62/NW 46W 220-240V DM	-
01861798	BRP390 LED56/NW 41W 220-240V DM	-
01861898	BRP390 LED50/NW 36W 220-240V DM	-
01861998	BRP391 LED112/NW 80W 220-240V DM PSR	-
01862098	BRP391 LED105/NW 75W 220-240V DM PSR	-
01862198	BRP391 LED100/NW 70W 220-240V DM PSR	-
01862298	BRP391 LED93/NW 67W 220-240V DM PSR	-
01862398	BRP391 LED87/NW 63W 220-240V DM PSR	-
01865198	BRP390 LED76/WW 57W 220-240V DM	-
01865298	BRP390 LED70/WW 52W 220-240V DM	-
01865398	BRP390 LED64/WW 48W 220-240V DM	-
01865498	BRP390 LED58/WW 46W 220-240V DM	-
01865598	BRP390 LED52/WW 41W 220-240V DM	-
01865698	BRP390 LED46/WW 36W 220-240V DM	-
01865798	BRP391 LED105/WW 80W 220-240V DM PSR	-
01865898	BRP391 LED100/WW 75W 220-240V DM PSR	-
01865998	BRP391 LED93/WW 70W 220-240V DM PSR	-
01866098	BRP391 LED87/WW 67W 220-240V DM PSR	-
01866198	BRP391 LED81/WW 63W 220-240V DM PSR	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
01814798	BRP394 LED348/NW 290W 220-240V DM	4000 K	34800 lm

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
01814898	BRP394 LED300/NW 250W 220-240V DM	4000 K	30000 lm

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
01814998	BRP394 LED312/NW 260W 220-240V DM	4000 K	31200 lm
01815098	BRP394 LED288/NW 240W 220-240V DM	4000 K	28800 lm
01815198	BRP394 LED276/NW 230W 220-240V DM	4000 K	27600 lm
01815298	BRP394 LED252/NW 210W 220-240V DM	4000 K	25200 lm
01815398	BRP394 LED240/NW 200W 220-240V DM	4000 K	24000 lm
01815498	BRP394 LED228/NW 190W 220-240V DM	4000 K	22800 lm
01816898	BRP394 LED204/NW 170W 220-240V DM	4000 K	20400 lm
01816998	BRP394 LED216/NW 180W 220-240V DM	4000 K	21600 lm
01817098	BRP394 LED264/NW 220W 220-240V DM	4000 K	26400 lm
01817198	BRP394 LED324/NW 270W 220-240V DM	4000 K	32400 lm
01817298	BRP394 LED336/NW 280W 220-240V DM	4000 K	33600 lm
01817398	BRP394 LED360/NW 300W 220-240V DM	4000 K	36000 lm
01817498	BRP394 LED372/NW 310W 220-240V DM	4000 K	37200 lm
01817598	BRP394 LED384/NW 320W 220-240V DM	4000 K	38400 lm
01864198	BRP394 LED449/NW 316W 220-240V DM PSR	4000 K	44991 lm
01864298	BRP394 LED437/NW 308W 220-240V DM PSR	4000 K	43742 lm
01864398	BRP394 LED424/NW 300W 220-240V DM PSR	4000 K	42492 lm
01864498	BRP394 LED412/NW 285W 220-240V DM PSR	4000 K	41243 lm
01864598	BRP394 LED398/NW 276W 220-240V DM PSR	4000 K	39828 lm
01864698	BRP394 LED385/NW 268W 220-240V DM PSR	4000 K	38583 lm
01864798	BRP394 LED373/NW 259W 220-240V DM PSR	4000 K	37338 lm
01864898	BRP394 LED360/NW 251W 220-240V DM PSR	4000 K	36093 lm
01864998	BRP394 LED348/NW 242W 220-240V DM PSR	4000 K	34849 lm
01865098	BRP394 LED336/NW 234W 220-240V DM PSR	4000 K	33604 lm
01867998	BRP394 LED421/WW 316W 220-240V DM PSR	3000 K	42179 lm

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
01868098	BRP394 LED410/WW 308W 220-240V DM PSR	3000 K	41008 lm
01868198	BRP394 LED400/WW 300W 220-240V DM PSR	3000 K	39837 lm
01868298	BRP394 LED386/WW 285W 220-240V DM PSR	3000 K	38665 lm
01868398	BRP394 LED373/WW 276W 220-240V DM PSR	3000 K	37338 lm
01868498	BRP394 LED361/WW 268W 220-240V DM PSR	3000 K	36171 lm
01868598	BRP394 LED350/WW 259W 220-240V DM PSR	3000 K	35005 lm
01868698	BRP394 LED338/WW 251W 220-240V DM PSR	3000 K	33838 lm
01868798	BRP394 LED326/WW 242W 220-240V DM PSR	3000 K	32671 lm
01868898	BRP394 LED315/WW 234W 220-240V DM PSR	3000 K	31504 lm
01815598	BRP392 LED156/NW 130W 220-240V DM	4000 K	15600 lm
01815698	BRP392 LED120/NW 100W 220-240V DM	4000 K	12000 lm
01816298	BRP392 LED108/NW 90W 220-240V DM	4000 K	10800 lm
01816398	BRP392 LED132/NW 110W 220-240V DM	4000 K	13200 lm
01816498	BRP392 LED144/NW 120W 220-240V DM	4000 K	14400 lm
01816598	BRP392 LED168/NW 140W 220-240V DM	4000 K	16800 lm
01816698	BRP392 LED180/NW 150W 220-240V DM	4000 K	18000 lm
01816798	BRP392 LED192/NW 160W 220-240V DM	4000 K	19200 lm
01862498	BRP392 LED224/NW 158W 220-240V DM PSR	4000 K	22495 lm
01862598	BRP392 LED212/NW 150W 220-240V DM PSR	4000 K	21246 lm
01862698	BRP392 LED200/NW 138W 220-240V DM PSR	4000 K	19914 lm
01862798	BRP392 LED186/NW 130W 220-240V DM PSR	4000 K	18669 lm
01862898	BRP392 LED174/NW 121W 220-240V DM PSR	4000 K	17425 lm
01862998	BRP392 LED161/NW 113W 220-240V DM PSR	4000 K	16179 lm
01863098	BRP392 LED150/NW 104W 220-240V DM PSR	4000 K	14935 lm
01863198	BRP392 LED136/NW 96W 220-240V DM PSR	4000 K	13690 lm

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
01863298	BRP392 LED124/NW 88W 220-240V DM PSR	4000 K	12446 lm
01863398	BRP393 LED323/NW 225W 220-240V DM PSR	4000 K	32360 lm
01863498	BRP393 LED311/NW 217W 220-240V DM PSR	4000 K	31115 lm
01863598	BRP393 LED298/NW 208W 220-240V DM PSR	4000 K	29871 lm
01863698	BRP393 LED286/NW 200W 220-240V DM PSR	4000 K	28626 lm
01863798	BRP393 LED273/NW 192W 220-240V DM PSR	4000 K	27382 lm
01863898	BRP393 LED261/NW 183W 220-240V DM PSR	4000 K	26136 lm
01863998	BRP393 LED248/NW 174W 220-240V DM PSR	4000 K	24892 lm
01864098	BRP393 LED236/NW 166W 220-240V DM PSR	4000 K	23647 lm
01866298	BRP392 LED210/WW 158W 220-240V DM PSR	3000 K	21089 lm
01866398	BRP392 LED200/WW 150W 220-240V DM PSR	3000 K	19918 lm
01866498	BRP392 LED186/WW 138W 220-240V DM PSR	3000 K	18669 lm
01866598	BRP392 LED175/WW 130W 220-240V DM PSR	3000 K	17502 lm
01866698	BRP392 LED163/WW 121W 220-240V DM PSR	3000 K	16336 lm
01866798	BRP392 LED151/WW 113W 220-240V DM PSR	3000 K	15168 lm
01866898	BRP392 LED140/WW 104W 220-240V DM PSR	3000 K	14002 lm
01866998	BRP392 LED128/WW 96W 220-240V DM PSR	3000 K	12835 lm
01867098	BRP392 LED116/WW 88W 220-240V DM PSR	3000 K	11668 lm
01867198	BRP393 LED303/WW 225W 220-240V DM PSR	3000 K	30338 lm
01867298	BRP393 LED291/WW 217W 220-240V DM PSR	3000 K	29170 lm
01867398	BRP393 LED280/WW 208W 220-240V DM PSR	3000 K	28004 lm
01867498	BRP393 LED268/WW 200W 220-240V DM PSR	3000 K	26837 lm
01867598	BRP393 LED256/WW 192W 220-240V DM PSR	3000 K	25670 lm
01867698	BRP393 LED245/WW 183W 220-240V DM PSR	3000 K	24503 lm
01867798	BRP393 LED233/WW 174W 220-240V DM PSR	3000 K	23337 lm

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
01867898	BRP393 LED221/WW 166W 220-240V DM PSR	3000 K	22169 lm
01815798	BRP391 LED96/NW 80W 220-240V DM	4000 K	9600 lm
01815898	BRP391 LED48/NW 40W 220-240V DM	4000 K	4800 lm
01815998	BRP391 LED60/NW 50W 220-240V DM	4000 K	6000 lm
01816098	BRP391 LED72/NW 60W 220-240V DM	4000 K	7200 lm
32822500	BRP391 LED84/NW 70W 220-240V DM	4000 K	8400 lm
01861398	BRP390 LED81/NW 57W 220-240V DM	4000 K	8123 lm
01861498	BRP390 LED74/NW 52W 220-240V DM	4000 K	7498 lm
01861598	BRP390 LED68/NW 48W 220-240V DM	4000 K	6874 lm
01861698	BRP390 LED62/NW 46W 220-240V DM	4000 K	6249 lm
01861798	BRP390 LED56/NW 41W 220-240V DM	4000 K	5624 lm
01861898	BRP390 LED50/NW 36W 220-240V DM	4000 K	4999 lm
01861998	BRP391 LED112/NW 80W 220-240V DM PSR	4000 K	11201 lm
01862098	BRP391 LED105/NW 75W 220-240V DM PSR	4000 K	10579 lm
01862198	BRP391 LED100/NW 70W 220-240V DM PSR	4000 K	9957 lm
01862298	BRP391 LED93/NW 67W 220-240V DM PSR	4000 K	9334 lm
01862398	BRP391 LED87/NW 63W 220-240V DM PSR	4000 K	8712 lm
01865198	BRP390 LED76/WW 57W 220-240V DM	3000 K	7615 lm
01865298	BRP390 LED70/WW 52W 220-240V DM	3000 K	7030 lm
01865398	BRP390 LED64/WW 48W 220-240V DM	3000 K	6444 lm
01865498	BRP390 LED58/WW 46W 220-240V DM	3000 K	5859 lm
01865598	BRP390 LED52/WW 41W 220-240V DM	3000 K	5272 lm
01865698	BRP390 LED46/WW 36W 220-240V DM	3000 K	4687 lm
01865798	BRP391 LED105/WW 80W 220-240V DM PSR	3000 K	10501 lm
01865898	BRP391 LED100/WW 75W 220-240V DM PSR	3000 K	9918 lm

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
01865998	BRP391 LED93/WW 70W 220-240V DM PSR	3000 K	9335 lm
01866098	BRP391 LED87/WW 67W 220-240V DM PSR	3000 K	8751 lm

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
01866198	BRP391 LED81/WW 63W 220-240V DM PSR	3000 K	8167 lm

Light Technical

Order Code	Full Product Name	Standard tilt	
		angle side entry	Upward light output ratio
01814798	BRP394 LED348/NW 290W 220-240V DM	0°	0
01814898	BRP394 LED300/NW 250W 220-240V DM	0°	0
01814998	BRP394 LED312/NW 260W 220-240V DM	0°	0
01815098	BRP394 LED288/NW 240W 220-240V DM	0°	0
01815198	BRP394 LED276/NW 230W 220-240V DM	0°	0
01815298	BRP394 LED252/NW 210W 220-240V DM	0°	0
01815398	BRP394 LED240/NW 200W 220-240V DM	0°	0
01815498	BRP394 LED228/NW 190W 220-240V DM	0°	0
01816898	BRP394 LED204/NW 170W 220-240V DM	0°	0
01816998	BRP394 LED216/NW 180W 220-240V DM	0°	0
01817098	BRP394 LED264/NW 220W 220-240V DM	0°	0
01817198	BRP394 LED324/NW 270W 220-240V DM	0°	0
01817298	BRP394 LED336/NW 280W 220-240V DM	0°	0
01817398	BRP394 LED360/NW 300W 220-240V DM	0°	0
01817498	BRP394 LED372/NW 310W 220-240V DM	0°	0
01817598	BRP394 LED384/NW 320W 220-240V DM	0°	0
01864198	BRP394 LED449/NW 316W 220-240V DM PSR	-	-
01864298	BRP394 LED437/NW 308W 220-240V DM PSR	-	-
01864398	BRP394 LED424/NW 300W 220-240V DM PSR	-	-
01864498	BRP394 LED412/NW 285W 220-240V DM PSR	-	-
01864598	BRP394 LED398/NW 276W 220-240V DM PSR	-	-
01864698	BRP394 LED385/NW 268W 220-240V DM PSR	-	-
01864798	BRP394 LED373/NW 259W 220-240V DM PSR	-	-
01864898	BRP394 LED360/NW 251W 220-240V DM PSR	-	-
01864998	BRP394 LED348/NW 242W 220-240V DM PSR	-	-
01865098	BRP394 LED336/NW 234W 220-240V DM PSR	-	-
01867998	BRP394 LED421/WW 316W 220-240V DM PSR	-	-
01868098	BRP394 LED410/WW 308W 220-240V DM PSR	-	-

Order Code	Full Product Name	Standard tilt	
		angle side entry	Upward light output ratio
01868198	BRP394 LED400/WW 300W 220-240V DM PSR	-	-
01868298	BRP394 LED386/WW 285W 220-240V DM PSR	-	-
01868398	BRP394 LED373/WW 276W 220-240V DM PSR	-	-
01868498	BRP394 LED361/WW 268W 220-240V DM PSR	-	-
01868598	BRP394 LED350/WW 259W 220-240V DM PSR	-	-
01868698	BRP394 LED338/WW 251W 220-240V DM PSR	-	-
01868798	BRP394 LED326/WW 242W 220-240V DM PSR	-	-
01868898	BRP394 LED315/WW 234W 220-240V DM PSR	-	-
01815598	BRP392 LED156/NW 130W 220-240V DM	0°	0
01815698	BRP392 LED120/NW 100W 220-240V DM	0°	0
01816298	BRP392 LED108/NW 90W 220-240V DM	0°	0
01816398	BRP392 LED132/NW 110W 220-240V DM	0°	0
01816498	BRP392 LED144/NW 120W 220-240V DM	0°	0
01816598	BRP392 LED168/NW 140W 220-240V DM	0°	0
01816698	BRP392 LED180/NW 150W 220-240V DM	0°	0
01816798	BRP392 LED192/NW 160W 220-240V DM	0°	0
01862498	BRP392 LED224/NW 158W 220-240V DM PSR	-	-
01862598	BRP392 LED212/NW 150W 220-240V DM PSR	-	-
01862698	BRP392 LED200/NW 138W 220-240V DM PSR	-	-
01862798	BRP392 LED186/NW 130W 220-240V DM PSR	-	-
01862898	BRP392 LED174/NW 121W 220-240V DM PSR	-	-
01862998	BRP392 LED161/NW 113W 220-240V DM PSR	-	-
01863098	BRP392 LED150/NW 104W 220-240V DM PSR	-	-
01863198	BRP392 LED136/NW 96W 220-240V DM PSR	-	-

Order Code	Full Product Name	Standard tilt angle side entry	Upward light output ratio
01863298	BRP392 LED124/NW 88W 220-240V DM PSR	-	-
01863398	BRP393 LED323/NW 225W 220-240V DM PSR	-	-
01863498	BRP393 LED311/NW 217W 220-240V DM PSR	-	-
01863598	BRP393 LED298/NW 208W 220-240V DM PSR	-	-
01863698	BRP393 LED286/NW 200W 220-240V DM PSR	-	-
01863798	BRP393 LED273/NW 192W 220-240V DM PSR	-	-
01863898	BRP393 LED261/NW 183W 220-240V DM PSR	-	-
01863998	BRP393 LED248/NW 174W 220-240V DM PSR	-	-
01864098	BRP393 LED236/NW 166W 220-240V DM PSR	-	-
01866298	BRP392 LED210/WW 158W 220-240V DM PSR	-	-
01866398	BRP392 LED200/WW 150W 220-240V DM PSR	-	-
01866498	BRP392 LED186/WW 138W 220-240V DM PSR	-	-
01866598	BRP392 LED175/WW 130W 220-240V DM PSR	-	-
01866698	BRP392 LED163/WW 121W 220-240V DM PSR	-	-
01866798	BRP392 LED151/WW 113W 220-240V DM PSR	-	-
01866898	BRP392 LED140/WW 104W 220-240V DM PSR	-	-
01866998	BRP392 LED128/WW 96W 220-240V DM PSR	-	-
01867098	BRP392 LED116/WW 88W 220-240V DM PSR	-	-
01867198	BRP393 LED303/WW 225W 220-240V DM PSR	-	-
01867298	BRP393 LED291/WW 217W 220-240V DM PSR	-	-
01867398	BRP393 LED280/WW 208W 220-240V DM PSR	-	-
01867498	BRP393 LED268/WW 200W 220-240V DM PSR	-	-

Order Code	Full Product Name	Standard tilt angle side entry	Upward light output ratio
01867598	BRP393 LED256/WW 192W 220-240V DM PSR	-	-
01867698	BRP393 LED245/WW 183W 220-240V DM PSR	-	-
01867798	BRP393 LED233/WW 174W 220-240V DM PSR	-	-
01867898	BRP393 LED221/WW 166W 220-240V DM PSR	-	-
01815798	BRP391 LED96/NW 80W 220-240V DM	0°	0
01815898	BRP391 LED48/NW 40W 220-240V DM	0°	0
01815998	BRP391 LED60/NW 50W 220-240V DM	0°	0
01816098	BRP391 LED72/NW 60W 220-240V DM	0°	0
32822500	BRP391 LED84/NW 70W 220-240V DM	0°	0
01861398	BRP390 LED81/NW 57W 220-240V DM	-	-
01861498	BRP390 LED74/NW 52W 220-240V DM	-	-
01861598	BRP390 LED68/NW 48W 220-240V DM	-	-
01861698	BRP390 LED62/NW 46W 220-240V DM	-	-
01861798	BRP390 LED56/NW 41W 220-240V DM	-	-
01861898	BRP390 LED50/NW 36W 220-240V DM	-	-
01861998	BRP391 LED112/NW 80W 220-240V DM PSR	-	-
01862098	BRP391 LED105/NW 75W 220-240V DM PSR	-	-
01862198	BRP391 LED100/NW 70W 220-240V DM PSR	-	-
01862298	BRP391 LED93/NW 67W 220-240V DM PSR	-	-
01862398	BRP391 LED87/NW 63W 220-240V DM PSR	-	-
01865198	BRP390 LED76/WW 57W 220-240V DM	-	-
01865298	BRP390 LED70/WW 52W 220-240V DM	-	-
01865398	BRP390 LED64/WW 48W 220-240V DM	-	-
01865498	BRP390 LED58/WW 46W 220-240V DM	-	-
01865598	BRP390 LED52/WW 41W 220-240V DM	-	-
01865698	BRP390 LED46/WW 36W 220-240V DM	-	-
01865798	BRP391 LED105/WW 80W 220-240V DM PSR	-	-
01865898	BRP391 LED100/WW 75W 220-240V DM PSR	-	-
01865998	BRP391 LED93/WW 70W 220-240V DM PSR	-	-
01866098	BRP391 LED87/WW 67W 220-240V DM PSR	-	-
01866198	BRP391 LED81/WW 63W 220-240V DM PSR	-	-

