



# Setting the standard in Surface-mounted LED Downlight

## GreenSpace Surface-mounted

Philips GreenSpace Surface-mounted LED Downlight delivers a superior LED alternative that's up to 66% more energy efficient than the conventional downlight retrofits. Blending seamlessly into its environment, GreenSpace Surface-mounted LED Downlight mimics the form of conventional recessed downlights minus the associated high energy and maintenance costs. Philips GreenSpace Surface-mounted LED Downlight is also ideal for all commercial lighting applications as well as public indoor space where there is limited space in the ceiling.

### Benefits

- Lumen output: Different lumens in different sizes and mounting heights with options of 1000lm, 2000lm, 3800lm & 6600lm.
- Superior light performance: Colours rendered accurately (CRI>80) and high system efficacy (100lm/w)
- Varieties: IP20, IP65 version with choice of different lumen output, and option of black housing through tailor-made
- Long lifetime: 50,000 hour lifetime ensures more savings in the long run

### Features

- System efficacy: 100lm/W, energy saving up to 66% vs conventional downlights
- Reliable performance: Lifetime 50,000 hours (L70B50@Ta25°C)
- Excellent light quality - CRI>=80 @3000K, 4000K and 6500K
- Integral lightweight design - Installation cost is significantly reduced

## GreenSpace Surface-mounted

### Application

- Shopping mall
- Station concourse
- Canopy
- Airport public area
- Stadium public area

### Versions



SM291C/SM293C



SM295C LED68

# GreenSpace Surface-mounted

## Application Conditions

Ambient temperature range	-20 to +40 °C
Suitable for random switching	No

## Approval and Application

Mech. impact protection code	IK02
------------------------------	------

## Controls and Dimming

Dimmable	No
----------	----

## Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

## General Information

CE mark	CE mark
Protection class IEC	Safety class I (I)
Optical cover/lens type	Reflector
Driver included	Yes
Glow-wire test	750/5
Light source replaceable	No
Number of gear units	1 unit
Optic type	C

## Initial Performance (IEC Compliant)

Init. Colour rendering index	>80
Luminous flux tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Median useful life L80B50	40000 h
Median useful life L90B50	20000 h

-

Order Code	Full Product Name	Driver failure rate at 5,000 hours
01508831	SM291C LED10/830 PSU WH	1.00 %
01508931	SM291C LED10/840 PSU WH	1.00 %
01509031	SM291C LED10/865 PSU WH	1.00 %
01509131	SM291C LED10/830 PSU BK	1.00 %
01509231	SM291C LED10/840 PSU BK	1.00 %
01509331	SM291C LED10/865 PSU BK	1.00 %
01509431	SM293C LED20/830 PSU WH	1.00 %
01509531	SM293C LED20/840 PSU WH	1.00 %
01509631	SM293C LED20/865 PSU WH	1.00 %
01509731	SM293C LED20/830 PSU BK	1.00 %
01509831	SM293C LED20/840 PSU BK	1.00 %
01509931	SM293C LED20/865 PSU BK	1.00 %
01510031	SM294C LED40/830 PSU WH	1.00 %
01510131	SM294C LED40/840 PSU WH	1.00 %
01510231	SM294C LED40/865 PSU WH	1.00 %
01510331	SM294C LED40/830 PSU BK	1.00 %
01510431	SM294C LED40/840 PSU BK	1.00 %
01510531	SM294C LED40/865 PSU BK	1.00 %
01511231	SM294C LED40/830 PSU WP WH	1.00 %
01511331	SM294C LED40/840 PSU WP WH	1.00 %
01511431	SM294C LED40/865 PSU WP WH	1.00 %
01511531	SM294C LED40/830 PSU WP BK	1.00 %
01511631	SM294C LED40/840 PSU WP BK	1.00 %
01511731	SM294C LED40/865 PSU WP BK	1.00 %
01847199	SM291C LED10/830 PSU WH GM	1.00 %
01847299	SM291C LED10/840 PSU WH GM	1.00 %
01847399	SM291C LED10/865 PSU WH GM	1.00 %
01847499	SM293C LED20/830 PSU WH GM	1.00 %
01847599	SM293C LED20/840 PSU WH GM	1.00 %
01847699	SM293C LED20/865 PSU WH GM	1.00 %
01847799	SM295C LED70/840 PSU WP WH GM	1.00 %
01847899	SM295C LED70/830 PSU WP WH GM	1.00 %
01847999	SM294C LED40/840 PSU WP WH GM	1.00 %
01848299	SM294C LED40/865 PSU WP WH GM	1.00 %
01848399	SM294C LED40/830 PSU WP WH GM	1.00 %
01848599	SM294C LED40/830 PSU WH GM	1.00 %
01848699	SM294C LED40/840 PSU WH GM	1.00 %
01848799	SM294C LED40/865 PSU WH GM	1.00 %
01848899	SM295C LED70/840 PSU WH GM	1.00 %
01510631	SM295C LED68/830 PSU WH	0.01 %
01510731	SM295C LED68/840 PSU WH	0.01 %
01510831	SM295C LED68/865 PSU WH	0.01 %
01510931	SM295C LED68/830 PSU BK	0.01 %
01511031	SM295C LED68/840 PSU BK	0.01 %
01511131	SM295C LED68/865 PSU BK	0.01 %
01511831	SM295C LED68/830 PSU WP WH	0.01 %
01511931	SM295C LED68/840 PSU WP WH	0.01 %
01512031	SM295C LED68/865 PSU WP WH	0.01 %
01512131	SM295C LED68/830 PSU WP BK	0.01 %
01512231	SM295C LED68/840 PSU WP BK	0.01 %
01512331	SM295C LED68/865 PSU WP BK	0.01 %

# GreenSpace Surface-mounted

## Application Conditions

Order Code	Full Product Name	Maximum dimming level	Order Code	Full Product Name	Maximum dimming level
01508831	SM291C LED10/830 PSU WH	-	01847399	SM291C LED10/865 PSU WH GM	-
01508931	SM291C LED10/840 PSU WH	-	01847499	SM293C LED20/830 PSU WH GM	-
01509031	SM291C LED10/865 PSU WH	-	01847599	SM293C LED20/840 PSU WH GM	-
01509131	SM291C LED10/830 PSU BK	-	01847699	SM293C LED20/865 PSU WH GM	-
01509231	SM291C LED10/840 PSU BK	-	01847799	SM295C LED70/840 PSU WP WH GM	-
01509331	SM291C LED10/865 PSU BK	-	01847899	SM295C LED70/830 PSU WP WH GM	-
01509431	SM293C LED20/830 PSU WH	-	01847999	SM294C LED40/840 PSU WP WH GM	-
01509531	SM293C LED20/840 PSU WH	-	01848299	SM294C LED40/865 PSU WP WH GM	-
01509631	SM293C LED20/865 PSU WH	-	01848399	SM294C LED40/830 PSU WP WH GM	-
01509731	SM293C LED20/830 PSU BK	-	01848599	SM294C LED40/830 PSU WH GM	-
01509831	SM293C LED20/840 PSU BK	-	01848699	SM294C LED40/840 PSU WH GM	-
01509931	SM293C LED20/865 PSU BK	-	01848799	SM294C LED40/865 PSU WH GM	-
01510031	SM294C LED40/830 PSU WH	-	01848899	SM295C LED70/840 PSU WH GM	-
01510131	SM294C LED40/840 PSU WH	-	01510631	SM295C LED68/830 PSU WH	Not applicable
01510231	SM294C LED40/865 PSU WH	-	01510731	SM295C LED68/840 PSU WH	Not applicable
01510331	SM294C LED40/830 PSU BK	-	01510831	SM295C LED68/865 PSU WH	Not applicable
01510431	SM294C LED40/840 PSU BK	-	01510931	SM295C LED68/830 PSU BK	Not applicable
01510531	SM294C LED40/865 PSU BK	-	01511031	SM295C LED68/840 PSU BK	Not applicable
01511231	SM294C LED40/830 PSU WP WH	-	01511131	SM295C LED68/865 PSU BK	Not applicable
01511331	SM294C LED40/840 PSU WP WH	-	01511831	SM295C LED68/830 PSU WP WH	Not applicable
01511431	SM294C LED40/865 PSU WP WH	-	01511931	SM295C LED68/840 PSU WP WH	Not applicable
01511531	SM294C LED40/830 PSU WP BK	-	01512031	SM295C LED68/865 PSU WP WH	Not applicable
01511631	SM294C LED40/840 PSU WP BK	-	01512131	SM295C LED68/830 PSU WP BK	Not applicable
01511731	SM294C LED40/865 PSU WP BK	-	01512231	SM295C LED68/840 PSU WP BK	Not applicable
01847199	SM291C LED10/830 PSU WH GM	-	01512331	SM295C LED68/865 PSU WP BK	Not applicable
01847299	SM291C LED10/840 PSU WH GM	-			

## Approval and Application

Order Code	Full Product Name	Ingress protection code	Order Code	Full Product Name	Ingress protection code
01508831	SM291C LED10/830 PSU WH	IP20	01511431	SM294C LED40/865 PSU WP WH	IP65
01508931	SM291C LED10/840 PSU WH	IP20	01511531	SM294C LED40/830 PSU WP BK	IP65
01509031	SM291C LED10/865 PSU WH	IP20	01511631	SM294C LED40/840 PSU WP BK	IP65
01509131	SM291C LED10/830 PSU BK	IP20	01511731	SM294C LED40/865 PSU WP BK	IP65
01509231	SM291C LED10/840 PSU BK	IP20	01847199	SM291C LED10/830 PSU WH GM	IP20
01509331	SM291C LED10/865 PSU BK	IP20	01847299	SM291C LED10/840 PSU WH GM	IP20
01509431	SM293C LED20/830 PSU WH	IP20	01847399	SM291C LED10/865 PSU WH GM	IP20
01509531	SM293C LED20/840 PSU WH	IP20	01847499	SM293C LED20/830 PSU WH GM	IP20
01509631	SM293C LED20/865 PSU WH	IP20	01847599	SM293C LED20/840 PSU WH GM	IP20
01509731	SM293C LED20/830 PSU BK	IP20	01847699	SM293C LED20/865 PSU WH GM	IP20
01509831	SM293C LED20/840 PSU BK	IP20	01847799	SM295C LED70/840 PSU WP WH GM	IP65
01509931	SM293C LED20/865 PSU BK	IP20	01847899	SM295C LED70/830 PSU WP WH GM	IP65
01510031	SM294C LED40/830 PSU WH	IP65	01847999	SM294C LED40/840 PSU WP WH GM	IP65
01510131	SM294C LED40/840 PSU WH	IP65	01848299	SM294C LED40/865 PSU WP WH GM	IP65
01510231	SM294C LED40/865 PSU WH	IP65	01848399	SM294C LED40/830 PSU WP WH GM	IP65
01510331	SM294C LED40/830 PSU BK	IP65	01848599	SM294C LED40/830 PSU WH GM	IP20
01510431	SM294C LED40/840 PSU BK	IP65	01848699	SM294C LED40/840 PSU WH GM	IP20
01510531	SM294C LED40/865 PSU BK	IP65	01848799	SM294C LED40/865 PSU WH GM	IP20
01511231	SM294C LED40/830 PSU WP WH	IP65	01848899	SM295C LED70/840 PSU WH GM	IP20
01511331	SM294C LED40/840 PSU WP WH	IP65	01510631	SM295C LED68/830 PSU WH	IP65

## GreenSpace Surface-mounted

Order Code	Full Product Name	Ingress protection code
01510731	SM295C LED68/840 PSU WH	IP65
01510831	SM295C LED68/865 PSU WH	IP65
01510931	SM295C LED68/830 PSU BK	IP65
01511031	SM295C LED68/840 PSU BK	IP65
01511131	SM295C LED68/865 PSU BK	IP65
01511831	SM295C LED68/830 PSU WP WH	IP65

Order Code	Full Product Name	Ingress protection code
01511931	SM295C LED68/840 PSU WP WH	IP65
01512031	SM295C LED68/865 PSU WP WH	IP65
01512131	SM295C LED68/830 PSU WP BK	IP65
01512231	SM295C LED68/840 PSU WP BK	IP65
01512331	SM295C LED68/865 PSU WP BK	IP65

### General Information

Order Code	Full Product Name	Beam angle		
		of light source	ENEC mark	Flammability mark
01508831	SM291C LED10/830 PSU WH	-	-	-
01508931	SM291C LED10/840 PSU WH	-	-	-
01509031	SM291C LED10/865 PSU WH	-	-	-
01509131	SM291C LED10/830 PSU BK	-	-	-
01509231	SM291C LED10/840 PSU BK	-	-	-
01509331	SM291C LED10/865 PSU BK	-	-	-
01509431	SM293C LED20/830 PSU WH	-	-	-
01509531	SM293C LED20/840 PSU WH	-	-	-
01509631	SM293C LED20/865 PSU WH	-	-	-
01509731	SM293C LED20/830 PSU BK	-	-	-
01509831	SM293C LED20/840 PSU BK	-	-	-
01509931	SM293C LED20/865 PSU BK	-	-	-
01510031	SM294C LED40/830 PSU WH	-	-	-
01510131	SM294C LED40/840 PSU WH	-	-	-
01510231	SM294C LED40/865 PSU WH	-	-	-
01510331	SM294C LED40/830 PSU BK	-	-	-
01510431	SM294C LED40/840 PSU BK	-	-	-
01510531	SM294C LED40/865 PSU BK	-	-	-
01511231	SM294C LED40/830 PSU WP WH	-	-	-
01511331	SM294C LED40/840 PSU WP WH	-	-	-
01511431	SM294C LED40/865 PSU WP WH	-	-	-
01511531	SM294C LED40/830 PSU WP BK	-	-	-
01511631	SM294C LED40/840 PSU WP BK	-	-	-
01511731	SM294C LED40/865 PSU WP BK	-	-	-
01847199	SM291C LED10/830 PSU WH GM	-°	-	NO
01847299	SM291C LED10/840 PSU WH GM	-°	-	NO
01847399	SM291C LED10/865 PSU WH GM	-°	-	NO
01847499	SM293C LED20/830 PSU WH GM	-°	-	NO
01847599	SM293C LED20/840 PSU WH GM	-°	-	NO

Order Code	Full Product Name	Beam angle		
		of light source	ENEC mark	Flammability mark
01847699	SM293C LED20/865 PSU WH GM	-°	-	NO
01847799	SM295C LED70/840 PSU WP WH GM	-°	-	NO
01847899	SM295C LED70/830 PSU WP WH GM	-°	-	NO
01847999	SM294C LED40/840 PSU WP WH GM	-°	-	NO
01848299	SM294C LED40/865 PSU WP WH GM	-°	-	NO
01848399	SM294C LED40/830 PSU WP WH GM	-°	-	NO
01848599	SM294C LED40/830 PSU WH GM	-°	-	NO
01848699	SM294C LED40/840 PSU WH GM	-°	-	NO
01848799	SM294C LED40/865 PSU WH GM	-°	-	NO
01848899	SM295C LED70/840 PSU WH GM	-°	-	NO
01510631	SM295C LED68/830 PSU WH	-	-	-
01510731	SM295C LED68/840 PSU WH	-	-	-
01510831	SM295C LED68/865 PSU WH	-	-	-
01510931	SM295C LED68/830 PSU BK	-	-	-
01511031	SM295C LED68/840 PSU BK	-	-	-
01511131	SM295C LED68/865 PSU BK	-	-	-
01511831	SM295C LED68/830 PSU WP WH	-	-	-
01511931	SM295C LED68/840 PSU WP WH	-	-	-
01512031	SM295C LED68/865 PSU WP WH	-	-	-
01512131	SM295C LED68/830 PSU WP BK	-	-	-
01512231	SM295C LED68/840 PSU WP BK	-	-	-
01512331	SM295C LED68/865 PSU WP BK	-	-	-

## Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
01508831	SM291C LED10/830 PSU WH	(0.44, 0.40) SDCM <5	3000 K	100 lm/W	1000 lm
01508931	SM291C LED10/840 PSU WH	(0.38, 0.38) SDCM <5	4000 K	100 lm/W	1000 lm
01509031	SM291C LED10/865 PSU WH	(0.31, 0.32) SDCM <5	6500 K	100 lm/W	1000 lm
01509131	SM291C LED10/830 PSU BK	(0.44, 0.40) SDCM <5	3000 K	100 lm/W	1000 lm
01509231	SM291C LED10/840 PSU BK	(0.38, 0.38) SDCM <5	4000 K	100 lm/W	1000 lm
01509331	SM291C LED10/865 PSU BK	(0.31, 0.32) SDCM <5	6500 K	100 lm/W	1000 lm
01509431	SM293C LED20/830 PSU WH	(0.44, 0.40) SDCM <5	3000 K	105 lm/W	2000 lm
01509531	SM293C LED20/840 PSU WH	(0.38, 0.38) SDCM <5	4000 K	105 lm/W	2000 lm
01509631	SM293C LED20/865 PSU WH	(0.31, 0.32) SDCM <5	6500 K	105 lm/W	2000 lm
01509731	SM293C LED20/830 PSU BK	(0.44, 0.40) SDCM <5	3000 K	105 lm/W	2000 lm
01509831	SM293C LED20/840 PSU BK	(0.38, 0.38) SDCM <5	4000 K	105 lm/W	2000 lm
01509931	SM293C LED20/865 PSU BK	(0.31, 0.32) SDCM <5	6500 K	105 lm/W	2000 lm
01510031	SM294C LED40/830 PSU WH	(0.44, 0.40) SDCM <5	3000 K	105 lm/W	3800 lm
01510131	SM294C LED40/840 PSU WH	(0.38, 0.38) SDCM <5	4000 K	105 lm/W	3800 lm
01510231	SM294C LED40/865 PSU WH	(0.31, 0.32) SDCM <5	6500 K	105 lm/W	3800 lm
01510331	SM294C LED40/830 PSU BK	(0.44, 0.40) SDCM <5	3000 K	105 lm/W	3800 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
01510431	SM294C LED40/840 PSU BK	(0.38, 0.38) SDCM <5	4000 K	105 lm/W	3800 lm
01510531	SM294C LED40/865 PSU BK	(0.31, 0.32) SDCM <5	6500 K	105 lm/W	3800 lm
01511231	SM294C LED40/830 PSU WP WH	(0.44, 0.40) SDCM <5	3000 K	105 lm/W	3800 lm
01511331	SM294C LED40/840 PSU WP WH	(0.38, 0.38) SDCM <5	4000 K	105 lm/W	3800 lm
01511431	SM294C LED40/865 PSU WP WH	(0.31, 0.32) SDCM <5	6500 K	105 lm/W	3800 lm
01511531	SM294C LED40/830 PSU WP BK	(0.44, 0.40) SDCM <5	3000 K	105 lm/W	3800 lm
01511631	SM294C LED40/840 PSU WP BK	(0.38, 0.38) SDCM <5	4000 K	105 lm/W	3800 lm
01511731	SM294C LED40/865 PSU WP BK	(0.31, 0.32) SDCM <5	6500 K	105 lm/W	3800 lm
01847199	SM291C LED10/830 PSU WH GM	(0.44, 0.40) SDCM <5	3000 K	100 lm/W	1000 lm
01847299	SM291C LED10/840 PSU WH GM	(0.38, 0.38) SDCM <5	4000 K	100 lm/W	1000 lm
01847399	SM291C LED10/865 PSU WH GM	(0.31, 0.32) SDCM <5	6500 K	100 lm/W	1000 lm
01847499	SM293C LED20/830 PSU WH GM	(0.44, 0.40) SDCM <5	3000 K	105 lm/W	2000 lm
01847599	SM293C LED20/840 PSU WH GM	(0.38, 0.38) SDCM <5	4000 K	105 lm/W	2000 lm
01847699	SM293C LED20/865 PSU WH GM	(0.31, 0.32) SDCM <5	6500 K	105 lm/W	2000 lm
01847799	SM295C LED70/840 PSU WP WH GM	(0.38, 0.38) SDCM <5	4000 K	100 lm/W	6600 lm
01847899	SM295C LED70/830	(0.44, 0.40) SDCM <5	3000 K	100 lm/W	6600 lm

## GreenSpace Surface-mounted

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
	PSU WP WH GM				
01847999	SM294C LED40/840 PSU WP WH GM	(0.38, 0.38)	4000 K	105 lm/W	3800 lm
01848299	SM294C LED40/865 PSU WP WH GM	(0.31, 0.32)	6500 K	105 lm/W	3800 lm
01848399	SM294C LED40/830 PSU WP WH GM	(0.44, 0.40)	3000 K	105 lm/W	3800 lm
01848599	SM294C LED40/830 PSU WH GM	(0.44, 0.40)	3000 K	100 lm/W	3800 lm
01848699	SM294C LED40/840 PSU WH GM	(0.38, 0.38)	4000 K	100 lm/W	3800 lm
01848799	SM294C LED40/865 PSU WH GM	(0.31, 0.32)	6500 K	100 lm/W	3800 lm
01848899	SM295C LED70/840 PSU WH GM	(0.38, 0.38)	4000 K	100 lm/W	6600 lm
01510631	SM295C LED68/830 PSU WH	(0.44, 0.40)	3000 K	100 lm/W	6600 lm
01510731	SM295C LED68/840 PSU WH	(0.38, 0.38)	4000 K	100 lm/W	6600 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
01510831	SM295C LED68/865 PSU WH	(0.31, 0.32)	6500 K	100 lm/W	6600 lm
01510931	SM295C LED68/830 PSU BK	(0.44, 0.40)	3000 K	100 lm/W	6600 lm
01511031	SM295C LED68/840 PSU BK	(0.38, 0.38)	4000 K	100 lm/W	6600 lm
01511131	SM295C LED68/865 PSU BK	(0.31, 0.32)	6500 K	100 lm/W	6600 lm
01511831	SM295C LED68/830 PSU WP WH	(0.44, 0.40)	3000 K	100 lm/W	6600 lm
01511931	SM295C LED68/840 PSU WP WH	(0.38, 0.38)	4000 K	100 lm/W	6600 lm
01512031	SM295C LED68/865 PSU WP WH	(0.31, 0.32)	6500 K	100 lm/W	6600 lm
01512131	SM295C LED68/830 PSU WP BK	(0.44, 0.40)	3000 K	100 lm/W	6600 lm
01512231	SM295C LED68/840 PSU WP BK	(0.38, 0.38)	4000 K	100 lm/W	6600 lm
01512331	SM295C LED68/865 PSU WP BK	(0.31, 0.32)	6500 K	100 lm/W	6600 lm

### Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
01508831	SM291C LED10/830 PSU WH	10 W
01508931	SM291C LED10/840 PSU WH	10 W
01509031	SM291C LED10/865 PSU WH	10 W
01509131	SM291C LED10/830 PSU BK	10 W
01509231	SM291C LED10/840 PSU BK	10 W
01509331	SM291C LED10/865 PSU BK	10 W
01509431	SM293C LED20/830 PSU WH	19 W
01509531	SM293C LED20/840 PSU WH	19 W
01509631	SM293C LED20/865 PSU WH	19 W
01509731	SM293C LED20/830 PSU BK	19 W
01509831	SM293C LED20/840 PSU BK	19 W
01509931	SM293C LED20/865 PSU BK	19 W
01510031	SM294C LED40/830 PSU WH	36 W
01510131	SM294C LED40/840 PSU WH	36 W

Order Code	Full Product Name	Initial input power
01510231	SM294C LED40/865 PSU WH	36 W
01510331	SM294C LED40/830 PSU BK	36 W
01510431	SM294C LED40/840 PSU BK	36 W
01510531	SM294C LED40/865 PSU BK	36 W
01511231	SM294C LED40/830 PSU WP WH	36 W
01511331	SM294C LED40/840 PSU WP WH	36 W
01511431	SM294C LED40/865 PSU WP WH	36 W
01511531	SM294C LED40/830 PSU WP BK	36 W
01511631	SM294C LED40/840 PSU WP BK	36 W
01511731	SM294C LED40/865 PSU WP BK	36 W
01847199	SM291C LED10/830 PSU WH GM	10 W
01847299	SM291C LED10/840 PSU WH GM	10 W
01847399	SM291C LED10/865 PSU WH GM	10 W
01847499	SM293C LED20/830 PSU WH GM	19 W

## GreenSpace Surface-mounted

Order Code	Full Product Name	Initial input power
01847599	SM293C LED20/840 PSU WH GM	19 W
01847699	SM293C LED20/865 PSU WH GM	19 W
01847799	SM295C LED70/840 PSU WP WH GM	66 W
01847899	SM295C LED70/830 PSU WP WH GM	66 W
01847999	SM294C LED40/840 PSU WP WH GM	36 W
01848299	SM294C LED40/865 PSU WP WH GM	36 W
01848399	SM294C LED40/830 PSU WP WH GM	36 W
01848599	SM294C LED40/830 PSU WH GM	38 W
01848699	SM294C LED40/840 PSU WH GM	38 W
01848799	SM294C LED40/865 PSU WH GM	38 W
01848899	SM295C LED70/840 PSU WH GM	66 W
01510631	SM295C LED68/830 PSU WH	66 W

Order Code	Full Product Name	Initial input power
01510731	SM295C LED68/840 PSU WH	66 W
01510831	SM295C LED68/865 PSU WH	66 W
01510931	SM295C LED68/830 PSU BK	66 W
01511031	SM295C LED68/840 PSU BK	66 W
01511131	SM295C LED68/865 PSU BK	66 W
01511831	SM295C LED68/830 PSU WP WH	66 W
01511931	SM295C LED68/840 PSU WP WH	66 W
01512031	SM295C LED68/865 PSU WP WH	66 W
01512131	SM295C LED68/830 PSU WP BK	66 W
01512231	SM295C LED68/840 PSU WP BK	66 W
01512331	SM295C LED68/865 PSU WP BK	66 W

### Mechanical and Housing

Order Code	Full Product Name	Colour
01508831	SM291C LED10/830 PSU WH	White
01508931	SM291C LED10/840 PSU WH	White
01509031	SM291C LED10/865 PSU WH	White
01509131	SM291C LED10/830 PSU BK	black
01509231	SM291C LED10/840 PSU BK	black
01509331	SM291C LED10/865 PSU BK	black
01509431	SM293C LED20/830 PSU WH	White
01509531	SM293C LED20/840 PSU WH	White
01509631	SM293C LED20/865 PSU WH	White
01509731	SM293C LED20/830 PSU BK	black
01509831	SM293C LED20/840 PSU BK	black
01509931	SM293C LED20/865 PSU BK	black
01510031	SM294C LED40/830 PSU WH	White
01510131	SM294C LED40/840 PSU WH	White
01510231	SM294C LED40/865 PSU WH	White
01510331	SM294C LED40/830 PSU BK	black
01510431	SM294C LED40/840 PSU BK	black
01510531	SM294C LED40/865 PSU BK	black
01511231	SM294C LED40/830 PSU WP WH	White
01511331	SM294C LED40/840 PSU WP WH	White
01511431	SM294C LED40/865 PSU WP WH	White
01511531	SM294C LED40/830 PSU WP BK	black
01511631	SM294C LED40/840 PSU WP BK	black
01511731	SM294C LED40/865 PSU WP BK	black
01847199	SM291C LED10/830 PSU WH GM	White
01847299	SM291C LED10/840 PSU WH GM	White

Order Code	Full Product Name	Colour
01847399	SM291C LED10/865 PSU WH GM	White
01847499	SM293C LED20/830 PSU WH GM	White
01847599	SM293C LED20/840 PSU WH GM	White
01847699	SM293C LED20/865 PSU WH GM	White
01847799	SM295C LED70/840 PSU WP WH GM	White
01847899	SM295C LED70/830 PSU WP WH GM	White
01847999	SM294C LED40/840 PSU WP WH GM	White
01848299	SM294C LED40/865 PSU WP WH GM	White
01848399	SM294C LED40/830 PSU WP WH GM	White
01848599	SM294C LED40/830 PSU WH GM	White
01848699	SM294C LED40/840 PSU WH GM	White
01848799	SM294C LED40/865 PSU WH GM	White
01848899	SM295C LED70/840 PSU WH GM	White
01510631	SM295C LED68/830 PSU WH	White
01510731	SM295C LED68/840 PSU WH	White
01510831	SM295C LED68/865 PSU WH	White
01510931	SM295C LED68/830 PSU BK	black
01511031	SM295C LED68/840 PSU BK	black
01511131	SM295C LED68/865 PSU BK	black
01511831	SM295C LED68/830 PSU WP WH	White
01511931	SM295C LED68/840 PSU WP WH	White
01512031	SM295C LED68/865 PSU WP WH	White
01512131	SM295C LED68/830 PSU WP BK	black
01512231	SM295C LED68/840 PSU WP BK	black
01512331	SM295C LED68/865 PSU WP BK	black



## GreenSpace Surface-mounted

