



Creating attractive inner-city landscapes

OptiSpace

OptiSpace is a creative bollard solution which enables you to build a more attractive, citizen-centric inner-city space by avoiding verticalisation of the urban landscape. OptiSpace delivers all this and more while delivering an attractive TCO for your investment. Enabled by the different control options, you can reduce energy consumption and minimise TCO further. And thanks to the excellent and optimised light distribution options, you can maximise spacing between the bollards, thereby minimising the number of light points needed to be installed. To support different design schemes, OptiSpace is also available in different colours: Philips Ultra Dark Grey is the standard colour and other colours are available on request.

Benefits

- A discreet design, nicely blending into modern inner-city spaces
- Attractive Total Cost of Ownership
- Compliant with key national and international regulations in Europe

Features

- Enabling wide spacing, up to 20 metres
- Delivering up to 4,300 lm light output
- IP66 and IK10 ratings
- Warm White (WW)/Neutral White (NW) colour temperature options
- Choice of both asymmetric and symmetrical optics
- Ground section accessory

Application

- Parks and plazas
- Pedestrian and cycle paths
- Building facades and car parks

Specifications

Ambient Temperature	-40 to +50 °C
Main colour of the luminaire	Black
Initial correlated colour temperature	4000 K 3,000 K or 4,000 K
Initial input power	20 W, 37.2 W
Initial LED luminaire efficacy	167, 173 lm/W

Initial luminous flux	2390 lm, 4900 lm
Input frequency	50 to 60 Hz
Input voltage	220-240 V
Inrush current (A)	15, 22 A
Material	Housing: aluminum die-cast
Warranty period	5 years 5 years

Versions



OPTISPACE BOLLARD - LED module 2700 lm



OPTISPACE BOLLARD

Product details




OptiSpace-BCB500 -5DPP.TIF



OptiSpace-BCB500 -1DPP.TIF



OptiSpace-BCB500 -9DPP.TIF



OptiSpace-BCB500 -7DPP.TIF

Product details



OptiSpace-BCB500 -2DPP.TIF



OptiSpace-BCB500 -3DPP.TIF



OptiSpace-BCB500 -4DPP.TIF



OptiSpace-BCB500 -8DPP.TIF



OptiSpace-BCB500 -6DPP.TIF



OptiSpace-BCB500 -10DPP.TIF

Accessories



OPTISPACE BOLLARD ACC.

Ordercode 48144500

-	
Driver failure rate at 5000 h	0.5 %
Approval and Application	
Mech. impact protection code	IK10
Surge Protection (Common/Differential)	Luminaire surge protection level up to 6 kV differential mode and 6 kV common mode
Controls and Dimming	
Dimmable	No
General Information	
CE mark	CE mark
Light source colour	740 neutral white
Optical cover/lens type	PCC
Driver included	Yes
Flammability mark	F
Light source replaceable	Yes
Number of gear units	1 unit
Product Family Code	BCB500
Initial Performance (IEC Compliant)	
Init. Corr. Colour Temperature	4000 K
Init. Colour Rendering Index	>70
Light Technical	
Standard tilt angle side entry	0°
Standard tilt angle posttop	-
Upward light output ratio	0
Mechanical and Housing	
Colour	Black

General Information

Order Code	Full Product Name	Luminaire light beam spread	Lamp family code	Optic type
48118600	BCB500 LED56-4S/740 S DGR	177°	LED56	Symmetrical
48120900	BCB500 LED27-4S/740 ANB14 II A DGR	7° - 9° x 177°	LED27	Asymmetrical

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial luminous flux
48118600	BCB500 LED56-4S/740 S DGR	4900 lm



Order Code	Full Product Name	Initial luminous flux
48120900	BCB500 LED27-4S/740 ANB14 II A DGR	2390 lm

