



Elegant outlook design projector for the retail segment

Truefashion Projector GCGM

The Truefashion Projector is ideal for the retail segment with its attractive outlook design, excellent quality of light and dedicated light recipe, as well as system connectivity, to create a comfortable ambience and impressive shopping experience to stimulate the sales for retail customers.

Benefits

- A slim and compact outlook design with inside track driver.
- Excellent punch-effect light quality.
- Dedicated light recipe for fashion and food.
- System connectivity with Dali-VLC.

Features

- Lumen packages (1,000/2,000/3,000/4,000 lm).
- 3 beams options (NB/MB/WB).
- Dali-VLC Control.
- Track version available in 1C, 3C
- CB, EMC, CCC, ACC.
- Lifetime 50,000 hours.

Application

- Retail fashion outlets
- Shopping centre
- Food and large retail

Warnings and Safety

- 3 years

Truefashion Projector GCGM

Versions



Approval and Application

Mech. impact protection code	-
Ingress protection code	IP20

Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

General Information

CE mark	CE mark
Protection class IEC	Safety class II (II)

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Application Conditions

Truefashion Projector GCGM

Order Code	Full Product Name	Ambient temperature range	Maximum dimming level	Suitable for random switching
01518371	GD700B LED10 830 PSU MB WH	-15 to +35 °C	-	-
01518571	GD700B LED20 930PW PSU MB WH	-15 to +35 °C	-	-
01530571	GD700B LED20 940PW PSU MB WH HB	-15 to +35 °C	-	-
01518471	GD700B LED10 830 PSU MB BK	-15 to +35 °C	-	-
01518671	GD700B LED20 930PW PSU MB BK	-15 to +35 °C	-	-
01518771	GD700B 2XLED10 830 PSU MB WH	-15 to +35 °C	-	-
01518971	GD700B 2XLED20 930PW PSU MB WH	-15 to +35 °C	-	-
01518871	GD700B 2XLED10 830 PSU MB BK	-15 to +35 °C	-	-
01519071	GD700B 2XLED20 930PW PSU MB BK	-15 to +35 °C	-	-
01519471	RS700B LED10 830 PSU MB WH	-15 to +35 °C	-	-
01519571	RS700B LED10 830 PSU WB WH	-15 to +35 °C	-	-
01519771	RS700B LED20 930PW PSU NB WH	-15 to +35 °C	-	-
01519871	RS700B LED20 930PW PSU MB WH	-15 to +35 °C	-	-
01519971	RS700B LED20 930PW PSU WB WH	-15 to +35 °C	-	-
01520071	RS700B LED20 940PW PSU MB WH	-15 to +35 °C	-	-
01520571	RS700B LED20 930PC PSU MB WH	-15 to +35 °C	-	-
01522271	RS700B LED20 940PW PSU MB WH HB	-15 to +35 °C	-	-
01520171	RS700B LED20 930PW PSU NB BK	-15 to +35 °C	-	-
01520271	RS700B LED20 930PW PSU MB BK	-15 to +35 °C	-	-
01520371	RS700B LED20 930PW PSU WB BK	-15 to +35 °C	-	-
01520471	RS700B LED20 940PW PSU MB BK	-15 to +35 °C	-	-
01520671	RS700B LED30 930PW PSU NB WH	-15 to +35 °C	-	-
01520771	RS700B LED30 930PW PSU MB WH	-15 to +35 °C	-	-
01520871	RS700B LED30 930PW PSU WB WH	-15 to +35 °C	-	-

Order Code	Full Product Name	Ambient temperature range	Maximum dimming level	Suitable for random switching
01520971	RS700B LED30 940PW PSU MB WH	-15 to +35 °C	-	-
01521471	RS700B LED30 930PC PSU MB WH	-15 to +35 °C	-	-
01521571	RS700B LED40 930PW PSU MB WH	-15 to +35 °C	-	-
01521671	RS700B LED40 930PW PSU WB WH	-15 to +35 °C	-	-
01521771	RS700B LED40 940PW PSU MB WH	-15 to +35 °C	-	-
01522171	RS700B LED40 930PC PSU MB WH	-15 to +35 °C	-	-
01522371	RS700B LED40 940PW PSU MB WH HB	-15 to +35 °C	-	-
01522471	RS700B LED30 930PW PSD VLC NB WH	-15 to +35 °C	-	-
01522571	RS700B LED30 930PW PSD VLC MB WH	-15 to +35 °C	-	-
01522671	RS700B LED30 930PW PSD VLC WB WH	-15 to +35 °C	-	-
01521071	RS700B LED30 930PW PSU NB BK	-15 to +35 °C	-	-
01521171	RS700B LED30 930PW PSU MB BK	-15 to +35 °C	-	-
01521271	RS700B LED30 930PW PSU WB BK	-15 to +35 °C	-	-
01521371	RS700B LED30 940PW PSU MB BK	-15 to +35 °C	-	-
01521871	RS700B LED40 930PW PSU MB BK	-15 to +35 °C	-	-
01521971	RS700B LED40 930PW PSU WB BK	-15 to +35 °C	-	-
01522071	RS700B LED40 940PW PSU MB BK	-15 to +35 °C	-	-
01522771	RS700B LED30 930PW PSD VLC NB BK	-15 to +35 °C	-	-
01522871	RS700B LED30 930PW PSD VLC MB BK	-15 to +35 °C	-	-
01522971	RS700B LED30 930PW PSD VLC WB BK	-15 to +35 °C	-	-
01546661	ST700T LED20 930PC PSU NB 1C WH	-20 to +35 °C	Not applicable	No
01546761	ST700T LED20 930PC PSU MB 1C WH	-20 to +35 °C	Not applicable	No
01546861	ST700T LED20 930PC PSU WB 1C WH	-20 to +35 °C	Not applicable	No
01546961	ST700T LED20 930PC PSU NB 1C BK	-20 to +35 °C	Not applicable	No
01547061	ST700T LED20 930PC PSU MB 1C BK	-20 to +35 °C	Not applicable	No

Truefashion Projector GCGM

Order Code	Full Product Name	Ambient temperature range	Maximum dimming level	Suitable for random switching
01547161	ST700T LED20 930PC PSU WB 1C BK	-20 to +35 °C	Not applicable	No
01547261	ST700T LED30 930PC PSU MB 1C WH	-20 to +35 °C	Not applicable	No
01547361	ST700T LED30 930PC PSU WB 1C WH	-20 to +35 °C	Not applicable	No
01547461	ST700T LED30 930PC PSU MB 1C BK	-20 to +35 °C	Not applicable	No
01547561	ST700T LED30 930PC PSU WB 1C BK	-20 to +35 °C	Not applicable	No
01547661	ST700T LED40 930PC PSU MB 1C WH	-20 to +35 °C	Not applicable	No
01547761	ST700T LED40 930PC PSU WB 1C WH	-20 to +35 °C	Not applicable	No
01547861	ST700T LED40 930PC PSU MB 1C BK	-20 to +35 °C	Not applicable	No
01547961	ST700T LED40 930PC PSU WB 1C BK	-20 to +35 °C	Not applicable	No
01548061	ST700T LED20 930PC PSU MB 1C WH HB	-20 to +35 °C	Not applicable	No
01548161	ST700T LED20 930PC PSU MB 1C BK HB	-20 to +35 °C	Not applicable	No
01548261	ST700T LED40 930PC PSU MB 1C WH HB	-20 to +35 °C	Not applicable	No
01548361	ST700T LED40 930PC PSU MB 1C BK HB	-20 to +35 °C	Not applicable	No
01561661	ST700T LED10 830 PSU MB 1C WH	-20 to +35 °C	Not applicable	No
01561761	ST700T LED10 830 PSU WB 1C WH	-20 to +35 °C	Not applicable	No

Order Code	Full Product Name	Ambient temperature range	Maximum dimming level	Suitable for random switching
01561861	ST700T LED10 830 PSU MB 1C BK	-20 to +35 °C	Not applicable	No
01561961	ST700T LED10 830 PSU WB 1C BK	-20 to +35 °C	Not applicable	No
01562061	ST700T LED20 830 PSU NB 1C WH	-20 to +35 °C	Not applicable	No
01562161	ST700T LED20 830 PSU WB 1C WH	-20 to +35 °C	Not applicable	No
01562261	ST700T LED20 830 PSU NB 1C BK	-20 to +35 °C	Not applicable	No
01562361	ST700T LED20 830 PSU WB 1C BK	-20 to +35 °C	Not applicable	No
01575561	ST700T LED30 930PW PSU MB 3C BK	-20 to +35 °C	-	-
01575661	ST700T LED30 930PW PSU WB 3C BK	-20 to +35 °C	-	-
01575761	ST700T LED30 930PW PSU MB 3C WH	-20 to +35 °C	-	-
01575861	ST700T LED30 930PW PSU WB 3C WH	-20 to +35 °C	-	-
01575961	ST700T LED30 930PW PSD VLC MB BK	-20 to +35 °C	-	-
01576061	ST700T LED30 930PW PSD VLC WB BK	-20 to +35 °C	-	-
01576161	ST700T LED30 930PW PSD VLC MB WH	-20 to +35 °C	-	-
01576261	ST700T LED30 930PW PSD VLC WB WH	-20 to +35 °C	-	-

Controls and Dimming

Order Code	Full Product Name	Dimmable
01518371	GD700B LED10 830 PSU MB WH	No
01518571	GD700B LED20 930PW PSU MB WH	No
01530571	GD700B LED20 940PW PSU MB WH HB	No
01518471	GD700B LED10 830 PSU MB BK	No
01518671	GD700B LED20 930PW PSU MB BK	No
01518771	GD700B 2XLED10 830 PSU MB WH	No
01518971	GD700B 2XLED20 930PW PSU MB WH	No
01518871	GD700B 2XLED10 830 PSU MB BK	No
01519071	GD700B 2XLED20 930PW PSU MB BK	No
01519471	RS700B LED10 830 PSU MB WH	No
01519571	RS700B LED10 830 PSU WB WH	No
01519771	RS700B LED20 930PW PSU NB WH	No
01519871	RS700B LED20 930PW PSU MB WH	No
01519971	RS700B LED20 930PW PSU WB WH	No
01520071	RS700B LED20 940PW PSU MB WH	No
01520571	RS700B LED20 930PC PSU MB WH	No

Order Code	Full Product Name	Dimmable
01522271	RS700B LED20 940PW PSU MB WH HB	No
01520171	RS700B LED20 930PW PSU NB BK	No
01520271	RS700B LED20 930PW PSU MB BK	No
01520371	RS700B LED20 930PW PSU WB BK	No
01520471	RS700B LED20 940PW PSU MB BK	No
01520671	RS700B LED30 930PW PSU NB WH	No
01520771	RS700B LED30 930PW PSU MB WH	No
01520871	RS700B LED30 930PW PSU WB WH	No
01520971	RS700B LED30 940PW PSU MB WH	No
01521471	RS700B LED30 930PC PSU MB WH	No
01521571	RS700B LED40 930PW PSU MB WH	No
01521671	RS700B LED40 930PW PSU WB WH	No
01521771	RS700B LED40 940PW PSU MB WH	No
01522171	RS700B LED40 930PC PSU MB WH	No
01522371	RS700B LED40 940PW PSU MB WH HB	No
01522471	RS700B LED30 930PW PSD VLC NB WH	Yes

Truefashion Projector GCGM

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
01522571	RS700B LED30 930PW PSD VLC MB WH	Yes	01547761	ST700T LED40 930PC PSU WB 1C WH	No
01522671	RS700B LED30 930PW PSD VLC WB WH	Yes	01547861	ST700T LED40 930PC PSU MB 1C BK	No
01521071	RS700B LED30 930PW PSU NB BK	No	01547961	ST700T LED40 930PC PSU WB 1C BK	No
01521171	RS700B LED30 930PW PSU MB BK	No	01548061	ST700T LED20 930PC PSU MB 1C WH HB	No
01521271	RS700B LED30 930PW PSU WB BK	No	01548161	ST700T LED20 930PC PSU MB 1C BK HB	No
01521371	RS700B LED30 940PW PSU MB BK	No	01548261	ST700T LED40 930PC PSU MB 1C WH HB	No
01521871	RS700B LED40 930PW PSU MB BK	No	01548361	ST700T LED40 930PC PSU MB 1C BK HB	No
01521971	RS700B LED40 930PW PSU WB BK	No	01561661	ST700T LED10 830 PSU MB 1C WH	No
01522071	RS700B LED40 940PW PSU MB BK	No	01561761	ST700T LED10 830 PSU WB 1C WH	No
01522771	RS700B LED30 930PW PSD VLC NB BK	Yes	01561861	ST700T LED10 830 PSU MB 1C BK	No
01522871	RS700B LED30 930PW PSD VLC MB BK	Yes	01561961	ST700T LED10 830 PSU WB 1C BK	No
01522971	RS700B LED30 930PW PSD VLC WB BK	Yes	01562061	ST700T LED20 830 PSU NB 1C WH	No
01546661	ST700T LED20 930PC PSU NB 1C WH	No	01562161	ST700T LED20 830 PSU WB 1C WH	No
01546761	ST700T LED20 930PC PSU MB 1C WH	No	01562261	ST700T LED20 830 PSU NB 1C BK	No
01546861	ST700T LED20 930PC PSU WB 1C WH	No	01562361	ST700T LED20 830 PSU WB 1C BK	No
01546961	ST700T LED20 930PC PSU NB 1C BK	No	01575561	ST700T LED30 930PW PSU MB 3C BK	No
01547061	ST700T LED20 930PC PSU MB 1C BK	No	01575661	ST700T LED30 930PW PSU WB 3C BK	No
01547161	ST700T LED20 930PC PSU WB 1C BK	No	01575761	ST700T LED30 930PW PSU MB 3C WH	No
01547261	ST700T LED30 930PC PSU MB 1C WH	No	01575861	ST700T LED30 930PW PSU WB 3C WH	No
01547361	ST700T LED30 930PC PSU WB 1C WH	No	01575961	ST700T LED30 930PW PSD VLC MB BK	No
01547461	ST700T LED30 930PC PSU MB 1C BK	No	01576061	ST700T LED30 930PW PSD VLC WB BK	No
01547561	ST700T LED30 930PC PSU WB 1C BK	No	01576161	ST700T LED30 930PW PSD VLC MB WH	No
01547661	ST700T LED40 930PC PSU MB 1C WH	No	01576261	ST700T LED30 930PW PSD VLC WB WH	No

General Information

Order Code	Full Product Name	Beam angle of light source	Optical cover/lens type	Light source			Number of gear units	Optic type
				Driver included	ENEC mark	replaceable		
01518371	GD700B LED10 830 PSU MB WH	-	Lens	-	-	-	-	-
01518571	GD700B LED20 930PW PSU MB WH	-	Lens	-	-	-	-	-
01530571	GD700B LED20 940PW PSU MB WH HB	-	Lens	-	-	-	-	-
01518471	GD700B LED10 830 PSU MB BK	-	Lens	-	-	-	-	-
01518671	GD700B LED20 930PW PSU MB BK	-	Lens	-	-	-	-	-
01518771	GD700B 2XLED10 830 PSU MB WH	-	Lens	-	-	-	-	-
01518971	GD700B 2XLED20 930PW PSU MB WH	-	Lens	-	-	-	-	-
01518871	GD700B 2XLED10 830 PSU MB BK	-	Lens	-	-	-	-	-
01519071	GD700B 2XLED20 930PW PSU MB BK	-	Lens	-	-	-	-	-
01519471	RS700B LED10 830 PSU MB WH	-	Lens	-	-	-	-	-
01519571	RS700B LED10 830 PSU WB WH	-	Lens	-	-	-	-	-
01519771	RS700B LED20 930PW PSU NB WH	-	Lens	-	-	-	-	-
01519871	RS700B LED20 930PW PSU MB WH	-	Lens	-	-	-	-	-
01519971	RS700B LED20 930PW PSU WB WH	-	Lens	-	-	-	-	-
01520071	RS700B LED20 940PW PSU MB WH	-	Lens	-	-	-	-	-
01520571	RS700B LED20 930PC PSU MB WH	-	Lens	-	-	-	-	-
01522271	RS700B LED20 940PW PSU MB WH HB	-	Lens	-	-	-	-	-
01520171	RS700B LED20 930PW PSU NB BK	-	Lens	-	-	-	-	-
01520271	RS700B LED20 930PW PSU MB BK	-	Lens	-	-	-	-	-
01520371	RS700B LED20 930PW PSU WB BK	-	Lens	-	-	-	-	-
01520471	RS700B LED20 940PW PSU MB BK	-	Lens	-	-	-	-	-
01520671	RS700B LED30 930PW PSU NB WH	-	Lens	-	-	-	-	-
01520771	RS700B LED30 930PW PSU MB WH	-	Lens	-	-	-	-	-
01520871	RS700B LED30 930PW PSU WB WH	-	Lens	-	-	-	-	-

Truefashion Projector GCGM

Order Code	Full Product Name	Beam angle of light source	Optical cover/lens		Light source replaceable	Number of gear units	Optic type	
			type	Driver included				
01520971	RS700B LED30 940PW PSU MB WH	-	Lens	-	-	-	-	
01521471	RS700B LED30 930PC PSU MB WH	-	Lens	-	-	-	-	
01521571	RS700B LED40 930PW PSU MB WH	-	Lens	-	-	-	-	
01521671	RS700B LED40 930PW PSU WB WH	-	Lens	-	-	-	-	
01521771	RS700B LED40 940PW PSU MB WH	-	Lens	-	-	-	-	
01522171	RS700B LED40 930PC PSU MB WH	-	Lens	-	-	-	-	
01522371	RS700B LED40 940PW PSU MB WH HB	-	Lens	-	-	-	-	
01522471	RS700B LED30 930PW PSD VLC NB WH	-	Lens	-	-	-	-	
01522571	RS700B LED30 930PW PSD VLC MB WH	-	Lens	-	-	-	-	
01522671	RS700B LED30 930PW PSD VLC WB WH	-	Lens	-	-	-	-	
01521071	RS700B LED30 930PW PSU NB BK	-	Lens	-	-	-	-	
01521171	RS700B LED30 930PW PSU MB BK	-	Lens	-	-	-	-	
01521271	RS700B LED30 930PW PSU WB BK	-	Lens	-	-	-	-	
01521371	RS700B LED30 940PW PSU MB BK	-	Lens	-	-	-	-	
01521871	RS700B LED40 930PW PSU MB BK	-	Lens	-	-	-	-	
01521971	RS700B LED40 930PW PSU WB BK	-	Lens	-	-	-	-	
01522071	RS700B LED40 940PW PSU MB BK	-	Lens	-	-	-	-	
01522771	RS700B LED30 930PW PSD VLC NB BK	-	Lens	-	-	-	-	
01522871	RS700B LED30 930PW PSD VLC MB BK	-	Lens	-	-	-	-	
01522971	RS700B LED30 930PW PSD VLC WB BK	-	Lens	-	-	-	-	
01546661	ST700T LED20 930PC PSU NB 1C WH	120 °	Lens	Yes	-	No	1 unit	15
01546761	ST700T LED20 930PC PSU MB 1C WH	120 °	Lens	Yes	-	No	1 unit	24
01546861	ST700T LED20 930PC PSU WB 1C WH	120 °	Lens	Yes	-	No	1 unit	30
01546961	ST700T LED20 930PC PSU NB 1C BK	120 °	Lens	Yes	-	No	1 unit	15
01547061	ST700T LED20 930PC PSU MB 1C BK	120 °	Lens	Yes	-	No	1 unit	24
01547161	ST700T LED20 930PC PSU WB 1C BK	120 °	Lens	Yes	-	No	1 unit	30
01547261	ST700T LED30 930PC PSU MB 1C WH	120 °	Lens	Yes	-	No	1 unit	Beam angle 23°
01547361	ST700T LED30 930PC PSU WB 1C WH	120 °	Lens	Yes	-	No	1 unit	Beam angle 33°
01547461	ST700T LED30 930PC PSU MB 1C BK	120 °	Lens	Yes	-	No	1 unit	Beam angle 23°
01547561	ST700T LED30 930PC PSU WB 1C BK	120 °	Lens	Yes	-	No	1 unit	Beam angle 33°
01547661	ST700T LED40 930PC PSU MB 1C WH	120 °	Lens	Yes	-	No	1 unit	24
01547761	ST700T LED40 930PC PSU WB 1C WH	120 °	Lens	Yes	-	No	1 unit	Beam angle 34°
01547861	ST700T LED40 930PC PSU MB 1C BK	120 °	Lens	Yes	-	No	1 unit	24
01547961	ST700T LED40 930PC PSU WB 1C BK	120 °	Lens	Yes	-	No	1 unit	Beam angle 34°
01548061	ST700T LED20 930PC PSU MB 1C WH HB	120 °	Lens	Yes	-	No	1 unit	Beam angle 21°
01548161	ST700T LED20 930PC PSU MB 1C BK HB	120 °	Lens	Yes	-	No	1 unit	Beam angle 21°
01548261	ST700T LED40 930PC PSU MB 1C WH HB	120 °	Lens	Yes	-	No	1 unit	24
01548361	ST700T LED40 930PC PSU MB 1C BK HB	120 °	Lens	Yes	-	No	1 unit	24
01561661	ST700T LED10 830 PSU MB 1C WH	120 °	Lens	Yes	-	No	1 unit	24
01561761	ST700T LED10 830 PSU WB 1C WH	120 °	Lens	Yes	-	No	1 unit	30
01561861	ST700T LED10 830 PSU MB 1C BK	120 °	Lens	Yes	-	No	1 unit	24
01561961	ST700T LED10 830 PSU WB 1C BK	120 °	Lens	Yes	-	No	1 unit	30
01562061	ST700T LED20 830 PSU NB 1C WH	120 °	Lens	Yes	-	No	1 unit	15
01562161	ST700T LED20 830 PSU WB 1C WH	120 °	Lens	Yes	-	No	1 unit	30
01562261	ST700T LED20 830 PSU NB 1C BK	120 °	Lens	Yes	-	No	1 unit	15

Truefashion Projector GCGM

Order Code	Full Product Name	Beam angle of light source	Optical cover/lens type	Driver included	ENEC mark	Light source replaceable	Number of gear units	Optic type
01562361	ST700T LED20 830 PSU WB 1C BK	120 °	Lens	Yes	-	No	1 unit	30
01575561	ST700T LED30 930PW PSU MB 3C BK	-	Fashion proof optic beam angle 24°	-	-	-	-	-
01575661	ST700T LED30 930PW PSU WB 3C BK	-	Fashion proof optic beam angle 36°	-	-	-	-	-
01575761	ST700T LED30 930PW PSU MB 3C WH	-	Fashion proof optic beam angle 24°	-	-	-	-	-
01575861	ST700T LED30 930PW PSU WB 3C WH	-	Fashion proof optic beam angle 36°	-	-	-	-	-
01575961	ST700T LED30 930PW PSD VLC MB BK	-	Fashion proof optic beam angle 24°	-	-	-	-	-
01576061	ST700T LED30 930PW PSD VLC WB BK	-	Fashion proof optic beam angle 36°	-	-	-	-	-
01576161	ST700T LED30 930PW PSD VLC MB WH	-	Fashion proof optic beam angle 24°	-	-	-	-	-
01576261	ST700T LED30 930PW PSD VLC WB WH	-	Fashion proof optic beam angle 36°	-	-	-	-	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Init. Colour rendering index	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
01518371	GD700B LED10 830 PSU MB WH	-	3000 K	>80	114 lm/W	942 lm	8 W
01518571	GD700B LED20 930PW PSU MB WH	-	3000 K	>90	79 lm/W	1685 lm	21 W
01530571	GD700B LED20 940PW PSU MB WH HB	-	4000 K	>90	56 lm/W	1184 lm	21 W
01518471	GD700B LED10 830 PSU MB BK	-	3000 K	>80	114 lm/W	942 lm	8 W
01518671	GD700B LED20 930PW PSU MB BK	-	3000 K	>90	79 lm/W	1685 lm	21 W
01518771	GD700B 2XLED10 830 PSU MB WH	-	3000 K	>80	114 lm/W	1884 lm	16 W
01518971	GD700B 2XLED20 930PW PSU MB WH	-	3000 K	>90	79 lm/W	3369 lm	42 W
01518871	GD700B 2XLED10 830 PSU MB BK	-	3000 K	>80	114 lm/W	1884 lm	16 W
01519071	GD700B 2XLED20 930PW PSU MB BK	-	3000 K	>90	79 lm/W	3369 lm	42 W
01519471	RS700B LED10 830 PSU MB WH	-	3000 K	>80	114 lm/W	942 lm	8 W
01519571	RS700B LED10 830 PSU WB WH	-	3000 K	>80	108 lm/W	886 lm	8 W
01519771	RS700B LED20 930PW PSU NB WH	-	3000 K	>90	79 lm/W	1685 lm	21 W
01519871	RS700B LED20 930PW PSU MB WH	-	3000 K	>90	79 lm/W	1685 lm	21 W
01519971	RS700B LED20 930PW PSU WB WH	-	3000 K	>90	75 lm/W	1586 lm	21 W
01520071	RS700B LED20 940PW PSU MB WH	-	4000 K	>90	86 lm/W	1829 lm	21 W
01520571	RS700B LED20 930PC PSU MB WH	-	3000 K	>90	74 lm/W	1577 lm	21 W
01522271	RS700B LED20 940PW PSU MB WH HB	-	4000 K	>90	56 lm/W	1184 lm	21 W
01520171	RS700B LED20 930PW PSU NB BK	-	3000 K	>90	79 lm/W	1685 lm	21 W
01520271	RS700B LED20 930PW PSU MB BK	-	3000 K	>90	79 lm/W	1685 lm	21 W
01520371	RS700B LED20 930PW PSU WB BK	-	3000 K	>90	75 lm/W	1586 lm	21 W
01520471	RS700B LED20 940PW PSU MB BK	-	4000 K	>90	86 lm/W	1829 lm	21 W
01520671	RS700B LED30 930PW PSU NB WH	-	3000 K	>90	93 lm/W	2879 lm	31 W
01520771	RS700B LED30 930PW PSU MB WH	-	3000 K	>90	92 lm/W	2844 lm	31 W
01520871	RS700B LED30 930PW PSU WB WH	-	3000 K	>90	91 lm/W	2809 lm	31 W
01520971	RS700B LED30 940PW PSU MB WH	-	4000 K	>90	100 lm/W	3076 lm	31 W
01521471	RS700B LED30 930PC PSU MB WH	-	3000 K	>90	87 lm/W	2669 lm	31 W

Truefashion Projector GCGM

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour		Init. Colour rendering	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
			Temperature		index			
01521571	RS700B LED40 930PW PSU MB WH	-	3000 K		>90	93 lm/W	3737 lm	40 W
01521671	RS700B LED40 930PW PSU WB WH	-	3000 K		>90	89 lm/W	3596 lm	40 W
01521771	RS700B LED40 940PW PSU MB WH	-	4000 K		>90	100 lm/W	4025 lm	40 W
01522171	RS700B LED40 930PC PSU MB WH	-	3000 K		>90	85 lm/W	3429 lm	40 W
01522371	RS700B LED40 940PW PSU MB WH HB	-	4000 K		>90	57 lm/W	2293 lm	40 W
01522471	RS700B LED30 930PW PSD VLC NB WH	-	3000 K		>90	89 lm/W	3159 lm	35 W
01522571	RS700B LED30 930PW PSD VLC MB WH	-	3000 K		>90	88 lm/W	3120 lm	35 W
01522671	RS700B LED30 930PW PSD VLC WB WH	-	3000 K		>90	87 lm/W	3082 lm	35 W
01521071	RS700B LED30 930PW PSU NB BK	-	3000 K		>90	93 lm/W	2879 lm	31 W
01521171	RS700B LED30 930PW PSU MB BK	-	3000 K		>90	92 lm/W	2844 lm	31 W
01521271	RS700B LED30 930PW PSU WB BK	-	3000 K		>90	91 lm/W	2809 lm	31 W
01521371	RS700B LED30 940PW PSU MB BK	-	4000 K		>90	100 lm/W	3076 lm	31 W
01521871	RS700B LED40 930PW PSU MB BK	-	3000 K		>90	93 lm/W	3737 lm	40 W
01521971	RS700B LED40 930PW PSU WB BK	-	3000 K		>90	89 lm/W	3596 lm	40 W
01522071	RS700B LED40 940PW PSU MB BK	-	4000 K		>90	100 lm/W	4025 lm	40 W
01522771	RS700B LED30 930PW PSD VLC NB BK	-	3000 K		>90	89 lm/W	3159 lm	35 W
01522871	RS700B LED30 930PW PSD VLC MB BK	-	3000 K		>90	88 lm/W	3120 lm	35 W
01522971	RS700B LED30 930PW PSD VLC WB BK	-	3000 K		>90	87 lm/W	3082 lm	35 W
01546661	ST700T LED20 930PC PSU NB 1C WH SDCM<3	(0.422, 0.386)	3000 K		>90	72.1 lm/W	1604.8 lm	22.3 W
01546761	ST700T LED20 930PC PSU MB 1C WH SDCM<3	(0.422, 0.386)	3000 K		>90	72.1 lm/W	1604.8 lm	22.3 W
01546861	ST700T LED20 930PC PSU WB 1C WH SDCM<3	(0.422, 0.386)	3000 K		>90	67.9 lm/W	1510.4 lm	22.3 W
01546961	ST700T LED20 930PC PSU NB 1C BK SDCM<3	(0.422, 0.386)	3000 K		>90	72.1 lm/W	1604.8 lm	22.3 W
01547061	ST700T LED20 930PC PSU MB 1C BK SDCM<3	(0.422, 0.386)	3000 K		>90	72.1 lm/W	1604.8 lm	22.3 W
01547161	ST700T LED20 930PC PSU WB 1C BK SDCM<3	(0.422, 0.386)	3000 K		>90	67.9 lm/W	1510.4 lm	22.3 W
01547261	ST700T LED30 930PC PSU MB 1C WH SDCM<3	(0.422, 0.386)	3000 K		>90	70.5 lm/W	2684.72 lm	38.1 W
01547361	ST700T LED30 930PC PSU WB 1C WH SDCM<3	(0.422, 0.386)	3000 K		>90	67.6 lm/W	2575.9 lm	38.1 W
01547461	ST700T LED30 930PC PSU MB 1C BK SDCM<3	(0.422, 0.386)	3000 K		>90	70.5 lm/W	2684.72 lm	38.1 W
01547561	ST700T LED30 930PC PSU WB 1C BK SDCM<3	(0.422, 0.386)	3000 K		>90	67.6 lm/W	2575.88 lm	38.1 W
01547661	ST700T LED40 930PC PSU MB 1C WH SDCM<3	(0.422, 0.386)	3000 K		>90	75.3 lm/W	3299.16 lm	43.8 W
01547761	ST700T LED40 930PC PSU WB 1C WH SDCM<3	(0.422, 0.386)	3000 K		>90	71.4 lm/W	3125.52 lm	43.8 W

Truefashion Projector GCGM

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour		Init. Colour rendering		Initial luminous flux	Initial input power
			Temperature		index	Initial LED luminaire efficacy		
01547861	ST700T LED40 930PC PSU MB 1C BK	(0.422, 0.386)	3000 K		>90	75.3 lm/W	3299.16 lm	43.8 W
		SDCM<3						
01547961	ST700T LED40 930PC PSU WB 1C BK	(0.422, 0.386)	3000 K		>90	71.4 lm/W	3125.52 lm	43.8 W
		SDCM<3						
01548061	ST700T LED20 930PC PSU MB 1C WH	(0.422, 0.386)	3000 K		>90	46.7 lm/W	1038.4 lm	22.3 W
	HB	SDCM<3						
01548161	ST700T LED20 930PC PSU MB 1C BK	(0.422, 0.386)	3000 K		>90	46.7 lm/W	1038.4 lm	22.3 W
	HB	SDCM<3						
01548261	ST700T LED40 930PC PSU MB 1C WH	(0.422, 0.386)	3000 K		>80	44.6 lm/W	1953.45 lm	43.8 W
	HB	SDCM<3						
01548361	ST700T LED40 930PC PSU MB 1C BK	(0.422, 0.386)	3000 K		>80	44.6 lm/W	1953.45 lm	43.8 W
	HB	SDCM<3						
01561661	ST700T LED10 830 PSU MB 1C WH	(0.434, 0.403)	3000 K		>80	107.3 lm/W	1146.65 lm	10.7 W
		SDCM<3						
01561761	ST700T LED10 830 PSU WB 1C WH	(0.434, 0.403)	3000 K		>80	101 lm/W	1079.2 lm	10.7 W
		SDCM<3						
01561861	ST700T LED10 830 PSU MB 1C BK	(0.434, 0.403)	3000 K		>80	107.3 lm/W	1146.65 lm	10.7 W
		SDCM<3						
01561961	ST700T LED10 830 PSU WB 1C BK	(0.434, 0.403)	3000 K		>80	101 lm/W	1079.2 lm	10.7 W
		SDCM<3						
01562061	ST700T LED20 830 PSU NB 1C WH	(0.434, 0.403)	3000 K		>80	92.2 lm/W	2051.05 lm	22.3 W
		SDCM<3						
01562161	ST700T LED20 830 PSU WB 1C WH	(0.434, 0.403)	3000 K		>80	86.7 lm/W	1930.4 lm	22.3 W
		SDCM<3						
01562261	ST700T LED20 830 PSU NB 1C BK	(0.434, 0.403)	3000 K		>80	92.2 lm/W	2051.05 lm	22.3 W
		SDCM<3						
01562361	ST700T LED20 830 PSU WB 1C BK	(0.434, 0.403)	3000 K		>80	86.7 lm/W	1930.4 lm	22.3 W
		SDCM<3						
01575561	ST700T LED30 930PW PSU MB 3C BK	-	3000 K		>90	85.40831032215648 lm/W	3168.44 lm	37.1 W
01575661	ST700T LED30 930PW PSU WB 3C BK	-	3000 K		>90	80.91313609467456 lm/W	3001.68 lm	37.1 W
01575761	ST700T LED30 930PW PSU MB 3C WH	-	3000 K		>90	85.40831032215648 lm/W	3168.44 lm	37.1 W
01575861	ST700T LED30 930PW PSU WB 3C WH	-	3000 K		>90	80.91313609467456 lm/W	3001.68 lm	37.1 W
01575961	ST700T LED30 930PW PSD VLC MB	-	3000 K		>90	90.61613412228797 lm/W	3168.44 lm	35 W
	BK							
01576061	ST700T LED30 930PW PSD VLC WB	-	3000 K		>90	85.84686390532543 lm/W	3001.68 lm	35 W
	BK							
01576161	ST700T LED30 930PW PSD VLC MB	-	3000 K		>90	90.61613412228797 lm/W	3168.44 lm	35 W
	WH							
01576261	ST700T LED30 930PW PSD VLC WB	-	3000 K		>90	85.84686390532543 lm/W	3001.68 lm	35 W
	WH							

Mechanical and Housing

Order Code	Full Product Name	Colour	Order Code	Full Product Name	Colour
01518371	GD700B LED10 830 PSU MB WH	White RAL 9003	01518971	GD700B 2XLED20 930PW PSU MB WH	White RAL 9003
01518571	GD700B LED20 930PW PSU MB WH	White RAL 9003	01518871	GD700B 2XLED10 830 PSU MB BK	Black
01530571	GD700B LED20 940PW PSU MB WH HB	White RAL 9003	01519071	GD700B 2XLED20 930PW PSU MB BK	Black
01518471	GD700B LED10 830 PSU MB BK	Black	01519471	RS700B LED10 830 PSU MB WH	White RAL 9003
01518671	GD700B LED20 930PW PSU MB BK	Black	01519571	RS700B LED10 830 PSU WB WH	White RAL 9003
01518771	GD700B 2XLED10 830 PSU MB WH	White RAL 9003	01519771	RS700B LED20 930PW PSU NB WH	White RAL 9003

Truefashion Projector GCGM

Order Code	Full Product Name	Colour
01519871	RS700B LED20 930PW PSU MB WH	White RAL 9003
01519971	RS700B LED20 930PW PSU WB WH	White RAL 9003
01520071	RS700B LED20 940PW PSU MB WH	White RAL 9003
01520571	RS700B LED20 930PC PSU MB WH	White RAL 9003
01522271	RS700B LED20 940PW PSU MB WH HB	White RAL 9003
01520171	RS700B LED20 930PW PSU NB BK	Black
01520271	RS700B LED20 930PW PSU MB BK	Black
01520371	RS700B LED20 930PW PSU WB BK	Black
01520471	RS700B LED20 940PW PSU MB BK	Black
01520671	RS700B LED30 930PW PSU NB WH	White RAL 9003
01520771	RS700B LED30 930PW PSU MB WH	White RAL 9003
01520871	RS700B LED30 930PW PSU WB WH	White RAL 9003
01520971	RS700B LED30 940PW PSU MB WH	White RAL 9003
01521471	RS700B LED30 930PC PSU MB WH	White RAL 9003
01521571	RS700B LED40 930PW PSU MB WH	White RAL 9003
01521671	RS700B LED40 930PW PSU WB WH	White RAL 9003
01521771	RS700B LED40 940PW PSU MB WH	White RAL 9003
01522171	RS700B LED40 930PC PSU MB WH	White RAL 9003
01522371	RS700B LED40 940PW PSU MB WH HB	White RAL 9003
01522471	RS700B LED30 930PW PSD VLC NB WH	White RAL 9003
01522571	RS700B LED30 930PW PSD VLC MB WH	White RAL 9003
01522671	RS700B LED30 930PW PSD VLC WB WH	White RAL 9003
01521071	RS700B LED30 930PW PSU NB BK	Black
01521171	RS700B LED30 930PW PSU MB BK	Black
01521271	RS700B LED30 930PW PSU WB BK	Black
01521371	RS700B LED30 940PW PSU MB BK	Black
01521871	RS700B LED40 930PW PSU MB BK	Black
01521971	RS700B LED40 930PW PSU WB BK	Black
01522071	RS700B LED40 940PW PSU MB BK	Black
01522771	RS700B LED30 930PW PSD VLC NB BK	Black
01522871	RS700B LED30 930PW PSD VLC MB BK	Black
01522971	RS700B LED30 930PW PSD VLC WB BK	Black
01546661	ST700T LED20 930PC PSU NB 1C WH	White

Order Code	Full Product Name	Colour
01546761	ST700T LED20 930PC PSU MB 1C WH	White
01546861	ST700T LED20 930PC PSU WB 1C WH	White
01546961	ST700T LED20 930PC PSU NB 1C BK	Black
01547061	ST700T LED20 930PC PSU MB 1C BK	Black
01547161	ST700T LED20 930PC PSU WB 1C BK	Black
01547261	ST700T LED30 930PC PSU MB 1C WH	White
01547361	ST700T LED30 930PC PSU WB 1C WH	White
01547461	ST700T LED30 930PC PSU MB 1C BK	Black
01547561	ST700T LED30 930PC PSU WB 1C BK	Black
01547661	ST700T LED40 930PC PSU MB 1C WH	White
01547761	ST700T LED40 930PC PSU WB 1C WH	White
01547861	ST700T LED40 930PC PSU MB 1C BK	Black
01547961	ST700T LED40 930PC PSU WB 1C BK	Black
01548061	ST700T LED20 930PC PSU MB 1C WH HB	White
01548161	ST700T LED20 930PC PSU MB 1C BK HB	Black
01548261	ST700T LED40 930PC PSU MB 1C WH HB	White
01548361	ST700T LED40 930PC PSU MB 1C BK HB	Black
01561661	ST700T LED10 830 PSU MB 1C WH	White
01561761	ST700T LED10 830 PSU WB 1C WH	White
01561861	ST700T LED10 830 PSU MB 1C BK	Black
01561961	ST700T LED10 830 PSU WB 1C BK	Black
01562061	ST700T LED20 830 PSU NB 1C WH	White
01562161	ST700T LED20 830 PSU WB 1C WH	White
01562261	ST700T LED20 830 PSU NB 1C BK	Black
01562361	ST700T LED20 830 PSU WB 1C BK	Black
01575561	ST700T LED30 930PW PSU MB 3C BK	White and black
01575661	ST700T LED30 930PW PSU WB 3C BK	White and black
01575761	ST700T LED30 930PW PSU MB 3C WH	White and black
01575861	ST700T LED30 930PW PSU WB 3C WH	White and black
01575961	ST700T LED30 930PW PSD VLC MB BK	White and black
01576061	ST700T LED30 930PW PSD VLC WB BK	White and black
01576161	ST700T LED30 930PW PSD VLC MB WH	White and black
01576261	ST700T LED30 930PW PSD VLC WB WH	White and black

Order Code	Full Product Name	Driver failure rate at 5,000 hours
01518371	GD700B LED10 830 PSU MB WH	-
01518571	GD700B LED20 930PW PSU MB WH	-
01530571	GD700B LED20 940PW PSU MB WH HB	-
01518471	GD700B LED10 830 PSU MB BK	-
01518671	GD700B LED20 930PW PSU MB BK	-
01518771	GD700B 2XLED10 830 PSU MB WH	-
01518971	GD700B 2XLED20 930PW PSU MB WH	-
01518871	GD700B 2XLED10 830 PSU MB BK	-
01519071	GD700B 2XLED20 930PW PSU MB BK	-
01519471	RS700B LED10 830 PSU MB WH	-
01519571	RS700B LED10 830 PSU WB WH	-
01519771	RS700B LED20 930PW PSU NB WH	-
01519871	RS700B LED20 930PW PSU MB WH	-
01519971	RS700B LED20 930PW PSU WB WH	-

Order Code	Full Product Name	Driver failure rate at 5,000 hours
01520071	RS700B LED20 940PW PSU MB WH	-
01520571	RS700B LED20 930PC PSU MB WH	-
01522271	RS700B LED20 940PW PSU MB WH HB	-
01520171	RS700B LED20 930PW PSU NB BK	-
01520271	RS700B LED20 930PW PSU MB BK	-
01520371	RS700B LED20 930PW PSU WB BK	-
01520471	RS700B LED20 940PW PSU MB BK	-
01520671	RS700B LED30 930PW PSU NB WH	-
01520771	RS700B LED30 930PW PSU MB WH	-
01520871	RS700B LED30 930PW PSU WB WH	-
01520971	RS700B LED30 940PW PSU MB WH	-
01521471	RS700B LED30 930PC PSU MB WH	-
01521571	RS700B LED40 930PW PSU MB WH	-
01521671	RS700B LED40 930PW PSU WB WH	-

Truefashion Projector GCGM

Order Code	Full Product Name	Driver failure rate at 5,000 hours
01521771	RS700B LED40 940PW PSU MB WH	-
01522171	RS700B LED40 930PC PSU MB WH	-
01522371	RS700B LED40 940PW PSU MB WH HB	-
01522471	RS700B LED30 930PW PSD VLC NB WH	-
01522571	RS700B LED30 930PW PSD VLC MB WH	-
01522671	RS700B LED30 930PW PSD VLC WB WH	-
01521071	RS700B LED30 930PW PSU NB BK	-
01521171	RS700B LED30 930PW PSU MB BK	-
01521271	RS700B LED30 930PW PSU WB BK	-
01521371	RS700B LED30 940PW PSU MB BK	-
01521871	RS700B LED40 930PW PSU MB BK	-
01521971	RS700B LED40 930PW PSU WB BK	-
01522071	RS700B LED40 940PW PSU MB BK	-
01522771	RS700B LED30 930PW PSD VLC NB BK	-
01522871	RS700B LED30 930PW PSD VLC MB BK	-
01522971	RS700B LED30 930PW PSD VLC WB BK	-
01546661	ST700T LED20 930PC PSU NB 1C WH	0.14 %
01546761	ST700T LED20 930PC PSU MB 1C WH	0.14 %
01546861	ST700T LED20 930PC PSU WB 1C WH	0.14 %
01546961	ST700T LED20 930PC PSU NB 1C BK	0.14 %
01547061	ST700T LED20 930PC PSU MB 1C BK	0.14 %
01547161	ST700T LED20 930PC PSU WB 1C BK	0.14 %
01547261	ST700T LED30 930PC PSU MB 1C WH	0.14 %
01547361	ST700T LED30 930PC PSU WB 1C WH	0.14 %
01547461	ST700T LED30 930PC PSU MB 1C BK	0.14 %

Order Code	Full Product Name	Driver failure rate at 5,000 hours
01547561	ST700T LED30 930PC PSU WB 1C BK	0.14 %
01547661	ST700T LED40 930PC PSU MB 1C WH	0.23 %
01547761	ST700T LED40 930PC PSU WB 1C WH	0.23 %
01547861	ST700T LED40 930PC PSU MB 1C BK	0.23 %
01547961	ST700T LED40 930PC PSU WB 1C BK	0.23 %
01548061	ST700T LED20 930PC PSU MB 1C WH HB	0.14 %
01548161	ST700T LED20 930PC PSU MB 1C BK HB	0.14 %
01548261	ST700T LED40 930PC PSU MB 1C WH HB	0.23 %
01548361	ST700T LED40 930PC PSU MB 1C BK HB	0.23 %
01561661	ST700T LED10 830 PSU MB 1C WH	0.14 %
01561761	ST700T LED10 830 PSU WB 1C WH	0.14 %
01561861	ST700T LED10 830 PSU MB 1C BK	0.14 %
01561961	ST700T LED10 830 PSU WB 1C BK	0.14 %
01562061	ST700T LED20 830 PSU NB 1C WH	0.14 %
01562161	ST700T LED20 830 PSU WB 1C WH	0.14 %
01562261	ST700T LED20 830 PSU NB 1C BK	0.14 %
01562361	ST700T LED20 830 PSU WB 1C BK	0.14 %
01575561	ST700T LED30 930PW PSU MB 3C BK	-
01575661	ST700T LED30 930PW PSU WB 3C BK	-
01575761	ST700T LED30 930PW PSU MB 3C WH	-
01575861	ST700T LED30 930PW PSU WB 3C WH	-
01575961	ST700T LED30 930PW PSD VLC MB BK	-
01576061	ST700T LED30 930PW PSD VLC WB BK	-
01576161	ST700T LED30 930PW PSD VLC MB WH	-
01576261	ST700T LED30 930PW PSD VLC WB WH	-

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
01518371	GD700B LED10 830 PSU MB WH	-	-
01518571	GD700B LED20 930PW PSU MB WH	-	-
01530571	GD700B LED20 940PW PSU MB WH HB	-	-
01518471	GD700B LED10 830 PSU MB BK	-	-
01518671	GD700B LED20 930PW PSU MB BK	-	-
01518771	GD700B 2XLED10 830 PSU MB WH	-	-
01518971	GD700B 2XLED20 930PW PSU MB WH	-	-
01518871	GD700B 2XLED10 830 PSU MB BK	-	-
01519071	GD700B 2XLED20 930PW PSU MB BK	-	-
01519471	RS700B LED10 830 PSU MB WH	-	-
01519571	RS700B LED10 830 PSU WB WH	-	-
01519771	RS700B LED20 930PW PSU NB WH	-	-
01519871	RS700B LED20 930PW PSU MB WH	-	-
01519971	RS700B LED20 930PW PSU WB WH	-	-
01520071	RS700B LED20 940PW PSU MB WH	-	-
01520571	RS700B LED20 930PC PSU MB WH	-	-
01522271	RS700B LED20 940PW PSU MB WH HB	-	-
01520171	RS700B LED20 930PW PSU NB BK	-	-
01520271	RS700B LED20 930PW PSU MB BK	-	-
01520371	RS700B LED20 930PW PSU WB BK	-	-
01520471	RS700B LED20 940PW PSU MB BK	-	-

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
01520671	RS700B LED30 930PW PSU NB WH	-	-
01520771	RS700B LED30 930PW PSU MB WH	-	-
01520871	RS700B LED30 930PW PSU WB WH	-	-
01520971	RS700B LED30 940PW PSU MB WH	-	-
01521471	RS700B LED30 930PC PSU MB WH	-	-
01521571	RS700B LED40 930PW PSU MB WH	-	-
01521671	RS700B LED40 930PW PSU WB WH	-	-
01521771	RS700B LED40 940PW PSU MB WH	-	-
01522171	RS700B LED40 930PC PSU MB WH	-	-
01522371	RS700B LED40 940PW PSU MB WH HB	-	-
01522471	RS700B LED30 930PW PSD VLC NB WH	-	-
01522571	RS700B LED30 930PW PSD VLC MB WH	-	-
01522671	RS700B LED30 930PW PSD VLC WB WH	-	-
01521071	RS700B LED30 930PW PSU NB BK	-	-
01521171	RS700B LED30 930PW PSU MB BK	-	-
01521271	RS700B LED30 930PW PSU WB BK	-	-
01521371	RS700B LED30 940PW PSU MB BK	-	-
01521871	RS700B LED40 930PW PSU MB BK	-	-
01521971	RS700B LED40 930PW PSU WB BK	-	-
01522071	RS700B LED40 940PW PSU MB BK	-	-
01522771	RS700B LED30 930PW PSD VLC NB BK	-	-

Truefashion Projector GCGM

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
01522871	RS700B LED30 930PW PSD VLC MB BK	-	-
01522971	RS700B LED30 930PW PSD VLC WB BK	-	-
01546661	ST700T LED20 930PC PSU NB 1C WH	50000 h	32600 h
01546761	ST700T LED20 930PC PSU MB 1C WH	50000 h	32600 h
01546861	ST700T LED20 930PC PSU WB 1C WH	50000 h	32600 h
01546961	ST700T LED20 930PC PSU NB 1C BK	50000 h	32600 h
01547061	ST700T LED20 930PC PSU MB 1C BK	50000 h	32600 h
01547161	ST700T LED20 930PC PSU WB 1C BK	50000 h	32600 h
01547261	ST700T LED30 930PC PSU MB 1C WH	45000 h	21200 h
01547361	ST700T LED30 930PC PSU WB 1C WH	45000 h	21200 h
01547461	ST700T LED30 930PC PSU MB 1C BK	45000 h	21200 h
01547561	ST700T LED30 930PC PSU WB 1C BK	45000 h	21200 h
01547661	ST700T LED40 930PC PSU MB 1C WH	38700 h	18200 h
01547761	ST700T LED40 930PC PSU WB 1C WH	38700 h	18200 h
01547861	ST700T LED40 930PC PSU MB 1C BK	38700 h	18200 h
01547961	ST700T LED40 930PC PSU WB 1C BK	38700 h	18200 h
01548061	ST700T LED20 930PC PSU MB 1C WH HB	50000 h	32600 h
01548161	ST700T LED20 930PC PSU MB 1C BK HB	50000 h	32600 h

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
01548261	ST700T LED40 930PC PSU MB 1C WH HB	38700 h	18200 h
01548361	ST700T LED40 930PC PSU MB 1C BK HB	38700 h	18200 h
01561661	ST700T LED10 830 PSU MB 1C WH	50000 h	32600 h
01561761	ST700T LED10 830 PSU WB 1C WH	50000 h	32600 h
01561861	ST700T LED10 830 PSU MB 1C BK	50000 h	32600 h
01561961	ST700T LED10 830 PSU WB 1C BK	50000 h	32600 h
01562061	ST700T LED20 830 PSU NB 1C WH	50000 h	32600 h
01562161	ST700T LED20 830 PSU WB 1C WH	50000 h	32600 h
01562261	ST700T LED20 830 PSU NB 1C BK	50000 h	32600 h
01562361	ST700T LED20 830 PSU WB 1C BK	50000 h	32600 h
01575561	ST700T LED30 930PW PSU MB 3C BK	-	-
01575661	ST700T LED30 930PW PSU WB 3C BK	-	-
01575761	ST700T LED30 930PW PSU MB 3C WH	-	-
01575861	ST700T LED30 930PW PSU WB 3C WH	-	-
01575961	ST700T LED30 930PW PSD VLC MB BK	-	-
01576061	ST700T LED30 930PW PSD VLC WB BK	-	-
01576161	ST700T LED30 930PW PSD VLC MB WH	-	-
01576261	ST700T LED30 930PW PSD VLC WB WH	-	-

