



The Smartbright Waterproof Batten G3 provides flexibility to customers who can choose from three sizes, standard and through wiring versions, and two CCTs to cater for different customer needs

Smartbright Waterproof G3 WT0 68C

Philips Smartbright Waterproof G3 batten offers exceptional value. It is perfect for everyday lighting installations. Available in three standard sizes, it has the option of standard and through-wiring versions.

Smartbright Waterproof G3 WTO 68C

Benefits

- Lifetime: 30,000 hrs @ L70B50, 3-year warranty
- IP66, IK06
- Quick connector for easy installation

Features

- 2 colour temperatures, 3 sizes and standard and through-wiring version
- IP66/IK06 – Water and dustproof. For all weather
- Reliable with a long service life of 30,000 hours L70
- 3-year warranty
- Quick connector for easy installation

Application

- Parking Garages
- Offices

Versions



Smartbright Waterproof G3 WTO 68C

Application Conditions

Ambient temperature range -20 to +45 °C

Approval and Application

Mech. impact protection code IK06

Ingress protection code IP66

Controls and Dimming

Dimmable No

Operating and Electrical

Input Voltage 220 to 240 V

General Information

CE mark CE mark

Protection class IEC Safety class II (II)

Optical cover/lens type No

Initial Performance (IEC Compliant)

Init. Colour rendering index >80

Initial LED luminaire efficacy 110 lm/W

Luminous flux tolerance +/-10%

Mechanical and Housing

Colour White and grey

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux	Initial input power
36059199	WT068C CW LED18 L600 PSU	6500 K	1800 lm	16.5 W
36062199	WT068C NW LED18 L600 PSU	4000 K	1800 lm	16.5 W
36065299	WT068C CW LED18 L600 PSU TW1	6500 K	1800 lm	16.5 W
36068399	WT068C NW LED18 L600 PSU TW1	4000 K	1800 lm	16.5 W
36060799	WT068C CW LED36 L1200 PSU	6500 K	3600 lm	33 W
36063899	WT068C NW LED36 L1200 PSU	4000 K	3600 lm	33 W
36066999	WT068C CW LED36 L1200 PSU TW1	6500 K	3600 lm	33 W
36069099	WT068C NW LED36 L1200 PSU TW1	4000 K	3600 lm	33 W
36061499	WT068C CW LED56 L1500 PSU	6500 K	5600 lm	51 W
36064599	WT068C NW LED56 L1500 PSU	4000 K	5600 lm	51 W
36067699	WT068C CW LED56 L1500 PSU TW1	6500 K	5600 lm	51 W
36070699	WT068C NW LED56 L1500 PSU TW1	4000 K	5600 lm	51 W

