



# CityCharm Cordoba

## BDS490 CG25-/730 II A GR D11 76

CityCharm Cordoba, 15, LED module, system flux 2500 lm, LED, 730 warm white, Power supply unit regulating, 220 to 240 V, 50 to 60 Hz, Safety class II, Asymmetrical, Polycarbonate bowl/cover, Gray, Luminaire surge protection level until 6 kV differential mode and 8 kV common mode, Cable 0.2 m without plug, Spigot for diameter 76 mm

CityCharm Cordoba is designed for use in urban areas where comfortable lighting, ambiance and design play an important role. Its unobtrusive appearance makes it a timeless, future-proof luminaire that is ideal for residential areas, parks, footpaths and cycle lanes, where visual comfort and maximum efficiency are key. CityCharm offers a choice of two iconic designs (Cordoba and Cone) and various accessories, enabling you to create a lighting solution that carries your signature, both by day and by night. CityCharm luminaires are also available as a complete set, with a choice of dedicated poles and brackets.

### Product data

General Information			
Lamp family code	CG25 [LED module, system flux 2500 lm]	Product family code	BDS490 [CityCharm Cordoba]
Light source replaceable	Yes	Lighting Technology	LED
Number of gear units	1 unit	Value ladder	Performance
Gear	EB [Electronic]	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components	Flammability mark	-
Light source engine type	LED	ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 5 s
		EU RoHS compliant	Yes

Light Technical	
Upward light output ratio	0.03
Luminous Flux	2,117 lumen
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	96 lm/W
Color rendering index (CRI)	≥70
Number of light sources	15
Light source color	730 warm white
Optical cover/lens type	Polycarbonate bowl/cover
Luminaire light beam spread	360°
Optic type outdoor	Asymmetrical

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	27 A
Inrush time	15 ms
Power Consumption	22 W
Power Factor (Fraction)	0.848
Connection	Flying leads/wires
Cable	Cable 0.2 m without plug
Number of products on MCB of 16 A type B	32

Temperature	
Ambient temperature range	-40 to +50 °C

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit regulating
Control interface	-
Constant light output	No

Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Aluminum
Housing Color	Gray
Mounting device	Spigot for diameter 76 mm
Optical cover/lens shape	Flat

Optical cover/lens finish	Clear
Overall height	529 mm
Overall diameter	556 mm
Effective projected area	0.1124 m²

Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

Initial Performance (IEC Compliant)	
Initial chromaticity	(0.430, 0.400) SDCM <3
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.05 %
Lumen maintenance at median useful life*	L93
100000 h	

Application Conditions	
Maximum dim level	Not applicable
Performance ambient temperature Tq	25 °C

Product Data	
Full product code	871869693920800
Order product name	BDS490 CG25-/730 II A GR D11 76
Order code	93920800
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910505017425
Full product name	BDS490 CG25-/730 II A GR D11 76
EAN/UPC - Case	8718696939208
EAN/UPC - Product/Case	8718696939208

# CityCharm Cordoba

## Dimensional drawing

