



PowerBalance gen2

RC461B LED40S/940 PSD W60L60 VPC W AIR

PowerBalance recessed, Generation 2, LED module, system flux 4000 lm, 940 neutral white, Power supply unit with DALI interface, Plug-in connector 3-pole Wieland/Adels compatible

When it comes to lighting an office space with LED luminaires, people are usually willing to invest in sustainability provided the investment pays back. At the same time, the system should comply with office lighting norms to ensure a comfortable working environment. PowerBalance gen2 is Philips' most energy-efficient office-norm-compliant LED luminaire. It more than halves energy costs compared to a T5 solution, and the light source has a longer lifetime. This results in significantly lower operational costs, ensuring a payback that meets the needs of the specification market. The gen2 architecture enables a range of highly versatile modular and semi-modular luminaires. These luminaires can be easily mounted in ceilings with exposed T-bar and concealed T-bar, as well as plaster ceilings and bandraaster-type ceilings. PowerBalance is also available in a surface-mounted version.

Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore we strongly recommend that the environment in which the luminaire is to be installed should be suitably checked
- If the advice above is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void

Product data

General Information			
Lamp family code	LED40S [LED module, system flux 4000 lm]	Gear	-
Light source replaceable	No	Driver included	Yes
Number of gear units	1 unit	Service tag	Yes
		Product family code	RC461B [PowerBalance recessed]
		Lighting Technology	LED

PowerBalance gen2

Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes

Light Technical

Luminous Flux	4,000 lumen
Saturated Red (R9)	>50
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	143 lm/W
Color rendering index (CRI)	≥90
Flickering value (PstLM)	1
Stroboscopic effect value (SVM)	0.4
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	940 neutral white
Optic type	Wide beam office compliant
Optical cover/lens type	Polycarbonate bowl/cover
Luminaire light beam spread	86°
Unified glare rating CEN	16

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	19.4 A
Inrush time	0.230 ms
Power Consumption	28 W
Power Factor (Fraction)	0.9
Connection	Plug-in connector 3-pole Wieland/Adels compatible
Cable	-
Number of products on MCB of 16 A type B	30

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Steel
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate

Fixation material	-
Housing Color	White RAL 9003
Optical cover/lens finish	Matte
Overall length	597 mm
Overall width	597 mm
Overall height	86 mm
Dimensions (Height x Width x Depth)	86 x 597 x 597 mm

Approval and Application

Ingress protection code	IP20/40 [Finger-protected, Emitting surface]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	Lighting for circularity Lighting for wellbeing
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 5 %	
50000 h	
Lumen maintenance at median useful life*	L90
50000 h	
Lumen maintenance at median useful life*	L75
100000 h	

Application Conditions

Maximum dim level	1%
Performance ambient temperature Tq	25 °C
Suitable for random switching	No

Product Data

Full product code	871869996472600
Order product name	RC461B LED40S/940 PSD W60L60 VPC W AIR
Order code	96472600
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910505100266
Full product name	RC461B LED40S/940 PSD W60L60 VPC W AIR
EAN/UPC - Case	8718699964726
EAN/UPC - Product/Case	8718699964726

PowerBalance gen2

Dimensional drawing

