



# Maxos LED Performer

## 4MX900 491 LED40S/830 PSU WB WH

Maxos LED Performer - 1 unit for TL5 49 W - LED module, system flux 4000 lm - 830 warm white - Power supply unit - Wide beam - White

Customers want to save energy and reduce cost compared to what they are used to with conventional lighting. At the same time, excellent lighting conditions are needed: in industrial environments, to guarantee safety and productivity; and in retail environments, to make the merchandise stand out and attract shoppers. Maxos LED Performer is an extremely flexible solution that delivers low energy consumption and excellent beam shaping at an attractive investment level.

### Product data

General Information		Flammability mark	NO [-]
Number of light sources	1 [ 1 pc]	CE mark	CE mark
Lamp family code	LED40S [ LED module, system flux 4000 lm]	ENEC mark	ENEC mark
Beam angle of light source	120 °	Warranty period	5 years
Light source colour	830 warm white	Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Light source replaceable	No	Constant light output	No
Number of gear units	1 unit	Number of products on MCB (16 A type B)	24
Driver/power unit/transformer	PSU [ Power supply unit]	EU RoHS compliant	Yes
Driver included	Yes	Product family code	4MX900 [ Maxos LED Performer]
Optic type	WB [ Wide beam]		
Luminaire light beam spread	90°		
Emergency lighting	No [-]		
Connection	CU3 [ Connection unit 3-pole]		
Cable	-		
Protection class IEC	Safety class I (I)		
Glow-wire test	650/30 [ Temperature 650 °C, duration 30 s]		

# Maxos LED Performer

Unified glare rating CEN	Not applicable
<b>Operating and Electrical</b>	
Input Voltage	220 to 240 V
Input frequency	50 to 60 Hz
Control signal voltage	0-16 V DC DALI
Inrush current	17.8 A
Inrush time	0.282 ms
Power factor (min.)	0.9
<b>Controls and Dimming</b>	
Dimmable	No
<b>Mechanical and Housing</b>	
Trunking length	491 [ 1 unit for TL5 49 W]
Housing material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Steel
Optical cover/lens finish	Clear
Overall length	1479 mm
Overall width	87 mm
Overall height	82 mm
Colour	White
Dimensions (height x width x depth)	82 x 87 x 1479 mm (3.2 x 3.4 x 58.2 in)
<b>Approval and Application</b>	
Ingress protection code	IP40 [ Wire-protected]
Mech. impact protection code	IK02 [ 0.2 J standard]
<b>Initial Performance (IEC Compliant)</b>	
Initial luminous flux (system flux)	4000 lm

Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	125 lm/W
Init. Corr. Colour Temperature	3000 K
Init. Colour rendering index	≥80
Initial chromaticity	(0.43, 0.40) SDCM <3.5
Initial input power	32 W
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

## Application Conditions

Ambient temperature range	-20 to +40 °C
Performance ambient temperature Tq	25 °C
Suitable for random switching	Not applicable

## Product Data

Full product code	403073266496299
Order product name	4MX900 491 LED40S/830 PSU WB WH
EAN/UPC – product	4030732664962
Order code	66496299
SAP numerator – quantity per pack	1
Numerator – packs per outer box	2
SAP material	910629142426
SAP net weight (piece)	2.345 kg



## Dimensional drawing

953


Maxos LED Performer 4MX900-933

# Maxos LED Performer

## Photometric data

4MX900 G3 491 1xLED40S/830 PSU WB

1 x 4000 lm




LVS113250

2015-01-28

IFGU\_4MX900 G3 491 1xLED40S/830 PSU WB-General uniform lighting

4MX900 G3 491 1xLED40S/830 PSU WB

1 x 4000 lm



LVS113250

2015-01-28

IFPC\_4MX900 G3 491 1xLED40S/830 PSU WB-Polar Indoor (combined)

