



Maxos TL5 standard trunking

4MX656 493 5x2.5 SI

MAXOS TST5 - 3 units for TL5 49 W - 5 conductors cross-section 2.5 mm² - Silver

The trunking fulfils two functions: first, it provides a sturdy in-line mounting rail on which to fix the electrical units, and second, it provides a housing for the electrical cables that bring power to the units. All the light-line sections are made of hot-dip galvanized steel with a white or silver finish. They are available in dedicated TL5 lengths of 1, 2 and 3 electrical units 49 W (35/80 W) and 54 W (28 W). A flat ribbon cable (5 or 7 wires) or two flat ribbon cables (2 x 5 or 2 x 7 wires) are integrated in the trunking and guarantee (in combination with an integrated phase selection switch and contact blocks) safe and correct cabling. The 7-wire cable is used to integrate light regulation or emergency lighting for those electrical units that are equipped with emergency battery packs. Double wiring (2 x 5 or 2 x 7 wires) is needed to provide a completely separate mains supply to the electrical units. Double wiring is mostly used for emergency lighting by central emergency batteries or separate switching. Hence, no extra contact blocks or wiring are required. For suspended light lines, the light-line sections are connected using the integrated electrical connector and a sturdy external mechanical coupling piece (accessory). Surface-mounted light lines use the same integrated electrical connector and an internal coupler (accessory). On the upper part of the light-line section, special knock-out openings enable cable entry wherever needed. The trunking is available with a complete range of interchangeable components that optimize flexibility. The outstanding stability of the sections and coupling pieces allows suspension intervals of 3.4 to 5 m. The basic accessories of Maxos TL-D trunkings can also be used for the TL5 trunkings.

Product data

Maxos TL5 standard trunking

General Information

| | |
|----------------------|--|
| Spacing module | No [-] |
| Protection class IEC | Safety class I (I) |
| Flammability mark | F [For mounting on normally flammable surfaces] |
| ENEC mark | ENEC mark |
| Product family code | 4MX656 [MAXOS TST5] |

Operating and Electrical

| | |
|----------------|---|
| Circuit | No [-] |
| Circuit option | 5x2.5 [5 conductors cross-section 2.5 mm²] |

Mechanical and Housing

| | |
|-------------------------------------|--|
| Trunking length | 493 [3 units for TL5 49 W] |
| Overall length | 4437 mm |
| Colour | Silver |
| Dimensions (height x width x depth) | NaN x NaN x 4437 mm (NaN x NaN x 174.7 in) |

Approval and Application


| | |
|-------------------------|--------------------------|
| Ingress protection code | IP20 [Finger-protected] |
|-------------------------|--------------------------|

Product Data

| | |
|-----------------------------------|---------------------|
| Full product code | 403073258390499 |
| Order product name | 4MX656 493 5x2.5 SI |
| EAN/UPC – product | 4030732583904 |
| Order code | 58390499 |
| SAP numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 2 |
| SAP material | 910635117326 |
| SAP net weight (piece) | 6.170 kg |



Dimensional drawing



Maxos trunking 4MX056/856

