



# DigiStreet

## BGP762 LED210-/740 II DX70 DGR 76

DigiStreet Medium - LED module 21000 lm - 740 neutral white - Safety class II (II) - Distribution extra-wide 70 - Dark gray - Luminaire surge protection level up to 6 kV differential mode and 8 kV common mode - Spigot for diameter 76 mm

Developed with the aim of becoming your long-term partner, the system-ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come! Its two sockets enable you to connect directly to the Philips CityTouch system and it is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Philips Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain optimal ecosystems for bats or 2) preserve a dark night sky.

### Product data

General information		Connection	SCREW [ Screw connector]
Lamp family code	LED210 [ LED module 21000 lm]	Cable	-
Light source colour	740 neutral white	Protection class IEC	Safety class II (II)
Light source replaceable	Yes	Flammability mark	NO [ -]
Number of gear units	1 unit	CE mark	Yes
Driver/power unit/transformer	PSU [ Power supply unit]	ENEC mark	ENEC mark
Driver included	Yes	Warranty period	5 years
Optical cover/lens type	FG [ Flat glass]	Optic type outdoor	Distribution extra-wide 70
Luminaire light beam spread	106° x 86°		
Control interface	-		

Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Constant light output	No
Number of products on MCB (16 A type B)	8
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Light source engine type	LED
Serviceability class	Class A, the luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge-protection device, optics, front cover and mechanical parts
Product family code	BGP762 [ DigiStreet Medium]

## Light technical

Upward light output ratio	0
Standard tilt angle post-top	0°
Standard tilt angle side entry	0°

## Operating and electrical

Input Voltage	220-240 V
Input frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power factor (min.)	0.99

## Controls and dimming

Dimmable	Yes
----------	-----

## Mechanical and housing

Housing material	Aluminum die-cast
Reflector material	Polycarbonate
Optic material	Acrylate
Optical cover/lens material	Glass
Fixation material	Stainless steel
Mounting device	76 [ Spigot for diameter 76 mm]
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	860 mm
Overall width	361 mm
Overall height	107 mm
Effective projected area	0.068 m <sup>2</sup>
Colour	Dark gray

Dimensions (height x width x depth)	107 x 361 x 860 mm
-------------------------------------	--------------------

## Approval and application

Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [ 10 J]
Surge protection (common/differential)	Luminaire surge protection level up to 6 kV differential mode and 8 kV common mode
Sustainability rating	-

## Initial performance (IEC compliant)

Initial luminous flux (system flux)	18060 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	146 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	70
Initial chromaticity	(0.38, 0.38) SDCM <5
Initial input power	124 W
Power consumption tolerance	+/-10%
Init. colour rendering index tolerance	+/-2

## Over time performance (IEC compliant)


Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L96

## Application conditions


Ambient temperature range	-40 to +50 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	Not applicable

## Product data

Full product code	871869637837300
Order product name	BGP762 LED210-/740 II DX70 DGR 76
EAN/UPC – product	8718696378373
Order code	37837300
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910925866246
Net Weight (Piece)	9.160 kg




Dimensional drawing



BGP762 LED210-/740 II DX70 DGR 76

Photometric data



OFPC1\_BGP762T251xLED210-4S740DX70

