



DigiStreet

BGP763 LED340-/740 II DW10 DGR SRG10 62

DigiStreet Large - LED module 34000 lm - 740 neutral white - Safety class II (II) - Distribution wide 10 - Dark gray - Surge protection level until 10 kV - Spigot for diameter 62 mm

Developed with the aim of becoming your long-term partner, the system-ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come! Its two sockets enable you to connect directly to the Philips CityTouch system and it is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Philips Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain optimal ecosystems for bats or 2) preserve a dark night sky.

Product data

General Information		Cable	-
Lamp family code	LED340 [LED module 34000 lm]	Protection class IEC	Safety class II (II)
Light source colour	740 neutral white	Flammability mark	NO [-]
Light source replaceable	Yes	CE mark	CE mark
Number of gear units	2 units	ENEC mark	ENEC mark
Driver/power unit/transformer	PSU [Power supply unit]	Warranty period	5 years
Driver included	Yes	Optic type outdoor	Distribution wide 10
Optical cover/lens type	FG [Flat glass]	Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Luminaire light beam spread	-	Constant light output	No
Control interface	-		
Connection	SI [Screw connection block]		

Number of products on MCB (16 A type B)	4
EU RoHS compliant	Yes
Light source engine type	LED
Serviceability class	Class A, the luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge-protection device, optics, front cover and mechanical parts
Product family code	BGP763 [DigiStreet Large]

Light Technical

Upward light output ratio	0
Standard tilt angle post-top	0°
Standard tilt angle side entry	0°

Operating and Electrical

Input Voltage	220-240 V
Input frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power factor (min.)	0.99

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing material	Aluminum die-cast
Reflector material	Polycarbonate
Optic material	Acrylate
Optical cover/lens material	Glass
Fixation material	Stainless steel
Mounting device	62 [Spigot for diameter 62 mm]
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	1011 mm
Overall width	361 mm
Overall height	121 mm
Effective projected area	0.08 m ²
Colour	Dark gray
Dimensions (height x width x depth)	121 x 361 x 1011 mm (4.8 x 14.2 x 39.8 in)

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge protection (common/differential)	Surge protection level until 10 kV

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	29580 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	148 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	70
Initial chromaticity	(0.38. 0.38) SDCM <5
Initial input power	200 W
Power consumption tolerance	+/-10%
Init. colour rendering index tolerance	+/-2

Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L95

Application Conditions


Ambient temperature range	-40 to +50 °C
Maximum dimming level	Not applicable

Product Data

Full product code	871869637844100
Order product name	BGP763 LED340-/740 II DW10 DGR SRG10 62
EAN/UPC – product	8718696378441
Order code	37844100
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910925866251
SAP net weight (piece)	12.100 kg




Dimensional drawing



DigiStreet BGP760-BTP764

Photometric data



OFPC1_BGP763T251xLED340-4S740DW10

