



DigiStreet

BGP763 LED340-/740 II DW10 DGR SRG10 62

DigiStreet Large, LED module 34000 lm, 740 neutral white, Safety class II, Distribution wide 10, Dark gray, Luminaire surge protection level until 10 kV differential mode and 10 kV common mode, Spigot for diameter 62 mm

Developed with the aim of becoming your long-term partner, the system-ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come! Its two sockets enable you to connect directly to the Philips CityTouch system and it is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Philips Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain optimal ecosystems for bats or 2) preserve a dark night sky.

Product data

General Information		Lighting Technology	LED
Lamp family code	LED340 [LED module 34000 lm]	Value ladder	Specification
Light source replaceable	Yes	CE mark	Yes
Number of gear units	2 units	Warranty period	5 years
Driver included	Yes	Flammability mark	-
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components	ENEC mark	ENEC mark
Light source engine type	LED	EU RoHS compliant	Yes
Product family code	BGP763 [DigiStreet Large]	Light Technical	
		Upward light output ratio	0

Luminous Flux	29,580 lumen
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	148 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover/lens type	Flat glass
Luminaire light beam spread	61° x 150°
Optic type outdoor	Distribution wide 10

Operating and Electrical

Line Frequency	50 to 60 Hz
Input Voltage	220-240 V
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	200 W
Power Factor (Fraction)	0.99
Connection	Screw connector
Cable	-
Number of products on MCB of 16 A type B	4

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Acrylate
Optical cover/lens material	Glass
Fixation material	Stainless steel
Housing Color	Dark gray
Mounting device	Spigot for diameter 62 mm
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	1,011 mm
Overall width	361 mm
Overall height	121 mm
Effective projected area	0.08 m²

Dimensions (Height x Width x Depth)	121 x 361 x 1011 mm
-------------------------------------	---------------------

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <5
Luminous flux tolerance	+/-7%
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L95

Application Conditions

Maximum dim level	Not applicable
Performance ambient temperature Tq	25 °C

Product Data

Full product code	871869637844100
Order product name	BGP763 LED340-/740 II DW10 DGR SRG10 62
Order code	37844100
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910925866251
Full product name	BGP763 LED340-/740 II DW10 DGR SRG10 62
EAN/UPC - Case	8718696378441
EAN/UPC - Product/Case	8718696378441

Dimensional drawing

