



DigiStreet

BGP762 LED220-/740 II DW10 DGR SRG10 62

DigiStreet Medium, LED module 22000 lm, 740 neutral white, Safety class II, Distribution wide 10, Dark gray, Luminaire surge protection level until 10 kV differential mode and 10 kV common mode, Spigot for diameter 62 mm

Developed with the aim of becoming your long-term partner, the system-ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come! Its two sockets enable you to connect directly to the Philips CityTouch system and it is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Philips Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain optimal ecosystems for bats or 2) preserve a dark night sky.

Product data

| General Information | |
|--------------------------|--|
| Lamp family code | LED220 [LED module 22000 lm] |
| Light source replaceable | Yes |
| Number of gear units | 1 unit |
| Driver included | Yes |
| Remarks | * At extreme ambient temperatures the luminaire might automatically dim down to protect components |
| Light source engine type | LED |
| Product family code | BGP762 [DigiStreet Medium] |

| Lighting Technology | LED |
|---------------------------|---------------|
| Value ladder | Specification |
| CE mark | Yes |
| Warranty period | 5 years |
| Flammability mark | - |
| ENEC mark | ENEC mark |
| EU RoHS compliant | Yes |
| Light Technical | |
| Upward light output ratio | 0 |

| | |
|------------------------------------|----------------------|
| Luminous Flux | 19,580 lumen |
| Standard tilt angle posttop | 0° |
| Standard tilt angle side entry | 0° |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 151 lm/W |
| Color rendering index (CRI) | 70 |
| Light source color | 740 neutral white |
| Optical cover/lens type | Flat glass |
| Luminaire light beam spread | 61° x 150° |
| Optic type outdoor | Distribution wide 10 |

Operating and Electrical

| | |
|--|-----------------|
| Line Frequency | 50 to 60 Hz |
| Input Voltage | 220-240 V |
| Inrush current | 53 A |
| Inrush time | 0.3 ms |
| Power Consumption | 130 W |
| Power Factor (Fraction) | 0.99 |
| Connection | Screw connector |
| Cable | - |
| Number of products on MCB of 16 A type B | 8 |

Temperature

| | |
|---------------------------|---------------|
| Ambient temperature range | -40 to +50 °C |
|---------------------------|---------------|

Controls and Dimming

| | |
|-------------------------------|----------------------------|
| Dimmable | Yes |
| Driver/power unit/transformer | Power supply unit (On/Off) |
| Control interface | - |
| Constant light output | No |

Mechanical and Housing

| | |
|-----------------------------|---------------------------|
| Housing Material | Aluminum die cast |
| Reflector material | Polycarbonate |
| Optic material | Acrylate |
| Optical cover/lens material | Glass |
| Fixation material | Stainless steel |
| Housing Color | Dark gray |
| Mounting device | Spigot for diameter 62 mm |
| Optical cover/lens shape | Flat |
| Optical cover/lens finish | Clear |
| Overall length | 860 mm |
| Overall width | 361 mm |
| Overall height | 107 mm |
| Effective projected area | 0.068 m² |

| | |
|-------------------------------------|--------------------|
| Dimensions (Height x Width x Depth) | 107 x 361 x 860 mm |
|-------------------------------------|--------------------|

Approval and Application

| | |
|--|--|
| Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK09 [10 J] |
| Surge Protection (Common/Differential) | Luminaire surge protection level until 10 kV differential mode and 10 kV common mode |
| Sustainability rating | Lighting for circularity |
| Protection class IEC | Safety class II |
| Photobiological risk | Photobiological risk group 0 @200mm to EN62778 |

Initial Performance (IEC Compliant)

| | |
|---------------------------------------|----------------------|
| Initial chromaticity | (0.38, 0.38) SDCM <5 |
| Luminous flux tolerance | +/-7% |
| Power consumption tolerance | +/-10% |
| Init. Color Rendering Index Tolerance | +/-2 |

Over Time Performance (IEC Compliant)

| | |
|--|------|
| Control gear failure rate at median useful life 100000 h | 10 % |
| Lumen maintenance at median useful life* 100000 h | L96 |

Application Conditions

| | |
|------------------------------------|----------------|
| Maximum dim level | Not applicable |
| Performance ambient temperature Tq | 25 °C |

Product Data

| | |
|---------------------------------|--|
| Full product code | 871869637838000 |
| Order product name | BGP762 LED220-/740 II DW10 DGR SRG10 62 |
| Order code | 37838000 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |
| Material Nr. (12NC) | 910925866252 |
| Full product name | BGP762 LED220-/740 II DW10 DGR SRG10 62 |
| EAN/UPC - Case | 8718696378380 |
| EAN/UPC - Product/Case | 8718696378380 |

Dimensional drawing

