



# CoreLine Trunking Gen2

## LL200Z MB-SW 2xEP CU9 WH

Coreline Trunking Gen2 - - - Finger-protected - 0.2 J standard - White

CoreLine Trunking Gen2 is a light-line system that is designed for simplicity. It comes in a choice of lengths, flux packages and beam shapes to suit every project and application. Easy to use and integrate with spots and sensors, CoreLine Trunking Gen2 provides consistent, high-quality lighting with added protection against accidental water ingress. The innovative system is also easy to assemble and install for faster retrofits and refurbishments.

### Product data

| General Information             |                                  | Approval and Application          |                          |
|---------------------------------|----------------------------------|-----------------------------------|--------------------------|
| Protection class IEC            | Safety class I (I)               | Ingress protection code           | IP20 [ Finger-protected] |
| CE mark                         | CE mark                          | Mech. impact protection code      | IK02 [ 0.2 J standard]   |
| Material                        | Steel                            | <b>Product Data</b>               |                          |
| Angle                           | -                                | Full product code                 | 871951410820200          |
| Accessory colour                | White                            | Order product name                | LL200Z MB-SW 2xEP CU9 WH |
| Product family code             | LL200Z [ Coreline Trunking Gen2] | EAN/UPC – product                 | 8719514108202            |
| <b>Operating and Electrical</b> |                                  | Order code                        | 10820200                 |
| Input Voltage                   | 220 to 240 V                     | SAP numerator – quantity per pack | 1                        |
| Input frequency                 | 50 to 60 Hz                      | Numerator – packs per outer box   | 1                        |
| <b>Mechanical and Housing</b>   |                                  | SAP material                      | 910925867563             |
| Overall length                  | 267 mm                           |                                   |                          |
| Overall width                   | 80 mm                            |                                   |                          |

## CoreLine Trunking Gen2

---

SAP net weight (piece)

0.443 kg

