



GreenPerformance Troffer

RC100X LED37S 840 W60L60 POE MA G3

Variable linear-lens array in polycarbonate cover -

GreenPerform Troffer improves the compact design of the last generation with performance improvement and more variants for different markets. Integrates with all available systems: POE, InterAct office wireless, InterAct Office Pro, ActiLume controller. GreenPerform Troffer offers additional energy saving and connected features.

Product data

General Information		Operating and Electrical	
Light source colour	840 neutral white	Light source engine type	LED
Light source replaceable	No	Input Voltage	220 to 240 V
Number of gear units	1 unit	Input frequency	50 to 60 Hz
Driver included	Yes	Power factor (min.)	0.9
Optical cover/lens type	VAR-PC [Variable linear-lens array in polycarbonate cover]	Controls and Dimming	
Control interface	Power over Ethernet	Dimmable	Yes
Protection class IEC	Safety class I (I)	Mechanical and Housing	
Glow-wire test	60030 [Temperature 600 °C, duration 30 s]	Housing material	Metal
Flammability mark	F [For mounting on normally flammable surfaces]	Optic material	Polycarbonate
CE mark	CE mark	Optical cover/lens material	Polycarbonate
Warranty period	3 years	Fixation material	Steel
Constant light output	No	Optical cover/lens finish	Ribbed
Number of products on MCB (16 A type B)	24	Overall length	597 mm

GreenPerformance Troffer

Overall width	597 mm
Overall height	46 mm
Colour	White

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	3700 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	116 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	80
Initial chromaticity	SDCM<4
Initial input power	32 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	50000 h
---------------------------	---------

Application Conditions


Ambient temperature range	-20 to +40 °C
Suitable for random switching	No

Product Data

Full product code	911401511551
Order product name	RC100X LED375 840 W60L60 POE MA G3
Order code	01511551
SAP numerator – quantity per pack	1
Numerator – packs per outer box	2
SAP material	911401511551
SAP net weight (piece)	2.799 kg



Dimensional drawing



RC100X LED375 840 W60L60 POE MA G3

