



SmartBright Road

BRP131 LED100/CW 100W 220-240V DM GM MS

SmartBright Road - 10000 lm - 100 W - 5700 K

The SmartBright road is ideal for new streets and for renovating existing installations: this affordable range of lighting solutions combines clean, high-quality light with significant energy savings and reduced maintenance.

Product data

General information	
Light source colour	757 cool white
Driver included	Yes
Optical cover/lens type	PC-MLO [Polycarbonate micro lens optic]
Control interface	-
Connection	CU3 [Connection unit 3-pole]
Cable	-
Protection class IEC	Safety class I (I)
Flammability mark	F [For mounting on normally flammable surfaces]
CE mark	CE mark

Operating and electrical	
Input Voltage	220/240 V
Input frequency	50 or 60 Hz
Power factor (min.)	0.9

Controls and dimming	
Dimmable	Yes

Mechanical and housing	
Housing material	Aluminum

Optical cover/lens material	Polycarbonate
Overall length	453.8 mm
Overall width	277.2 mm
Overall height	85 mm
Effective projected area	0.11 m ²
Colour	Dark gray

Approval and application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Initial performance (IEC compliant)	
Initial luminous flux (system flux)	10000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	100 lm/W
Init. Corr. Colour Temperature	5700 K
Init. Colour rendering index	>70
Initial chromaticity	(0.33, 0.34) SDCM < 5
Initial input power	100 W
Power consumption tolerance	+/-10%

SmartBright Road

Application conditions

Ambient temperature range -40 to +50 °C

Product data

Full product code 911401654806
Order product name BRP131 LED100/CW 100W 220-240V DM GM MS
Order code 01654806

SAP numerator – quantity per pack 1


Numerator – packs per outer box 1

SAP material 911401654806

Net Weight (Piece) 3.299 kg



Dimensional drawing



BRP131 LED100/CW 100W 220-240V DM GM MS

