



RoadFlair

BRP393 LED303/WW 225W 220-240V DM PSR

RoadFlair - 30338 lm - 225 W - 3000 K

Designed for major and city roads, Philips RoadFlair is a new and exciting product set to brighten your streets beyond imagination. Smartly-designed to bring cities the highest savings possible with best-in-class lumen per watt, this road lighting production comes at a competitive price bound to excite. Philips RoadFlair brings energy efficiency, improves a city's sustainability drive and delivers significant cost reduction in urban environments. The right road luminaire coupled with the right lighting application will create the best environment for your municipality, benefiting local communities and boosting tourism and businesses.

Product data

| General Information | |
|--------------------------|---------------------------------------------------------------------------------------------------|
| Light source colour | 730 warm white |
| Light source replaceable | No |
| Driver included | Yes |
| Optical cover/lens type | PC-MLO [Polycarbonate micro lens optic] |
| Control interface | Analog |
| Connection | Mains outlet socket |
| Cable | - |
| Protection class IEC | Safety class I (I) |
| Flammability mark | F [For mounting on normally flammable surfaces] |
| CE mark | CE mark |
| ENEC mark | - |
| Light source engine type | LED |
| Serviceability class | Class B, the luminaire is equipped with some serviceable parts (when applicable): driver, control |

| | |
|--|------------------------------------------------------------------|
| | units, surge-protection device, front cover and mechanical parts |
|--|------------------------------------------------------------------|

| Light Technical | |
|--------------------------------|---|
| Standard tilt angle post-top | - |
| Standard tilt angle side entry | - |

| Operating and Electrical | |
|--------------------------|--------------|
| Input Voltage | 220 to 240 V |
| Input frequency | 50 or 60 Hz |
| Power factor (min.) | 0.9 |

| Controls and Dimming | |
|----------------------|-----|
| Dimmable | Yes |

| Mechanical and Housing | |
|------------------------|-------------------|
| Housing material | Aluminum die-cast |

RoadFlair

| | |
|-----------------------------|--------------------------------------------|
| Optical cover/lens material | Polycarbonate |
| Mounting device | 48/60S [Side-entry for diameter 48-60 mm] |
| Optical cover/lens shape | Ball, globular |
| Optical cover/lens finish | Frosted |
| Overall length | 651 mm |
| Overall width | 295 mm |
| Overall height | 86 mm |
| Effective projected area | 0.17 m ² |
| Colour | Gray |

Approval and Application

| | |
|------------------------------|-----------------------------------------------|
| Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK08 [5 J vandal-protected] |

Initial Performance (IEC Compliant)

| | |
|-------------------------------------|----------|
| Initial luminous flux (system flux) | 30338 lm |
| Luminous flux tolerance | +/-10% |
| Initial LED luminaire efficacy | 140 lm/W |
| Init. Corr. Colour Temperature | 3000 K |
| Init. Colour rendering index | >70 |

| | |
|-----------------------------|-----------------------|
| Initial chromaticity | (0.43, 0.40) SDCM < 5 |
| Initial input power | 225 W |
| Power consumption tolerance | +/-10% |

Application Conditions


| | |
|---------------------------|---------------|
| Ambient temperature range | -40 to +50 °C |
| Maximum dimming level | 10% |

Product Data

| | |
|-----------------------------------|---------------------------------------|
| Full product code | 911401867198 |
| Order product name | BRP393 LED303/WW 225W 220-240V DM PSR |
| Order code | 01867198 |
| SAP numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 1 |
| SAP material | 911401867198 |
| SAP net weight (piece) | 7.999 kg |



Dimensional drawing



BRP391/392/393/394 RoadFlair

