



Quebec LED

BRP776 LED22-4S/830 PSDD DX50 PGR BK DDF

QUEBEC LED - LED module 2200 lm - 4th generation, screw fixation - 830 warm white - Power supply unit with DynaDimmer - Safety class I (I) - Distribution extra wide 50 - Flat glass - Black - Philips standard surge protection level kV - - - 25 °C - -

Quebec LED is a stylish luminaire designed to brighten up residential streets and pathways, precincts, parks and other urban spaces. It incorporates an energy-efficient LED engine with high-performance optics, while at the same time retaining the character of the original Quebec fixture. It also offers a choice of bowl versions and mounting options. All these factors together make Quebec LED a versatile solution that can meet the needs of any project.

Product data

General information		Protection class IEC	Safety class I (I)
Lamp family code	LED22 [LED module 2200 lm]	Flammability mark	NO [-]
Lamp version	4S [4th generation, screw fixation]	CE mark	CE mark
Light source colour	830 warm white	ENEC mark	ENEC mark
Light source replaceable	Yes	Warranty period	5 years
Number of gear units	1 unit	Optic type outdoor	Distribution extra wide 50
Driver/power unit/transformer	PSDD [Power supply unit with DynaDimmer]	Remarks	* - According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires - January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme
Driver included	Yes		
Optical cover/lens type	FG [Flat glass]		
Luminaire light beam spread	17° - 5° x 132°		
Connection	W [Plug-in connector 3-pole Wieland/Adels compatible]		
Cable	-		

Quebec LED

	ambient temperatures the luminaire might automatically dim down to protect components
Constant light output	No
Number of products on MCB (16 A type B)	29
EU RoHS compliant	Yes
Light source engine type	LED
Serviceability class	Class A, the luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge-protection device, optics, front cover and mechanical parts
Product family code	BRP776 [QUEBEC LED]

Light Technical

Upward light output ratio	0.03
Standard tilt angle post-top	-
Standard tilt angle side entry	0°

Operating and Electrical

Input Voltage	220 to 240 V
Input frequency	50 to 60 Hz
Inrush current	15 A
Inrush time	0.295 ms
Power factor (min.)	0.99
Power factor (nom.)	0.92

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Glass
Fixation material	Aluminium
Mounting device	No [-]
Optical cover/lens shape	Flat
Optical cover/lens finish	Silkscreen print gray
Overall height	388 mm
Overall diameter	472 mm
Effective projected area	0.094 m ²
Colour	Black

Dimensions (height x width x depth)	388 x NaN x NaN mm (15.3 x NaN x NaN in)
-------------------------------------	--

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge protection (common/differential)	Philips standard surge protection level kV

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	1848 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	102 lm/W
Init. Corr. Colour Temperature	3000 K
Init. Colour rendering index	>80
Initial chromaticity	(0.410, 0.390) SDCM <5
Initial input power	18.2 W
Power consumption tolerance	+/-10%
Init. colour rendering index tolerance	+/-2

Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L97

Application Conditions


Ambient temperature range	-40 to +50 °C
Performance ambient temperature Tq	25 °C

Product Data

Full product code	871869908989400
Order product name	BRP776 LED22-4S/830 PSDD DX50 PGR BK DDF
EAN/UPC – product	8718699089894
Order code	08989400
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	912300023479
SAP net weight (piece)	7.030 kg




Dimensional drawing




Quebec LED BRP775/776

Photometric data



OFPL1_BRP776FGT251xLED22-4S830DX50



OFPC1_BRP776FGT251xLED22-4S830DX50

