



ClearFlood Large

BVP651 LED650-4S/740 OFA52 ALU PSU

ClearFlood large, LED module 65000 lm, LED, Power supply unit (On/Off), Optiflux asymmetrical axis angle 52°, Aluminum

ClearFlood Large is designed to meet the requirements of a wide range of floodlighting applications. It also includes all the necessary control features and interfaces to make it future-proof and even more efficient. ClearFlood Large lets you choose the exact number of lumens you need for your application. Incorporating extremely high-efficiency optics and state-of-the-art LEDs, it is a highly competitive solution offering an outstanding lux/euro ratio and energy savings of up to 40% (without the use of additional controls). The wide choice of optics ensures maximum application coverage. ClearFlood Large is easy to install – you simply plug it in and select the best option for your needs. Perfect for replacing conventional technology and enabling intelligent lighting control while retaining the same electrical installation and poles.

Product data

General Information			
Lamp family code	LED650 [LED module 65000 lm]		might automatically dim down to protect components
Light source replaceable	Yes	Light source engine type	LED
Number of gear units	2 units	Service tag	Yes
Driver included	Yes	Product family code	BVP651 [ClearFlood large]
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire	Lighting Technology	LED
		Value ladder	Specification
		CE mark	Yes
		Warranty period	5 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark

ClearFlood Large

EU RoHS compliant	Yes
-------------------	-----

Light Technical

Upward light output ratio	0
Luminous Flux	55,440 lumen
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	137 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover/lens type	Flat glass
Luminaire light beam spread	39° - 11° x 98°
Optic type outdoor	Optiflux asymmetrical axis angle 52°

Operating and Electrical

Line Frequency	50 to 60 Hz
Input Voltage	220 to 240 V
Inrush current	13 A
Inrush time	1.32 ms
Power Consumption	405 W
Power Factor (Fraction)	0.99
Connection	Connection unit 5-pole
Cable	-

Number of products on MCB of 16 A type 3

B

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Glass
Fixation material	Steel
Housing Color	Aluminum
Mounting device	Mounting bracket adjustable

Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	817 mm
Overall width	597 mm
Overall height	80 mm
Effective projected area	0.41 m ²
Dimensions (Height x Width x Depth)	80 x 597 x 817 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 4 kV differential mode and 4 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Initial chromaticity	(0.380, 0.390) SDCM <5
Luminous flux tolerance	+/-7%
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.005 %
Control gear failure rate at median useful life 100000 h	0.1 %
Lumen maintenance at median useful life* 100000 h	L96

Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

Product Data

Full product code	871869910804500
Order product name	BVP651 LED650-4S/740 OFA52 ALU PSU
Order code	10804500
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912300023760
Full product name	BVP651 LED650-4S/740 OFA52 ALU PSU
EAN/UPC - Case	8718699108045
EAN/UPC - Product/Case	8718699108045

ClearFlood Large

Dimensional drawing

← 52 →

