



ClassicStreet

BDP794 LED63-4S/740 II DW10 MK-WH FG BK

BDP794 | ClassicStreet Top - LED63 | LED module 6300 lm - 740 neutral white - Power supply unit regulating external with constant light output - Safety class II - Distribution wide 10 - Mask white - Flat glass - Constant light output and DynaDimmer fixed presets version 2 - Luminaire surge protection level until 10 kV differential mode and 10 kV common mode - External connector - Cable 1.0 m with plug Wieland/Adels compatible 2-pole - Post-top for diameter 60 mm

Recalling the iconic beauty of 20th-century street lanterns, ClassicStreet combines elegant design with the subtle details of heritage luminaires while meeting today's urban lighting requirements. Though echoing the past, the ClassicStreet luminaire is very much shaped for the future. Its gently curved design, together with dedicated brackets and poles, creates a contemporary look that beautifies our cities and creates distinctive and warm night- and daytime ambiances. Not only in historical and traditional architectural settings, but also in more modern urban environments too. Designed around its LED engine, ClassicStreet delivers outstanding levels of lighting and energy performance.

Product data

General information	
Lamp family code	LED63 [LED module 6300 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Remarks	*-Per Lighting Europe guidance paper *Evaluating performance of LED based

luminaires - January 2018¹: statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire

ClassicStreet

	might automatically dim down to protect components
Light source engine type	LED
Service tag	Yes
Product family code	BDP794 [ClassicStreet Top]
Lighting Technology	LED
Value ladder	Performance
Embedded control	Constant light output and DynaDimmer fixed presets version 2
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
EU RoHS compliant	Yes

Light Technical

Upward light output ratio	0.03
Luminous Flux	4,320 lumen
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	112 lm/W
Color rendering index (CRI)	70
Number of light sources	20
Light source color	740 neutral white
Optical cover/lens type	Flat glass
Luminaire light beam spread	52° - 7° x 151°
Optic type outdoor	Distribution wide 10

Operating and Electrical

Line Frequency	50 to 60 Hz
Input Voltage	220-240 V
Initial CLO power consumption	38.5 W
Average CLO power consumption	39 W
End CLO power consumption	39.5 W
Inrush current	21 A
Inrush time	0.225 ms
Power Consumption	38.5 W
Power Factor (Fraction)	0.98
Connection	External connector
Cable	Cable 1.0 m with plug Wieland/Adels compatible 2-pole

Number of products on MCB of 16 A type B 26

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating external with constant light output

Control interface	-
Constant light output	Yes

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Glass
Fixation material	Aluminum
Housing Color	Black
Mounting device	Post-top for diameter 60 mm
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	428 mm
Overall width	428 mm
Overall height	586 mm
Effective projected area	0.15 m²
Dimensions (Height x Width x Depth)	586 x 428 x 428 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	4 m

Initial Performance (IEC Compliant)

Initial chromaticity	(0.380, 0.380) SDCM <5
Luminous flux tolerance	+/-7%
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L100

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

Product Data

Full product code	871869911690300
Order product name	BDP794 LED63-4S/740 II DW10 MK-WH FG BK
Order code	11690300
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	1
Material Nr. (12NC)	912300023860
Full product name	BDP794 LED63-4S/740 II DW10 MK-WH FG BK

EAN/UPC - Case	8718699116903
EAN/UPC - Product/Case	8718699116903

Dimensional drawing

