



Coreline tempo X-Large

BVP140 LED420-4S 36K1/740 PSU S

Coreline tempo X-Large, Floodlight, 250 W, 36120 lumen, 4000 K, CRI70, Symmetrical, IP66

CoreLine tempo X-Large delivers on the CoreLine promise of innovative, easy to use and high-quality floodlighting. The CoreLine tempo X-Large offers lumen packages for many different application areas as well as a choice of high-performance asymmetrical and symmetrical optics. A direct replacement for 250W, 400W HID and SON-T lamps, thanks to a narrow range of options, it's easy to find the best lux-for-lux replacement. The installation is also made easy due to a U-shaped universal mounting bracket and the external quick 3-poles connector. It is an ideal solution for outdoor led flood lighting for industrial/commercial areas, parking lots, etc.

Product data

General Information	
Lamp family code	LED420 [LED module 42000 lm]
Light source replaceable	Yes
Number of gear units	2 units
Driver included	Yes
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Light source engine type	LED
Product family code	BVP140 [CORELINE TEMPO X-LARGE]
Lighting Technology	LED
Value ladder	Performance
CE mark	Yes

Warranty period	5 years
Flammability mark	For mounting on easily flammable surfaces
ENEC mark	ENEC plus mark
EU RoHS compliant	Yes
Light Technical	
Upward light output ratio	0
Luminous Flux	36,120 lumen
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	144 lm/W
Color rendering index (CRI)	>70

Coreline tempo X-Large

Light source color	740 neutral white
Optical cover/lens type	Flat glass
Luminaire light beam spread	73° x 26°
Optic type outdoor	Symmetrical

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	250 W
Power Factor (Fraction)	0.99
Connection	Connection unit 3-pole
Cable	Cable 1.0 m with plug Wieland/Adels compatible 3-pole
Number of products on MCB of 16 A type B	4

Temperature

Ambient temperature range	-40 to +45 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Glass
Fixation material	Steel
Housing Color	Aluminum
Mounting device	Mounting bracket adjustable
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	540 mm
Overall width	560 mm
Overall height	70 mm
Effective projected area	0.26 m ²
Dimensions (Height x Width x Depth)	70 x 560 x 540 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Sustainability rating	-
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <5
Luminous flux tolerance	+/-7%
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 75000 h	10 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 75000 h	L80
Lumen maintenance at median useful life* 100000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

Product Data

Full product code	871869987283000
Order product name	BVP140 LED420-4S 36K1/740 PSU S
Order code	87283000
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912300024339
Full product name	BVP140 LED420-4S 36K1/740 PSU S
EAN/UPC - Case	8718699872830
EAN/UPC - Product/Case	8718699872830

Coreline tempo X-Large

Dimensional drawing

