



OccuSwitch

LRM1070/00 Sensr Mov Det St

Movement detector with a built-in switch up to 6 A controls max 25 m² area Basic

Movement detector with a built-in switch - up to 6 A - controls max 25 m² area - Basic


Product data

General information	
Type description – long text	Movement detector with a built-in switch - up to 6 A - controls max 25 m ² area - Basic
Product data	
Full product code	871155973138499
Order product name	LRM1070/00 SENSR MOV DET ST
EAN/UPC – product	8711559731384
Order code	73138499

SAP numerator – quantity per pack	1
Local code description	SENSOR LRM1070/00SENSRMOVDST
Numerator – packs per outer box	42
SAP material	913700327803
Net Weight (Piece)	0.200 kg

OccuSwitch

Dimensional drawing



LRM1070/00 SENSR MOV DET ST

