



PrimaVision Compact for CDM

HID-PV C 35 /I CDM 220-240V 50/60Hz

High-quality, compact and lightweight HID electronic gear for optimal and reliable performance of 20, 35, 50 and 70 W CDM lamps

Product data

Operating and Electrical		Approval and Application	
Line Frequency	50 to 60 Hz	Safety Standard	EN 61347-2-12
Input Frequency	50 to 60 Hz	Environmental Standard	ISO 14001
Input Voltage	220 to 240 V	Approval Marks	CE marking ENEC certificate
Earth Leakage Current (Max)	0.25 mA	Product Data	
Inrush Current Width	0.25 ms	Full product code	872790085973700
Inrush Current Peak (Max)	26 A	Order product name	HID-PV C 35 /I CDM 220-240V 50/60Hz
Number of Products on MCB (16A Type B) (Nom)	24		NG
Wiring		Order code	85973700
Cable Length From Device to Lamp	2.0 m	Numerator - Quantity Per Pack	1
Connector Type	Insert	Numerator - Packs per outer box	12
Temperature		Material Nr. (12NC)	913700653166
Ambient temperature range	-20 °C to 50 °C	Full product name	HID-PV C 35 /I CDM 220-240V 50/60Hz
T-Case Lifetime (Nom)	75 °C	EAN/UPC - Case	8727900859737
T-Case Maximum (Max)	75 °C	Mechanical and Housing	
Housing		Housing	/I

PrimaVision Compact for CDM

Dimensional drawing

A2

Product	D1	C1	A1	A2	B1
HID-PV C 35 /I CDM 220-240V 50/60Hz NG	4.8 mm	34.5 mm	188.0 mm	170.0 mm	82.7 mm

