



# PrimaVision Compact for CDM

## HID-PV C 70 /I CDM 220-240V 50/60Hz

High-quality, compact and lightweight HID electronic gear for optimal and reliable performance of 20, 35, 50 and 70 W CDM lamps

### Product data

Operating and Electrical		Approval and Application	
Line Frequency	50 to 60 Hz	Safety Standard	EN 61347-2-12
Input Frequency	50 to 60 Hz	Environmental Standard	ISO 14001
Input Voltage	220 to 240 V	Approval Marks	CE marking ENEC certificate
Earth Leakage Current (Max)	0.25 mA		
Inrush Current Width	0.33 ms	Product Data	
Inrush Current Peak (Max)	33 A	Full product code	872790085988100
Number of Products on MCB (16A Type B) (Nom)	20	Order product name	HID-PV C 70 /I CDM 220-240V 50/60Hz NG
		Order code	85988100
Wiring		Numerator - Quantity Per Pack	1
Cable Length From Device to Lamp	2.0 m	Numerator - Packs per outer box	12
Connector Type	Insert	Material Nr. (12NC)	913700653266
		Full product name	HID-PV C 70 /I CDM 220-240V 50/60Hz
Temperature		EAN/UPC - Case	8727900859881
Ambient temperature range	-20 °C to 45 °C		
T-Case Lifetime (Nom)	75 °C		
T-Case Maximum (Max)	75 °C		
Mechanical and Housing			
Housing	/I		

# PrimaVision Compact for CDM

## Dimensional drawing

A2

Product	D1	C1	A1	A2	B1
HID-PV C 70 /I CDM 220-240V 50/60Hz NG	4.8 mm	34.5 mm	188.0 mm	170.0 mm	82.7 mm

