

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

BSN 100 K302-A2-ITS 230V 50Hz

Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps



Product data

| Operating and Electrical | |
|--------------------------|-----------------------------|
| Line Frequency | 50 Hz |
| Input Frequency | 50 Hz |
| Input Voltage | 230 V |
| Wiring | |
| Connector Type | Screw |
| Approval and Application | |
| Approval Marks | CE marking ENEC certificate |

| Product Data | |
|---------------------------------|-------------------------------|
| Full product code | 871869674086600 |
| Order product name | BSN 100 K302-A2-ITS 230V 50Hz |
| Order code | 74086600 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 6 |
| Material Nr. (12NC) | 913700752326 |
| Full product name | BSN 100 K302-A2-ITS 230V 50Hz |
| EAN/UPC - Case | 8718696740873 |

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

Dimensional drawing



| Product | A1 | A2 | B1 | C1 | D1 |
|-------------------------------|--------|-------|-------|-------|--------|
| BSN 100 K302-A2-ITS 230V 50Hz | 123 mm | 98 mm | 61 mm | 52 mm | 6.2 mm |

