



# Dynalite Sensors

## DUS360CS-DALI

lighting controls system - dynalite - DALI sensor

The Philips Dynalite sensor range combines motion detection, light level detection and IR receive in one unit. Each of these features can be operated at the same time, allowing automation scenarios such as turning on the lights after detecting motion and then dimming the lighting level once the available sunlight has been measured, thereby providing additional energy savings. By combining each of these functions into one device, operational efficiency is improved. Each sensor has an in-built microprocessor, allowing logical functions to control one small room, the floor of a building, or an entire building. All sensors receive their power from the DyNet network, and as they are fully remotely programmable, they can be configured to automate and control a virtually unlimited number of controlled outputs.

### Product data

General Information	
CE mark	CE mark
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options
EU RoHS compliant	Yes

  

Approval and Application	
UL recognised	Yes
UL recognised Canada and USA	Yes

  

Application Conditions	
Ambient temperature range	0 to +45 °C

  

Product Data	
Full product code	871869688852000
Order product name	DUS360CS-DALI
EAN/UPC – product	8718696888520
Order code	88852000
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	913703023909
SAP net weight (piece)	135.000 g