



# Dynalite Sensors

## DUS30CS

The Philips Dynalite sensor range combines motion detection, light level detection and IR receive in one unit. Each of these features can be operated at the same time, allowing automation scenarios such as turning on the lights after detecting motion and then dimming the lighting level once the available sunlight has been measured, thereby providing additional energy savings. By combining each of these functions into one device, operational efficiency is improved. Each sensor has an in-built microprocessor, allowing logical functions to control one small room, the floor of a building, or an entire building. All sensors receive their power from the DyNet network, and as they are fully remotely programmable, they can be configured to automate and control a virtually unlimited number of controlled outputs.

### Product data

General Information	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options
Temperature	
Ambient temperature range	-20 to +45 °C
Approval and Application	
Ingress protection code	IP20/54 [Finger-protected; dust accumulation-protected, splash-proof]
CE mark	CE mark
EU RoHS compliant	Yes

Product Data	
Full product code	871869688808700
Order product name	DUS30CS
Order code	88808700
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material number (12NC)	913703244309
Full product name	DUS30CS
EAN/UPC - Case	8718696895085



# Dynalite Sensors

## Dimensional drawing

