



EB-Certalume for TL5 lamps

EB-C 128 TL5 220-240V 50/60Hz

Affordable, reliable, high frequency electronic ballast for TL5 fluorescent lamps, ideal alternative for electromagnetic (EM) ballasts

Product data

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Input Voltage	220 to 240 V
Earth Leakage Current (Max)	0.7 mA

Wiring	
Connector Type Input Terminals	250 manual connector [Suitable for manual wiring and easy release button]
Color Input Terminals	Orange
Color Output Terminals	Grey
Connector Type Output Terminals	250 manual connector [Suitable for manual wiring and easy release button]

Temperature	
T-Case Lifetime (Nom)	75 °C


Mechanical and Housing	
Housing	L 275x20x21

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Energy Efficiency Index	A2
Approval Marks	CCC certificate CB Certificate

Product Data	
Full product code	872790088656600
Order product name	EB-C 128 TL5 220-240V 50/60Hz
Order code	88656600
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50
Material Nr. (12NC)	913713196414
Full product name	EB-C 128 TL5 220-240V 50/60Hz
EAN/UPC - Case	8727900886566

EB-Certalume for TL5 lamps

Dimensional drawing



Product	D1	C1	A1	A2	B1
EB-C 128 TL5 220-240V 50/60Hz	4.2 mm	21.0 mm	275.0 mm	265.0 mm	19.8 mm

