



# InfraRed Industrial Heat Incandescent

## BR125 IR 150W E27 230-250V CL 1CT/10

The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

### Product data

General information	
Cap base	E27 [ E27]
Operating position	UNIVERSAL [ Any or Universal (U)]
Main application	Infrared Industrial
Nominal lifetime (nom.)	5000 h
Rated lifetime (hours)	5000 h

Operating and electrical	
Power (Rated) (Nom)	150 W
Voltage (Nom)	230-250 V

Controls and dimming	
Dimmable	Yes

Mechanical and housing	
Lamp Finish	Clear

Bulb material	Hard Glass
Bulb shape	BR125


Luminaire design requirements	
Bulb temperature (max.)	500 °C

Product data	
Full product code	871150057522725
Order product name	BR125 IR 150W E27 230-250V CL 1CT/10
EAN/UPC – product	8711500575227
Order code	57522725
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	923211943801
Copy Net Weight (Piece)	104.000 g

# InfraRed Industrial Heat Incandescent

## Dimensional drawing



BR125 IR 150W E27 230-250V CL 1CT/10

Product	D	C (max)
BR125 IR 150W E27 230-250V CL 1CT/10	125 mm	173 mm

