



InfraRed Industrial Heat Incandescent

BR125 IR 250W E27 230-250V Red 1CT/10


The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

Product data

General Information		Bulb material	
Cap base	E27 [E27]	Bulb material	Hard Glass
Operating position	H45 [h45]	Bulb shape	BR125
Main application	Infrared Industrial	Luminaire Design Requirements	
Nominal lifetime (nom.)	5000 h	Bulb temperature (max.)	250 °C
Rated lifetime (hours)	5000 h	Product Data	
Operating and Electrical		Full product code	871150057521025
Power (Rated) (Nom)	250 W	Order product name	BR125 IR 250W E27 230-250V Red 1CT/10
Voltage (Nom)	230-250 V	EAN/UPC – product	8711500575210
Controls and Dimming		Order code	57521025
Dimmable	Yes	SAP numerator – quantity per pack	1
		Numerator – packs per outer box	10
Mechanical and Housing		SAP material	923212043801
Lamp Finish	Red	SAP net weight (piece)	107.000 g

InfraRed Industrial Heat Incandescent

Dimensional drawing



BR125 IR 250W E27 230-250V Red 1CT/10

Product	D	C (max)
BR125 IR 250W E27 230-250V Red 1CT/10	125 mm	173 mm

