



Halogen reflector

6423 150W GZ6.35 15V 1CT/10X5F

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.

Product data

General information	
Cap base	GZ6.35 [GZ6.35]
Philips code	6423
ANSI Code	EFR
LIF Code	A1/232
Operating position	P90/P15
Main application	Projection
Life to 50% failures (nom.)	50 h
Light technical	
Correlated Colour Temperature (Nom)	3380 K
Colour rendering index (nom.)	100
Operating and electrical	
Power (Rated) (Nom)	150 W


Voltage (Nom)	15 V
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb material	Quartz-UV Open
Reflector finish	Smooth
Filament dimensions WxH	-
Bulb shape	R50 [R 50mm]
Luminaire design requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	400 °C
Pinch temperature (max.)	400 °C

Halogen reflector

Working distance WD	32 mm
Product data	
Full product code	871150042733560
Order product name	6423 150W GZ6.35 15V 1CT/10X5F
EAN/UPC – product	8711500427335
Order code	42733560

SAP numerator – quantity per pack	1
Numerator – packs per outer box	50
SAP material	923916818504
Net Weight (Piece)	0.023 kg

Dimensional drawing



6423 150W GZ6.35 15V 1CT/10X5F

Product	D (max)	C (max)
6423 150W GZ6.35 15V 1CT/10X5F	50 mm	42 mm

