



Plusline Large

Plusline L 1000W R7s 240V 1CT/10

Mains-voltage linear lamp giving white halogen light

Product data

General Information	
Cap base	R7S [R7s]
Operating position	P4 [Parallel +/-4D or Horizontal(HOR)]
Nominal lifetime (nom.)	2000 h
Switching cycle	8,000X
Rated lifetime (hours)	2000 h

Light Technical	
Luminous flux (nom.)	21500 lm
Luminous flux (rated) (nom.)	21500 lm
Correlated Colour Temperature (Nom)	2900 K
Luminous efficacy (rated) (nom.)	21.5 lm/W
Colour rendering index (nom.)	100
LLMF at end of nominal lifetime (min.)	80 %

Operating and Electrical	
Power (Rated) (Nom)	1000.0 W
Lamp current (nom.)	4.17 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1
Voltage (Nom)	240 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T11 [T 11mm]

Approval and Application	
Energy consumption kWh/1,000 hours	1000 kWh

Luminaire Design Requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	350 °C

Product Data	
Full product code	872790080855100
Order product name	Plusline L 1000W R7s 240V 1CT/10
EAN/UPC – product	8727900808551
Order code	80855100
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	923932145741
SAP net weight (piece)	0.016 kg
ILCOS code	HDG//RS-1000-240-R7s-185,7

Plusline Large

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline L 1000W R7s 240V 1CT/10	11 mm	187.3 mm	185.7 mm	184.1 mm	189.1 mm

DEBig 1000W R7s 240V T11 CL

