



# Halogen reflector

## 6423FO 150W GZ6.35 15V 1CT

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.

### Product data

General Information	
Cap base	GZ6.35 [ GZ6.35]
Philips code	6423FO
ANSI Code	EFR
LIF Code	A1/232
Operating position	P90/P15
Main application	Projection
Life to 50% failures (nom.)	50 h
J code	-
Light Technical	
Luminous flux (nom.)	840 lm
Correlated Colour Temperature (Nom)	3380 K
Colour rendering index (nom.)	100

Operating and Electrical	
Power (Rated) (Nom)	150 W
Voltage (Nom)	15 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-base information	na [ -]
Bulb material	Quartz-UV Open
Reflector finish	-
Filament shape	-
Filament dimensions WxH	-
Bulb shape	R50 [ R 50mm]

# Halogen reflector

## Luminaire Design Requirements


Bulb temperature (max.)	900 °C
Pinch temperature (max.)	400 °C
Working distance WD	32 mm

## Product Data

Full product code	871150040971360
Order product name	6423FO 150W GZ6.35 15V 1CT/10X5F

EAN/UPC – product	8711500409713
Order code	40971360
SAP numerator – quantity per pack	1
Numerator – packs per outer box	50
SAP material	924048218504
SAP net weight (piece)	0.024 kg

## Dimensional drawing



6423FO 150W GZ6.35 15V 1CT/10X5F

Product	D (max)	C (max)
6423FO 150W GZ6.35 15V 1CT/10X5F	50 mm	42 mm

