



Halogen non-reflector

14623 95W G6.35 17V 1CT/10X10F

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

Product data

General Information	
Cap base	G6.35 [G6.35]
Philips code	14623
ANSI Code	-
LIF Code	-
Operating position	S90 [Standing +/-90D or Base Down (BDH)]
Main application	Projection
Life to 50% failures (nom.)	2000 h

Light Technical	
Luminous flux (rated) (nom.)	2150 lm
Colour rendering index (nom.)	-

Operating and Electrical	
Power (Rated) (Nom)	95 W
Voltage (Nom)	17 V


Mechanical and Housing	
Bulb material	Quartz-UV Open
Filament shape	Flat
Filament dimensions WxH	5.24 x 3.13

Luminaire Design Requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	350 °C

Product Data	
Full product code	871150042667350
Order product name	14623 95W G6.35 17V 1CT/10X10F
EAN/UPC – product	8711500426673
Order code	42667350
SAP numerator – quantity per pack	1
Numerator – packs per outer box	100
SAP material	924049819103
SAP net weight (piece)	0.004 kg

Halogen non-reflector

Dimensional drawing



14623 95W G6.35 17V

Product	D (max)	L (min)	L (max)	L	P (max)	P	P (min)	C (max)
14623 95W	11.5 mm	31.5 mm	32.25	32	1.05 mm	1 mm	0.95	50 mm
G6.35 17V			mm	mm			mm	
1CT/10X10F								

