



Plusline Small

Plusline S 300W R7s 230V 1CT/10X10F

Mains-voltage linear lamp giving white halogen light

Product data

General information	
Cap base	R7S [R7s]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime (nom.)	2000 h
Rated lifetime (hours)	2000 h
Light technical	
Luminous flux (nom.)	5114 lm
Correlated Colour Temperature (Nom)	2900 K
Luminous efficacy (rated) (nom.)	17 lm/W
Colour rendering index (nom.)	100
Operating and electrical	
Power (Rated) (Nom)	300 W
Lamp current (nom.)	1.3 A
Starting time (nom.)	0.0 s
Voltage (Nom)	230 V
Controls and dimming	
Dimmable	Yes

Mechanical and housing	
Lamp Finish	Clear
Bulb shape	T3 [T 12mm (T3)]
Luminaire design requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	350 °C
Pinch temperature (max.)	350 °C

Product data	
Full product code	872790080895700
Order product name	Plusline S 300W R7s 230V 1CT/10X10F
EAN/UPC – product	8727900808957
Order code	80895700
SAP numerator – quantity per pack	1
Numerator – packs per outer box	100
SAP material	924735444201
Net Weight (Piece)	0.010 kg
ILCOS code	HDG//RS-300-230-R7s-114,2

Plusline Small

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline S 300W R7s 230V 1CT/10X10F	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm

Plusline S 300W R7s 230V 1CT/10X10F

