



Halogen Clickline G9

Halogen MV Click 28W G9 230V CL 1CT

Ideal solution for small decorative luminaires. UV-block glass and safety fuse allow usage without cover glass. The compact Clickline gives crisp white light over a long lifetime.

Product data

General information	
Cap base	G9 [G9]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime (nom.)	2000 h
Switching cycle	8,000X
Rated lifetime (hours)	2000 h
Rated Lifetime (Years)	2 a
	Sphere

Light technical	
Luminous flux (nom.)	350 lm
Luminous flux (rated) (nom.)	370 lm
Chromaticity coordinate X (nom.)	0.452
Chromaticity coordinate Y (nom.)	0.409
Correlated Colour Temperature (Nom)	2800 K
Luminous efficacy (rated) (nom.)	12.1 lm/W
Colour rendering index (nom.)	100
LLMF at end of nominal lifetime (min.)	80 %

Operating and electrical	
Power (Rated) (Nom)	29 W
Lamp current (nom.)	0.12 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light

Power factor (nom.)	1
Voltage (Nom)	230 V

Controls and dimming	
Dimmable	Yes

Mechanical and housing	
Lamp Finish	Clear
Bulb shape	T13 [T 13 mm]

Approval and application	
Energy Efficiency Class	G
Energy consumption kWh/1,000 hours	29 kWh
	423233

Luminaire design requirements	
Bulb temperature (max.)	950 °C
Pinch temperature (max.)	350 °C
Pinch Temperature (Max)-DUP(do not use)	350 °C


Product data	
Full product code	872790086398700
Order product name	Halogen MV Click 28W G9 230V CL 1CT
EAN/UPC – product	8727900863987

Halogen Clickline G9

Order code	86398700
SAP numerator – quantity per pack	1
Local code description	8342226
Numerator – packs per outer box	100

SAP material	925640644205
Net Weight (Piece)	0.003 kg

Dimensional drawing



Halogen MV Click 28W G9 230V CL 1CT

Product	D (max)	L	C (max)
Halogen MV Click 28W G9 230V CL 1CT	13 mm	21.7 mm	45 mm

