



# Accentline

## Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F

Low-voltage halogen burner in glass reflector. Ideal solution for small decorative luminaires, putting your objects in the spotlight. Dichroic coating prevents heat transmission onto the object.

### Product data

General Information	
Cap base	GU5.3 [ GU5.3]
Operating position	UNIVERSAL [ Any or Universal (U)]
Life to 50% failures (nom.)	4000 h
Nominal lifetime (nom.)	4000 h
Switching cycle	16,000X
Rated lifetime (hours)	4000 h
Light Technical	
Beam Angle (Nom)	36 °
Luminous flux (nom.)	680 lm
Luminous intensity (max.)	1500 cd
Rated beam angle	36 °
Correlated Colour Temperature (Nom)	3000 K
Colour rendering index (nom.)	100
Luminous flux in 90° cone (rated)	680 lm
Operating and Electrical	
Power (Rated) (Nom)	50 W
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light s
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb shape	MR16 [ 2inch/50mm]
Approval and Application	
Energy consumption kWh/1,000 hours	53 kWh
Product Data	
Full product code	871869658845100
Order product name	Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F
EAN/UPC – product	8718696588451
Order code	58845100
SAP numerator – quantity per pack	1
Numerator – packs per outer box	50
SAP material	926000850063
SAP net weight (piece)	0.006 kg

# Accentline


## Dimensional drawing



MR16 4000h 12V 50W 36D GU5.3

Product	D (max)	C (max)
Accentline 50W 4000h GU5.3 12V 36D 1CT/10X5F	51 mm	46 mm

## Photometric data



Consumer Lamps, Halogen, Spectral power distribution

