



Actinic BL PL-S/PL-L

PL-L 36W/10/4P 1CT/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	2G11 [2G11]
Main application	Insect traps
Life to 50% failures (nom.)	11000 h
Light Technical	
Colour Code	210 [leadfree 360 glass (10)]
Chromaticity coordinate X (nom.)	220
Chromaticity coordinate Y (nom.)	215
UV Depreciation at 2,000 h	15 %
UV depreciation at 5000 hours	20 %
Operating and Electrical	
Power (Rated) (Nom)	36 W
Lamp current (nom.)	0.435 A


Voltage (Nom)	106 V
Mechanical and Housing	
Cap-base information	4 Pins (4P)
Bulb shape	2xT16
Approval and Application	
Mercury (Hg) content (max.)	2.1 mg
Mercury (Hg) content (nom.)	2.0 mg
UV	
UV-A radiation 100 hours (IEC)	8.5 W
Product Data	
Full product code	871150026481740

Actinic BL PL-S/PL-L

Order product name	Insect PL-L 36W /10
EAN/UPC – product	8711500264817
Order code	26481740
SAP numerator – quantity per pack	1
Numerator – packs per outer box	25

SAP material	927903421007
SAP net weight (piece)	104.000 g


Dimensional drawing




PL-L 36W/210/4P

Product	D1 (max)	D (max)	C1	A (max)	B (max)	C (max)
Insect PL-L 36W /10	18 mm	39 mm	20.0 mm	384.2 mm	410 mm	416.6 mm

Photometric data



XDPB_XURPLL_0001-Spectral power distribution B/W



XDPO_XURPLL_0001-Spectral power distribution Colour

