



MASTER TL-D Super 80

MASTER TL-D Super 80 18W/840 1SL/25

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Lamp Current (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		0.360 A
Flux measurement reference	Sphere	Controls and Dimming	
Life to 50% Failures (Nom)	15,000 hour(s)	Dimmable	Yes
Light Technical		Mechanical and Housing	
Color Code	840 [CCT of 4000K]	Bulb Shape	T8 [26 mm (T8)]
Luminous Flux	1,350 lumen	Approval and Application	
Color Designation	Cool White (CW)	Energy Efficiency Class	G
Chromaticity Coordinate X (Nom)	0.38	Mercury (Hg) Content (Nom)	1.7 mg
Chromaticity Coordinate Y (Nom)	0.38	Energy Consumption kWh/1000 h	19 kWh
Correlated Color Temperature (Nom)	4000 K	EPREL Registration Number	423364
Luminous Efficacy (rated) (Nom)	75 lm/W	Product Data	
Color rendering index (CRI)	81	Full product code	871150063171840
Operating and Electrical		Order product name	MASTER TL-D Super 80 18W/840 1SL/25
Power Consumption	18.2 W		

MASTER TL-D Super 80

Order code	63171840
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927920084023
Full product name	MASTER TL-D Super 80 18W/840 1SL/25


EAN/UPC - Case	8711500631725
EAN/UPC - Product/Case	8711500631718

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Super 80 18W/840 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D Super 80 18W/840 1SL/25

Lifetime



Life Expectancy Diagram - MASTER TL-D Super 80 18W/840 1SL/25



Life Expectancy Diagram - MASTER TL-D Super 80 18W/840 1SL/25

MASTER TL-D Super 80

Lifetime



Lumen Maintenance Diagram - MASTER TL-D Super 80 18W/840 1SL/25

