



# TL-D Standard Colours

## TL-D 30W/54-765 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Product data

| General Information                |                                 | Controls and Dimming            |                        |
|------------------------------------|---------------------------------|---------------------------------|------------------------|
| Cap-Base                           | G13 [Medium Bi-Pin Fluorescent] | Dimmable                        | Yes                    |
| Life to 50% Failures (Nom)         | 13,000 hour(s)                  |                                 |                        |
| Light Technical                    |                                 | Mechanical and Housing          |                        |
| Color Code                         | 54-765                          | Bulb Shape                      | T8 [26 mm (T8)]        |
| Luminous Flux                      | 1,825 lumen                     |                                 |                        |
| Color Designation                  | Cool Daylight                   | Approval and Application        |                        |
| Correlated Color Temperature (Nom) | 6200 K                          | Mercury (Hg) Content (Nom)      | 5.0 mg                 |
| Color rendering index (CRI)        | 72                              | Energy Consumption kWh/1000 h   | 36 kWh                 |
| Operating and Electrical           |                                 | Product Data                    |                        |
| Power Consumption                  | 30.0 W                          | Full product code               | 871869648774700        |
| Lamp Current (Nom)                 | 0.360 A                         | Order product name              | TL-D 30W/54-765 1SL/25 |
| Voltage (Nom)                      | 98 V                            | Order code                      | 48774700               |
| Voltage (Nom)                      | 98 V                            | Numerator - Quantity Per Pack   | 1                      |
|                                    |                                 | Numerator - Packs per outer box | 25                     |
|                                    |                                 | Material Nr. (12NC)             | 928025405451           |
|                                    |                                 | Full product name               | TL-D 30W/54-765 1SL/25 |

# TL-D Standard Colours


|                        |               |
|------------------------|---------------|
| EAN/UPC - Case         | 8718696487754 |
| EAN/UPC - Product/Case | 8718696487747 |

## Dimensional drawing




| Product                | D (max) | A (max)  | B (max)  | B (min)  | C (max)  |
|------------------------|---------|----------|----------|----------|----------|
| TL-D 30W/54-765 1SL/25 | 28 mm   | 894.6 mm | 901.7 mm | 899.3 mm | 908.8 mm |

## Photometric data




Spectral Power Distribution Colour - TL-D 30W/54-765 1SL/25

## Lifetime




Life Expectancy Diagram - TL-D 30W/54-765 1SL/25



Life Expectancy Diagram - TL-D 30W/54-765 1SL/25

## TL-D Standard Colours

### Lifetime



Lumen Maintenance Diagram - TL-D 30W/54-765 1SL/25

