



# MASTER MHN-LA

## MASTER MHN-LA 1000W/956 230V XWH

Compact quartz metal halide lamps with double-pinch

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Operating and Electrical	
Cap base	X528 [ X528]	Colour rendering index (nom.)	80
Operating position	P5 [ Parallel +/-5D or Horizontal(HOR)]	Lamp supply voltage	230 V [ 230]
Life to 5% failures (nom.)	6000 h	Power (Rated) (Nom)	1040.0 W
Life to 10% failures (nom.)	8000 h	Lamp current run-up (max.)	15 A
Life to 20% failures (nom.)	10000 h	Lamp current (EM) (nom.)	9.3 A
Life to 50% failures (nom.)	15000 h	Ignition supply voltage (min.)	198 V
Light Technical		Voltage (Max)	140 V
Colour Code	956 [ CCT of 5,600 K]	Voltage (Min)	110 V
Luminous flux (rated) (min.)	82000 lm	Voltage (Nom)	125 V
Luminous flux (rated) (nom.)	87000 lm	Controls and Dimming	
Colour designation	Daylight	Dimmable	No
Lumen maintenance 1,000 hours (nom.)	90 %	Mechanical and Housing	
Lumen maintenance 2,000 hours (nom.)	80 %	Lamp Finish	Clear
Chromaticity coordinate X (nom.)	337	Cap-base information	Cable (C)
Chromaticity coordinate Y (nom.)	331		
Correlated Colour Temperature (Nom)	5600 K		
Luminous efficacy (rated) (nom.)	86.0 lm/W		

# MASTER MHN-LA

## Approval and Application

Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	95 mg
Energy consumption kWh/1,000 hours	1144 kWh

## UV

Specific eff. radiant power	270 mW/klm
-----------------------------	------------


## Luminaire Design Requirements

Bulb temperature (max.)	920 °C
Pinch temperature (max.)	350 °C

## Product Data

Full product code	871150020077800
Order product name	MASTER MHN-LA 1000W/956 230V XWH
EAN/UPC – product	8718291548218
Order code	20077800
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	928072205130
SAP net weight (piece)	132.000 g
ILCOS code	MN-1000-E-K-/H


## Dimensional drawing



Product	D (max)	O	X	A
MASTER MHN-LA 1000W/956 230V XWH	40 mm	40.5 mm	35 mm	286 mm

MHN-LA 1000W/956 230V XWH

## Photometric data




LDPO\_MHN-LA\_0003-Spectral power distribution Colour

# MASTER MHN-LA

## Lifetime



LDLE\_MHN-LA\_0001-Life expectancy diagram



LDLM\_MHN-LA\_0001-Lumen maintenance diagram

