



MSR

MSR 700 1CT/8

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap base	G22 [G22]	Colour rendering index (nom.)	75
Operating position	UNIVERSAL [Any or Universal (U)]	Power (Rated) (Nom)	700 W
Main application	Studio/Disco	Lamp current (nom.)	12 A
Life to 50% failures (nom.)	1000 h	Ignition supply voltage (min.)	207 V
System description	na [-]		
Light Technical		Controls and Dimming	
Colour Code	- [Not Specified]	Dimmable	No
Luminous flux (min.)	48000 lm		
Luminous flux (nom.)	55000 lm	Mechanical and Housing	
Chromaticity coordinate X (nom.)	325	Cap-base information	na [-]
Chromaticity coordinate Y (nom.)	320		
Correlated Colour Temperature (Nom)	5900 K	Luminaire Design Requirements	
Luminous efficacy (rated) (nom.)	80 lm/W	Bulb temperature (max.)	700 °C

MSR

Pinch temperature (max.)	350 °C
Product Data	
Full product code	872790091575400
Order product name	MSR 700 1CT/8
EAN/UPC – product	8727900915754
Order code	91575400

SAP numerator – quantity per pack	1
Numerator – packs per outer box	8
SAP material	928078005114
SAP net weight (piece)	0.120 kg


Dimensional drawing



MSR 700 1CT/8

Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR 700 1CT/8	30 mm	8.0 mm	74 mm	76 mm	75 mm	152 mm	42 mm

Photometric data



XDPO_XDMSR_700_--Spectral power distribution Colour

