



# MSR

## MSR 1200 1CT/3

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Product data

General Information		Operating and Electrical	
Cap-Base	G22 [G22]	Power Consumption	1,200 W
Operating Position	UNIVERSAL [Any or Universal (U)]	Lamp Current (Nom)	13.8 A
Life to 50% Failures (Nom)	800 hour(s)		
Light Technical		Controls and Dimming	
Color Code	- [Not Specified]	Dimmable	No
Luminous Flux	103,000 lumen		
Chromaticity Coordinate X (Nom)	325	Product Data	
Chromaticity Coordinate Y (Nom)	327	Full product code	872790091121300
Correlated Color Temperature (Nom)	5900 K	Order product name	MSR 1200 1CT/3
Luminous Efficacy (rated) (Nom)	88 lm/W	Order code	91121300
Color rendering index (CRI)	80	Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	3
		Material Nr. (12NC)	928078105114
		Full product name	MSR 1200 1CT/3

# MSR


EAN/UPC - Case	8727900911220
EAN/UPC - Product/Case	8727900911213

## Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR 1200 1CT/3	40 mm	10.0 mm	84 mm	86 mm	85 mm	175 mm	53 mm

## Photometric data



Spectral Power Distribution Colour - MSR 1200 1CT/3

