



MASTERColour CDM-T

MASTERColour CDM-T 150W/942 G12 1CT

Range of single-ended, compact, high-efficiency, discharge lamps with a stable color over lifetime and a crisp, sparkling light

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General information	
Cap base	G12 [G12]
Operating position	UNIVERSAL [Any or Universal (U)]
Life to 5% failures (nom.)	9000 h
Life to 10% failures (nom.)	10000 h
Life to 20% failures (nom.)	11000 h
Life to 50% failures (nom.)	12000 h
ANSI code HID	C142/E
	Sphere
Light technical	
Colour Code	942 [CCT of 4,200 K]
Luminous flux (nom.)	12100 lm

Luminous flux (rated) (min.)	10900 lm
Luminous flux (rated) (nom.)	12100 lm
Colour designation	Cool White (CW)
Lumen maintenance 10,000 hours (nom.)	70 %
Lumen maintenance 2,000 hours (min.)	75 %
Lumen maintenance 2,000 hours (nom.)	85 %
Lumen maintenance 5,000 hours (min.)	70 %
Lumen maintenance 5,000 hours (nom.)	80 %
Chromaticity coordinate X (nom.)	0.371
Chromaticity coordinate Y (nom.)	0.366
Correlated Colour Temperature (Nom)	4200 K
Luminous efficacy (rated) (nom.)	82 lm/W

MASTERCcolour CDM-T

Colour rendering index (nom.)	96
Operating and electrical	
Power (Rated) (Nom)	150.1 W
Lamp current run-up (max.)	2.5 A
Lamp current (EM) (nom.)	1.9 A
Ignition supply voltage (max.)	198 V
Ignition peak voltage (max.)	5000 V
Ignition supply voltage (min.)	198 V
Ignition peak voltage (min.)	3500 V
Re-ignition time (min.) (max.)	15 min
Ignition time (max.)	30 s
Voltage (Max)	98 V
Voltage (Min)	82 V
Voltage (Nom)	90 V
Controls and dimming	
Dimmable	No
Run-up time 90% (max.)	3 min
Mechanical and housing	
Lamp Finish	Clear
Bulb shape	T19 [T 19mm]
Approval and application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	10.4 mg
Mercury (Hg) content (nom.)	10.4 mg

Energy consumption kWh/1,000 hours	151 kWh
	473338

UV

PET (NIOSH) (min.)	8 h/500lx
Damage factor D/fc (max.)	0.4


Luminaire design requirements

Bulb temperature (max.)	650 °C
Cap-base temperature (max.)	280 °C
Cap-Base Temperature (Max)-DUP(do not use)	536 °F
Pinch temperature (max.)	350 °C
Pinch Temperature (Max)-DUP(do not use)	350 °C

Product data

Full product code	871150020005115
Order product name	MASTERCcolour CDM-T 150W/942 G12 ICT
	1CT
EAN/UPC – product	8711500200051
Order code	20005115
SAP numerator – quantity per pack	1
Local code description	8348310
Numerator – packs per outer box	12
SAP material	928084605131
Net Weight (Piece)	0.033 kg
ILCOS code	MT/UB-150/942-H-G12-21/100

Dimensional drawing




MASTERCcolour CDM-T 150W/942 G12 ICT



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERCcolour CDM-T 150W/942 G12 ICT	20 mm	0.75 in	8 mm	55 mm	57 mm	56 mm	110 mm

MASTERCcolour CDM-T

Photometric data



Lifetime



LDLE_CDM-T_150W_942-Life expectancy diagram

LDLM_CDM-T_150W_942-Lumen maintenance diagram

